

Steckhülsen 2,8 mm

Clips femelles

Receptacles

DIN 46247/1

* ausgenommen
* excepté
* excepted

Werkstoff/Matière/Material

.2 = Bronze/bronze


.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011

Strombelastbarkeit / Intensité admissible / Current carrying capacity:

0.3 – 0.5 mm² / 2.5 A max.

0.5 – 1.0 mm² / 6.0 A max.




mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
0.14-0.3	26-24	2.8 x 0.5	3760a.6	*	14	6.3		5	2	0.25	3975b, 3984g 4084.3
	26-24	2.8 x 0.8	3762a.6	*	14	6.3		5	2	0.25	
	26-24	2.8 x 1.2	3762c.6	*	14	6.3		5	2	0.25	
0.3-0.5	24-22	2.8 x 0.5	3760b.6	46247/T1	14	6.3	3.3	5.5	2.9	0.25	3975b, 3984a 3988n, 4084.3
	24-22	2.8 x 0.8	3762b.2	46247/T1	14	6	4	5.5	2.9	0.25	
	24-22	2.8 x 0.8	3762b.6	46247/T1	14	6	4	5.5	2.9	0.25	
0.5-1	22-18	2.8 x 0.5	3764.6	46330/T2	12.5	5	3.3	5.5	2.5	0.25	3975b, 3984a 3988n, 4084.3
	22-18	2.8 x 0.8	3765.6	46330/T2	12.5	5	3.3	5.5	2.9	0.3	
	22-18	2.8 x 0.5	3766.6	46247/T1	14	6.3	3.3	5.5	2.9	0.25	
	22-18	2.8 x 0.8	3767.2	46247/T1	14	6.3	3.3	5.5	2.9	0.25	
	22-18	2.8 x 0.8	3767.6	46247/T1	14	6.3	3.3	5.5	2.9	0.25	

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011




mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
0.14-0.3	26-24	2.8 x 0.8	3763a.6	46340/T1	14	6.3	5.6	5.5	2.5	0.25	3975b, 3984g
0.5-1	22-18	2.8 x 0.8	3769.6	*	15.5	8	8.3	5.5	2.5	0.3	3975b, 3984a 3988n, 4084.3

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011




mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
0.5-1	22-18	2.8 x 0.5	3761a.6	*	9	5		1.9		0.25	3975b, 3988n
	22-18	2.8 x 0.8	3761.6	*	9	5		1.9		0.25	

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating
Seite/page/page 5.011



mm ²	AWG	Grösse Grandeur Size	Artikelnummer Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Werkzeuge Outils Toolings
0.5-1	22-18	2.8 x 0.5	3764w.6	*	8	5	3.3	7.2	2.5	0.3	3973b,
	22-18	2.8 x 0.8	3765w.6	*	8	5	3.3	7.2	2.5	0.3	3984wx