





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING


914CE2-21



NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 2.7 LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.01) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ± WEIGHT	
RELEASE FORCE — — — 1.0 LB MIN	5A 1/10HP 125 OR <u>250</u> VAC  		
DIFFERENTIAL TRAVEL — — — .004 MAX			
OVERTRAVEL — — — — — .118 MIN			



914CE2-21

M

DRAWING
NUMBER

1

ISSUE

REPLACES

RELEASE NO. PR-18774

CHECK

REVISIONS

CHECK

CHECK

24 OCT 90

SAV

DRAWN

DDM/CAD