

HONEYWELL
PART NUMBER


11SM405

PRODUCT CODE

TWY0500

REV	DOCUMENT	CHANGED BY	CHECK
7	0038104	PK 23APR08	ASD

PLASTIC PLUNGER



NOTES

- ▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-DEAD BREAK CONDITIONS
- A - MAX AMOUNT PERMISSIBLE — — — .0002 IN.
- 4-SWITCH WILL WITHSTAND TEMPERATURE OF 250°F.

RELEASE NO. SR - 10640

REPLACES -

CHARACTERISTICS

OPERATING FORCE — — — 3 1/2 OZ MAX

RELEASE FORCE — — — — 1 OZ MIN

DIFFERENTIAL TRAVEL — — .0005 - .0015

OVERTRAVEL — — — — .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP

MAXIMUM INRUSH 24 AMP

APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	UL, CSA	5A, 250 VAC

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±

THIRD ANGLE PROJECTION



DRAWN	VK	27 NOV 07
CHECK	RJ	27 NOV 07

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	11SM405	7
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1