




COIL: @ 25°C

RESISTANCE 1560 OHMS $\pm 10\%$

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.2 VDC

MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX. RELEASE TIME 1.5 MS MAX. CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/25/96 CK 126/206/203

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. QPL
CUST. NO. M39016/9-018L

TYPE JMA RELAY

JMAW-26XL