

LOC		DIST		REVISIONS							
AF		50		P	LTR	DESCRIPTION			DATE	DWN	APVD
					H4	REVISED PER ECR-12-009158			23MAY2012	KH	GJ

D

C

B



A

D

C

B

A



1 MATERIAL:
HOUSING: PBT, UL 94 V-0, COLOR:BLACK
SCREWS (6mm AND #10): STEEL
CLAMP BLOCK: ALUMINUM
GROUND LINK: COPPER

2 FINISH:
6mm SCREW: ZINC
#10-32 SCREW: NICKEL
CLAMP BLOCK: TIN

3 REFER TO TYCO ELECTRONICS DRAWING
C-1604281 FOR REQUIRED SCREW.

4 DESIGNED FOR USE IN ELECTRIC RANGES AND RECOGNIZED UNDER
UL/CSA REQUIREMENTS; CONDITIONS OF ACCEPTABILITY APPLY
PER UL FILE, SEE APPLICATION SPECIFICATION.

5 SCREWS PACKAGED 3 PER POLY BAG.


6 SCREWS BULK PACKAGED, 360 PER POLY BAG

7 SEE DRAWING C-1604281 FOR REQUIRED SCREWS

8 PRELIMINARY - NOT FOR PRODUCTION


9 OBSOLETE

SCREW, M6 - 1
6.35 HEX HEAD WITH CROSS RECESS,
3 PLACES




ACCEPTS RING-TONGUE OR
OPEN SPADE TERMINALS
6 PLC

0.50±0.02



-	SUPPLIED UNINSTALLED	3	SUPPLIED UNINSTALLED	1604532-9
3	SUPPLIED UNINSTALLED	-	NOT SUPPLIED	1604532-8
-	NOT SUPPLIED	3	INSTALLED	1604532-7
3	SUPPLIED UNINSTALLED	3	INSTALLED	1604532-6
-	NOT SUPPLIED	-	NOT SUPPLIED	1604532-5
3	INSTALLED	3	SUPPLIED UNINSTALLED	1604532-4
3	SUPPLIED UNINSTALLED	3	INSTALLED	1604532-3
3	INSTALLED	3	INSTALLED	1604532-2
-	NOT SUPPLIED	3	SUPPLIED UNINSTALLED	1604532-1

QTY	#10-32 UNF	QTY	M6 - 1	ASSEMBLY PART NUMBER
SCREW ASSEMBLY OPTIONS				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG 09NOV2004	 TE Connectivity	
DIMENSIONS:		CHK D DECKER 09NOV2004		
mm		APVD D DECKER 09NOV2004	NAME	
		PRODUCT SPEC 108-2136 APPLICATION SPEC 114-13100	ASSEMBLY, TERMINAL BLOCK LOW PROFILE POWER BLOCK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:			SIZE	
9 PLC ±			CAGE CODE	
2 PLC ±0.25			DRAWING NO	
3 PLC ±			RESTRICTED TO	
4 PLC ±			-	
ANGLES ±1°		WEIGHT		
FINISH		CUSTOMER DRAWING		
		SCALE 2:1		
		SHEET 1 OF 1		
		REV H4		