

**6LS1-4C**

( Home : Products : Switches : MICRO SWITCH™ Limit Switches : MICRO SWITCH™ Medium-Duty Limit Switches : LS )

Distributor Inventory

Input part number for stock availability



Enclosed Switches Series LS: Side Rotary with Yoke Style Lever; Steel Rollers;  
1NC 1NO DPDT Snap Action, Maintained, Double Break; 20 mm [0.79 in] conduit;  
Compact/Non Plug-in

Actual product  
appearance may vary.

Sales &amp; Service

Distributor Inventory

Overview

**Specs**

Documentation

Application Notes

**Product Specifications**

Availability	Global
Operating Force (OF)	0,34 N m [3 in lb] max.
Pretravel (PT)	55° max.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Side Rotary
Lever Type	Yoke Style Roller Lever with Steel Rollers (.75 in dia. x .25 in wide)
Circuitry	1NC 1NO SPDT Snap Action, Maintained, Double Break
Ampere Rating	10 A Ind./0.8 A Res./0.4 Res./0.1 A Res.
Supply Voltage	120 Vac, 240 Vac, 480 Vac/115 Vdc/230 Vdc/550 Vdc
Housing Material	Zinc Die-Cast
Termination Type	20 mm [0.79 in] Conduit
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Operating Temperature	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	Solder terminals, Two-position maintained
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

**Narrow Your Search****Modify Your Search****Products**

Select Option

**Technology**

Select Option

**Industries Served**

Select Option

**Product Search**

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

☐ New Products Only☒ Entire Product Catalog**Search****My Links**

eCOM Login  
Request Access to eCOM  
Rep/AD Portal Login  
Rep/AD Portal Access Request  
Sample Request  
Digital University Login

**Literature and Media**

Data Sheets  
Videos  
Literature  
Literature Request  
White Papers  
Application Notes

**Contacts**

Customer Service  
Technical Support  
Global Sales & Service  
Website Feedback

Limitless Microsite  
Supplier Microsite

Application Demos



[Terms & Conditions](#)

[Privacy Statement](#)

[Site Map](#)