

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

V3-3045

CK-X3465

V3-3045

M

DRAWING
NUMBER

ISSUE

REVISIONS

REVISIONS

A CO 52718

3 WJM FEB 83

B 0054315

JAP JAN 84

C 0055729

K E W 29 AUG 84

D 0055729

SMA 1 OCT 85

E CO 76104

GRT 9 OCT 93

FO-52848-A

J A P 21 DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

DEC 82

REPLACES X76257-V3

RELEASE NO. PR-11793

CHECK

CHECK



CHECK

CHECK

CHECK

CHECK

CHECK




NOTE -

- 1 - TERMINALS ARE PLATED FOR SOLDERING
- 2 - PLUNGER MATERIAL WILL WITHSTAND TEMPERATURE OF 300° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 150 GRAM MAX
RELEASE FORCE — — — — 15 GRAM MIN
DIFFERENTIAL TRAVEL — — — .001-.006
OVERTRAVEL — — — — .050 MIN
FREE POSITION — — — — .625 MAX
RELEASE TRAVEL — — — — .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L83
15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DM.	TOL.	DM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/64	X	0.015
ONE PLACE	X.X	0.0015	X.X	0.0015
TWO PLACES	X.XX	0.0005	X.XX	0.0005
THREE PLACES	X.XXX	0.0001	X.XXX	0.0001
ANGLES				

SI METRIC

US CUSTOMARY

DESIGN UNITS

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3-3045](#)