

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0548020411

Status:

Obsolete

Description:

0.80mm (.031") Pitch IEEE 1394a-2000 Shielded I/O PCB Socket, Right Angle, with Flange, Inverse Type, Unthreaded Hole

Replacement Part Number:

548020419

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Documents:

[Drawing \(PDF\)](#)

General	
Product Family	I/O Connectors
Series	54802
Application	Wire-to-Board
Comments	Inverse Type
Component Type	Receptacle
Obsolete Date	2004/08/01
Product Name	IEEE 1394
Replacement Part Number	548020419
Type	N/A
Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Right Angle
PC Tail Length	2.80mm (.110")
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	0.80mm (.031")
Pitch - Termination Interface	0.80mm (.031")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	3.048µm (120µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	5V
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-54030-032, PS-54030-033, PS-54030-034

Search Parts in this Series

54802Series

Mates With

IEEE1394 4Pin Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION