

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	T4	REVISED PER ECO-11-004587	11MAR11	RK	HMR

PHYSICAL PROPERTIES:
HOUSING MATERIAL: PBT
FLAMMABILITY: UL94V-0
COLOR: BLACK
MAX BOW/WARP: .0056 IN/IN.

MECHANICAL:
PITCH (TERMINAL SPACING): .563"
WIRE RANGE: 10-22 AWG
RECOMMENDED TIGHTENING TORQUE: 14IN-LBS MAX.

ELECTRICAL PROPERTIES:
MAXIMUM CURRENT: 30A
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:
OPERATING TEMP RANGE: -40°C TO 120°C

TERMINAL:
TERMINALS: BRASS, TIN PLATED. (UNLESS OTHERWISE STATED)
SCREWS: 8-32 STEEL, NICKEL PLATED. (UNLESS OTHERWISE STATED)
Q.C. TABS: BRASS, NICKEL PLATED.

△

STAINLESS STEEL SCREWS.

△

WHITE INK STAMP.

△

NICKEL PLATED BRASS TERMINALS.

△

NICKEL PLATED BRASS SCREWS.

△

SEE FIGURE.

△

PRELIMINARY PART NUMBER.

△

OBSOLETE PART NUMBER.

△

TE CONNECTIVITY LOGO LOCATED APPROXIMATE AREA SHOWN.

△	-	-	-	-	-	-	-	-	-	-	7.886	8.323	13	1-1546310-3
△	-	-	-	-	-	-	-	12	12	12	7.323	7.760	12	4-1546310-8
△	-	8	-	-	-	12	12	12	-	-	7.323	7.760	12	4-1546310-7
	-	-	-	-	12	12	12	-	-	-	7.323	7.760	12	4-1546310-6
	-	-	-	-	-	-	-	-	-	-	7.323	7.760	12	1-1546310-2
	-	-	-	-	-	-	-	-	-	-	6.760	7.179	11	1-1546310-1
	-	-	-	-	-	-	-	-	-	-	6.197	6.634	10	1-1546310-0
	-	-	-	-	-	-	-	-	-	-	5.634	6.071	9	1546310-9
△	-	-	-	-	-	-	-	-	-	8	5.071	5.508	8	4-1546310-5
	-	8	8	-	-	-	-	-	-	-	5.071	5.508	8	2-1546310-9
	-	-	-	-	-	-	-	-	-	-	5.071	5.508	8	1546310-8
	-	-	-	-	-	7	-	-	-	-	4.508	4.945	7	3-1546310-8
	-	-	-	-	-	-	-	-	-	-	4.508	4.945	7	1546310-7
△	-	-	-	-	-	-	-	-	-	6	3.945	4.382	6	4-1546310-4
△	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	4-1546310-3
	-	-	-	-	-	-	-	-	-	6	3.945	4.382	6	4-1546310-2
△	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	3-1546310-1
	-	-	-	-	-	6	-	-	-	-	3.945	4.382	6	3-1546310-0
	-	6	6	-	-	-	-	-	-	-	3.945	4.382	6	2-1546310-8
△	-	1	1	-	-	5	1	-	-	-	3.945	4.382	6	2-1546310-6
△	-	-	-	-	-	-	-	6	-	-	3.945	4.382	6	2-1546310-3
△	-	-	-	-	6	-	-	-	-	-	3.945	4.382	6	2-1546310-2
△	-	-	-	-	-	-	-	-	6	6	3.945	4.382	6	2-1546310-1
△	-	-	-	-	-	-	-	6	6	-	3.945	4.382	6	1546636-1
△	-	-	-	6	-	-	-	6	-	-	3.945	4.382	6	1-1546310-9
△	-	-	-	6	-	-	-	-	-	-	3.945	4.382	6	1546589-1
	-	-	-	-	-	-	-	-	-	-	3.945	4.382	6	1546310-6
	-	-	-	-	-	5	-	-	-	-	3.382	3.819	5	3-1546310-7
△	-	1	1	-	-	-	1	-	5	-	3.382	3.819	5	2-1546310-7
	-	-	-	-	-	-	-	-	-	-	3.382	3.819	5	1546310-5
△	-	-	-	-	-	-	-	4	4	4	2.819	3.256	4	5-1546310-0
△	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	4-1546310-1
△	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	4-1546310-0
△	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	3-1546310-9
	-	-	-	-	-	-	-	-	-	-	2.819	3.256	4	1546310-4
△	-	-	-	-	-	-	-	-	-	-	2.256	2.693	3	2-1546310-5
△	-	-	-	-	-	-	-	3	1	-	2.256	2.693	3	2-1546310-4
△	-	-	-	1	2	-	-	1	-	-	2.256	2.693	3	2-1546310-0
	-	-	-	-	-	-	-	-	-	-	2.256	2.693	3	1546310-3
	-	-	-	-	-	-	-	2	-	2	1.693	2.130	2	5-1546310-1
	-	-	-	-	-	-	-	-	-	-	1.693	2.130	2	1546310-2
NOTES	9	8	7	6	5	4	3	2	1		DIM B	DIM A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

MATERIAL

-

DWN
S SCHLEGEL
CHK
S YODER
APVD
S YODER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-
CUSTOMER DRAWING

16FEB2007
2/16/07
2/16/07

TE Connectivity

14.3 (.563) DBL ROW BARRIER STRIP
W/O WASHER

SIZE
A2
CAGE CODE
00779
DRAWING NO
1546310
RESTRICTED TO
-

SCALE
NTS
SHEET
1 of 4
REV
T4

1471-9 (3/11)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D

C

B






A

D

C

B

A




2	—	—	—	—	—	—	2	—	2	—	1.693	2.130		5-1546310-1								
	—	—	—	—	—	—	—	—	—	—	10.701	11.138	18	1-1546310-8								
	—	—	—	—	—	—	—	—	—	—	10.138	10.575	17	1-1546310-7								
	—	—	—	—	—	—	—	—	—	—	9.575	10.012	16	1-1546310-6								
	—	—	—	—	—	—	—	—	—	—	9.012	9.449	15	1-1546310-5								
2 6	—	—	—	—	—	—	—	14	14	14	8.449	8.886	14	4-1546310-9								
	—	—	—	—	—	—	—	—	—	—	8.449	8.886	14	1-1546310-4								
NOTES	9	OTB JUMPER	8	.250 QC TAB 90° DOUBLE SIDE	7	.250 QC TAB 90°/45° DOUBLE SIDE	6	.250 QC TAB 90° DOUBLE SIDE	5	.250 QC TAB 45° DOUBLE SIDE	4	.250 QC TAB STRAIGHT DOUBLE SIDE	3	.250 QC TAB 90° SINGLE SIDE	2	.250 QC TAB 45° SINGLE SIDE	1	.250 QC TAB STRAIGHT SINGLE SIDE	DIM B	DIM A	NO. OF POSN	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN S SCHLEGEL 16FEB2007	TE Connectivity			
DIMENSIONS: INCHES										CHK S YODER 2/16/07				
TOLERANCES UNLESS OTHERWISE SPECIFIED:										APVD S YODER 2/16/07	NAME 14.3 (.563) DBL ROW BARRIER STRIP W/O WASHER			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH										PRODUCT SPEC APPLICATION SPEC				
MATERIAL										WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=1546310	RESTRICTED TO -
CUSTOMER DRAWING										SCALE NTS	SHEET 2 of 4	REV T4		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		-	SEE SHEET 1	-	-	-

D




2-1546310-0




2-1546310-6

C




1546636-1

B



2-1546310-4



2-1546310-7

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL CHK S YODER APVD S YODER PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		16FEB2007 2/16/07 2/16/07		 TE Connectivity			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		14.3 (.563) DBL ROW BARRIER STRIP W/O WASHER			
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		RESTRICTED TO		—			
MATERIAL —		FINISH —		A2 00779 C=1546310		DRAWING NO SCALE NTS SHEET 3 of 4 REV T4			
CUSTOMER DRAWING									

D

C

B

A

1546310

