

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		J1	REVISED PER ECO-10-025533	15DEC10	HMR	JO

- 1

CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .150±.003, TOLERANCE NON-CUMULATIVE.
2. USE OF EXTRACTION TOOL #91052-1 TO REMOVE RECEPTACLE CONTACTS FROM HOUSING.



OBSOLETE	1.350	.475	.625	.300	.450	12	87148-8
OBSOLETE	4.950	2.275	2.425	2.100	2.250	60	87148-7
OBSOLETE	1.200	.475	.475	.300	.300	10	87148-6
OBSOLETE	3.450	1.525	1.675	1.350	1.500	40	87148-5
	2.850	1.225	1.375	1.050	1.200	32	87148-4
OBSOLETE	2.550	1.075	1.225	.900	1.050	28	87148-3
OBSOLETE	1.950	.775	.925	.600	.750	20	87148-2
OBSOLETE	1.650	.625	.775	.450	.600	16	87148-1
	E	D	C	B	A	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BOB BOLES CHK P.SREMCICH APVD P.SREMCICH PRODUCT SPEC APPLICATION SPEC — WEIGHT — CUSTOMER DRAWING	17OCT89 BG 05OCT93 05OCT93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME HOUSING, MOD IV, .150 X .150 GRID, DOUBLE ROW, CRIMP SNAP-IN (WITH MOUNTING EARS)			
	0 PLC	±	—	SIZE A2 CAGE CODE 00779 DRAWING NO C=87148 RESTRICTED TO —			
	1 PLC	±	—				
	2 PLC	±	—				
	3 PLC	±	—				
	4 PLC	±	.005				
MATERIAL GLASS FILLED NYLON COLOR—BLACK PER ASTM D4066		FINISH —		SCALE 4:1 SHEET 1 of 1 REV J1			
		ANGLES ± —					