



General ordering data

Order No.	1813260000
Part designation	SFC 0/30 NEUTRAL GE
Version	Conductor markers, L x W: 30 x 4 mm, Polyamide, yellow
EAN	4032248297009
Qty.	150 pc(s).

Markings

Cadmium	no
Can be labelled with thermal transfer printers	No
Can be printed with plotter	Yes
Can be written with dot-matrix printer	No
Can be written with laser printer	No
Conductor O.D., max.	2.5 mm
Conductor O.D., min.	1.5 mm
Conductor cross-section, max.	1 mm ²
Conductor cross-section, min.	0.5 mm ²
Function	Conductor and cable markers
Halogen	no
Height	5 mm
Insulation cross-section, max.	2.5 mm
Length	30 mm
Material	Polyamide
Material colour	yellow
Material colour according to resistance code	4
Max. temperature, continuous	100 °C
Min. temperature, continuous	-40 °C
Pin can be written (STI)	Yes
PrintJet	Yes
Printed characters	without
Silicone	no
Speed marking laser	Yes
Type of printing	Neutral
UL 94 flammability class	V2

Markings

Width 4 mm

Approvals

Approvals institutes n.a.

Classifications

ETIM 2.0	EC001530
ETIM 3.0	EC001530
eClass 4.1	24-19-02-19
eClass 5.0	27-14-91-03
eClass 5.1	27-14-91-03

Similar products

Order No.	Part designation	Version
1805730000	SFC 1/30 NEUTRAL GE	Conductor markers, L x W: 30 x 4 mm, Polyamide, yellow
1805830000	SFC 2/30 NEUTRAL GE	Conductor markers, L x W: 30 x 4 mm, Polyamide, yellow
1025320000	SFC 3/30 MC NE GE	Conductor markers, L x W: 30 x 4 mm, Polyamide, yellow