






LOC		DIST		REVISIONS			
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-11-025276	24DEC11	KH	DY

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A. SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



RIGHT GUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER	24DEC11	 TE Connectivity			
DIMENSIONS:		CHK J. E. EBY	24DEC11				
mm		APVD J. E. EBY	24DEC11	NAME IMPACT, 3 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, LEFT END WALL SIGNAL MODULE, 0.39 PTH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO			
9 PLC ±		APPLICATION SPEC		A100779C=2007799			
1 PLC ±0.25		WEIGHT		RESTRICTED TO			
2 PLC ±0.13		CUSTOMER DRAWING		SCALE 6:1 SHEET 1 OF 2 REV C			
3 PLC ±							
4 PLC ±							
ANGLES ±							
FINISH SEE TABLE							

LOC		DIST		REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			-	SEE SHEET 1	-	-	-	

	H	5.5	8-2007799-6
	H	4.9	8-2007799-5
	H	4.5	8-2007799-4
	H	5.5	8-2007799-3
	H	4.9	8-2007799-2
	H	4.5	8-2007799-1
	G	5.5	7-2007799-6
	G	4.9	7-2007799-5
	G	4.5	7-2007799-4
	G	5.5	7-2007799-3
	G	4.9	7-2007799-2
	G	4.5	7-2007799-1
	F	5.5	6-2007799-6
	F	4.9	6-2007799-5
	F	4.5	6-2007799-4
	F	5.5	6-2007799-3
	F	4.9	6-2007799-2
	F	4.5	6-2007799-1
	E	5.5	5-2007799-6
	E	4.9	5-2007799-5
	E	4.5	5-2007799-4
	E	5.5	5-2007799-3
	E	4.9	5-2007799-2
	E	4.5	5-2007799-1
	D	5.5	4-2007799-6
	D	4.9	4-2007799-5
	D	4.5	4-2007799-4
	D	5.5	4-2007799-3
	D	4.9	4-2007799-2
	D	4.5	4-2007799-1
	C	5.5	3-2007799-6
	C	4.9	3-2007799-5
	C	4.5	3-2007799-4
	C	5.5	3-2007799-3
	C	4.9	3-2007799-2
	C	4.5	3-2007799-1
	B	5.5	2-2007799-6
	B	4.9	2-2007799-5
	B	4.5	2-2007799-4
	B	5.5	2-2007799-3
	B	4.9	2-2007799-2
	B	4.5	2-2007799-1
	A	5.5	1-2007799-6
	A	4.9	1-2007799-5
	A	4.5	1-2007799-4
	A	5.5	1-2007799-3
	A	4.9	1-2007799-2
	A	4.5	1-2007799-1
	-	5.5	2007799-6
	-	4.9	2007799-5
	-	4.5	2007799-4
	-	5.5	2007799-3
	-	4.9	2007799-2
	-	4.5	2007799-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. K. SHOBER	24DEC11	TE Connectivity		
			CHK	J. EABY	24DEC11	NAME IMPACT, 3 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, LEFT END WALL SIGNAL MODULE, 0.39 PTH		
			APVD	J. EABY	24DEC11			
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC		
mm			9 PLC ±.1			APPLICATION SPEC		
			1 PLC ±0.25			WEIGHT		
			3 PLC ±0.13			CUSTOMER DRAWING		
			5 PLC ±			SCALE		
			4 PLC ±			SHEET		
			ANGLES ±			OF		
			FINISH ±			REV		
MATERIAL			SEE TABLE			C		
-			-			2		
-			-			2		
						5:1		
						A100779		
						C=2007799		
						-		
						-		