

Recommended land pattern dimension of PWB

a

c

a

b

Size code

a

b

c

Size code	a	b	c
D2E	2.4	2.9	3.7
D3L	2.4	2.9	3.7
D4	2.4	2.9	3.7

(unit : mm)

Size list

RV:Rated voltage

RV	2.0	2.5	4.0	6.3	10.0
μF					
150					D3L
220	D2E			D3L	
330	D2E	D3L	D3L	D3L	
470		D4,D3L	D3L	D4	
680		D4,D3L	D4		
1,000		D4			

93

TPF series characteristics list

Size code	Part number	Rated voltage (V)	Rated temperature (°C)	Rated capacitance (μF)	Category voltage (V)	Category temperature (°C)	DF (% max)	LC (μA) max/5min.	ESR (mΩ max) 100kHz/20°C	Maximum allowable ripple current (mA rms) 100kHz※1	MSL	
											Reflow temp. ≤ 260°C	Reflow temp. ≤ 250°C
D2E	2TPF330M6	2.0	105	330	2.0	105	10	132.0	6	4700	—	2a
	2TPF220M6	2.0	105	220	2.0	105	10	88.0	6	4700	—	2a
D3L	10TPF150ML	10	105	150	10	105	10	150.0	15	3600	—	2a
	6TPF330M9L	6.3	105	330	6.3	105	10	207.9	9	3900	3	2a
	6TPF220ML	6.3	105	220	6.3	105	10	138.6	12	4000	3	2a
	6TPF220M9L	6.3	105	220	6.3	105	10	138.6	9	4600	3	2a
	6TPF220M5L	6.3	105	220	6.3	105	10	138.6	5	6100	3	2a
	4TPF470ML	4.0	105	470	4.0	105	10	188.0	10	4400	3	2a
	4TPF330ML	4.0	105	330	4.0	105	10	132.0	12	4000	3	2a
	2R5TPF680ML	2.5	105	680	2.5	105	10	170.0	10	4400	3	2a
	2R5TPF680M7L	2.5	105	680	2.5	105	10	170.0	7	4400	3	2a
	2R5TPF680M6L	2.5	105	680	2.5	105	10	170.0	6	4400	3	2a
	2R5TPF470ML	2.5	105	470	2.5	105	10	117.5	10	4400	3	2a
	2R5TPF470M7L	2.5	105	470	2.5	105	10	117.5	7	4400	3	2a
	2R5TPF470M6L	2.5	105	470	2.5	105	10	117.5	6	4400	3	2a
	2R5TPF330M7L	2.5	105	330	2.5	105	10	82.5	7	4400	3	2a
	6TPF470MAH	6.3	105	470	6.3	105	10	296.1	10	4400	3	2a
	4TPF680MAH	4.0	105	680	4.0	105	10	272.0	10	4400	3	2a
D4	ETPF1000M6H	2.5	105	1000	2.5	105	10	250.0	6	5600	3	2a
	ETPF1000M5H	2.5	105	1000	2.5	105	10	250.0	5	6100	3	2a
	ETPF680M5H	2.5	105	680	2.5	105	10	170.0	5	6100	3	2a
	ETPF470M5H	2.5	105	470	2.5	105	10	117.5	5	6100	3	2a

※1 100k to 500kHz,45°C ※2 Under development