


[Connectors > Connector Accessories > Connector Hardware](#)Hardware Accessory Function: **Mounting**Connector Hardware Accessory Type: **Grounding Block**Operating Temperature (Max): **125 °C [257 °F]**Operating Temperature Range: **-65 – 125 °C [-85 – 257 °F]**

Features

Product Type Features

Hardware Accessory Function	Mounting
Connector Hardware Accessory Type	Grounding Block

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Product Compliance


[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (37% in component) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

[Product Compliance Disclaimer](#)

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 513319-000
MTC100Q-SH2-P22

Customers Also Bought



TE Part #043951-000
243D022-25-0



TE Part #NB15924001
RT-375-1/16-X-SP



TE Part #ZPF00000000099705
DMC-M 99-01 BN



TE Part #258215-000
MTCP-122-20S1



TE Part #218163-001
22759/34-12-9



TE Part #5260010007
TC-CAPS-4001-9



TE Part #81541-23
CONT PIN



TE Part #6418370001
TMS-SCE-1/8-2.0-4



Documents

Product Drawings

CHA-0308

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_F94336-000_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_F94336-000_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_F94336-000_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[MTC Quick-Disconnect Connectors with Removable Contacts](#)

English