






- | | |
|----|--|
| 3 | MOUNTING HOLES. |
| 4 | POST TO BE SOLDER DIPPED.
CONN. MUST MEET REQUIREMENTS OF MIL-STD-202 METHOD 208. |
| 5 | CONTACT MATL.; GILDING METAL. GOLD OVER NICKEL. |
| 6 | TOLERANCE NON CUMULATIVE. |
| 7 | TAB-HOUSING MATL.; DIALLYL PHTHALATE, GLASS FILLED PER MIL-M-14, TYPE S.D.G.-F.
COLOR; GREEN. |
| 8 | CUT OUT FOR KEYING BOSS, LOCATED WHERE REQD. (OPTIONAL) |
| 9 | FROM EDGE OF P.C. BOARD TO FACE OF TAB-HOUSING. |
| 10 | TE CONNECTIVITY P/N NOT TO BE MARKED ON PART.
CAGE CODE #00779, DATE CODE, & CUSTOMER P/N TO BE MARKED ON PART, SEE TABLE. |
| 11 | TE CONNECTIVITY PART NUMBER, DATE CODE AND MILITARY PART NUMBER .062 HIGH, MARKED THIS AREA AND ALL EVEN NUMBERED CONTACTS MARKED THIS AREA. |
| 12 | "D" DIMENSION APPLIES TO CONTACT ONLY PRIOR TO SOLDER DIPPING. |

4805 (3/11)