



CIRCUIT: 2P, SPST
CONTACT CONFIGURATION
ON-OFF (ILLUMINATED)






ACTUATOR: TRANSLUCENT
GREEN LENS



SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
2-1	OPEN

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 12 VDC MAX.
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: -20°C to 85°C
- ▲ 9. LED: 12V GREEN
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLANT.



E-SWITCH®			
TITLE			
RR3112BBLKGRNGRNEF4 - SPECIAL			
SCALE			
2:1			
DATE			
1/8/2007			
DR			
BLR			
DWG			
F130513			
REV			
B			