



LOC	DIST	REVISIONS					
AD	38	P	LTR	DESCRIPTION	DATE	DRN	APRD
			G	OG3C-0202-03	25APR03	TK	JO

1. TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN HEADERS ARE HELD FLAT AGAINST POINTED CIRCUIT BOARD.
2. OBSOLETE PART NUMBER
3. .000100-.000200 BRIGHT TIN OVER .000050-.000100 NICKEL.
4. .000100-.000200 BRIGHT TIN-LEAD OVER .000050-.000100 NICKEL.
5. PRELIMINARY PART



RECOMMENDED HOLE LAYOUT

SUPERCEDED BY 3-103322-5

SUPERCEDED BY 3-103322-2

SUPERCEDED BY 3-103322-0

SUPERCEDED BY 2-103322-5

SUPERCEDED BY 2-103322-1

SUPERCEDED BY 1-103322-6

SUPERCEDED BY 1-103322-2

SUPERCEDED BY 103322-9

SUPERCEDED BY 103322-2

	$\frac{3}{4}$	.125	.318	.500	5	.584	12	$\frac{3}{4}$ 4-87543-3
	$\frac{4}{4}$	.125	.318	4.100	41	4.184	80	$\frac{4}{4}$ 4-87543-2
		.125	.318	4.000	40	4.084	80	$\frac{4}{4}$ 4-87543-1
		.125	.318	3.900	39	3.984	80	4-87543-0
		.125	.318	3.800	38	3.884	78	$\frac{4}{4}$ 3-87543-9
		.125	.318	3.700	37	3.784	76	$\frac{4}{4}$ 3-87543-8
		.125	.318	3.600	36	3.684	74	$\frac{4}{4}$ 3-87543-7
		.125	.318	3.500	35	3.584	72	$\frac{4}{4}$ 3-87543-6
5		.125	.318	3.400	34	3.484	70	3-87543-5
		.125	.318	3.300	33	3.384	68	$\frac{4}{4}$ 3-87543-4
		.125	.318	3.200	32	3.284	66	$\frac{4}{4}$ 3-87543-3
2		.125	.318	3.100	31	3.184	64	3-87543-2
		.125	.318	3.000	30	3.084	62	$\frac{4}{4}$ 3-87543-1
0		.125	.318	2.900	29	2.984	60	3-87543-0
5		.125	.318	2.800	28	2.884	58	$\frac{4}{4}$ 2-87543-9
		.125	.318	2.700	27	2.784	56	$\frac{4}{4}$ 2-87543-8
		.125	.318	2.600	26	2.684	54	$\frac{4}{4}$ 2-87543-7
		.125	.318	2.500	25	2.584	52	$\frac{4}{4}$ 2-87543-6
		.125	.318	2.400	24	2.484	50	2-87543-5
		.125	.318	2.300	23	2.384	48	$\frac{4}{4}$ 2-87543-4
		.125	.318	2.200	22	2.284	46	$\frac{4}{4}$ 2-87543-3
		.125	.318	2.100	21	2.184	44	$\frac{4}{4}$ 2-87543-2
-1		.125	.318	2.000	20	2.084	42	2-87543-1
		.125	.318	1.900	19	1.984	40	2-87543-0
		.125	.318	1.800	18	1.884	38	$\frac{4}{4}$ 1-87543-9
		.125	.318	1.700	17	1.784	36	$\frac{4}{4}$ 1-87543-8
		.125	.318	1.600	16	1.684	34	1-87543-7
6		.125	.318	1.500	15	1.584	32	1-87543-6
		.125	.318	1.400	14	1.484	30	1-87543-5
		.125	.318	1.300	13	1.384	28	$\frac{4}{4}$ 1-87543-4
		.125	.318	1.200	12	1.284	26	1-87543-3
2		.125	.318	1.100	11	1.184	24	1-87543-2
		.125	.318	1.000	10	1.084	22	1-87543-1
		.125	.318	.900	9	.984	20	1-87543-0
9		.125	.318	.800	8	.884	18	87543-9
		.125	.318	.700	7	.784	16	87543-8
		.125	.318	.600	6	.684	14	87543-7
		.125	.318	.500	5	.584	12	87543-6
		.125	.318	.400	4	.484	10	87543-5
		.125	.318	.300	3	.384	8	87543-4
		.125	.318	.200	2	.284	6	87543-3
2		.125	.318	.100	1	.184	4	87543-2
	$\frac{4}{4}$	.125	.318	—	—	.084	2	87543-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.E.PASTEL 11-20-87 CHK T.C. CLARK 11-23-87 APVD T.C. CLARK 11-23-87		 Tyco Electronics Corporation Harrisburg, Pa	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		0 P.L.C. ± . 2 P.L.C. ± . 3 P.L.C. ± . 4 P.L.C. ± . ANGLES ± .		ASSEMBLY, MOD II, HEADER, DOUBLE ROW, .100X.100	
		PRODUCT SPEC		SIZE	
MATERIAL		APPLICATION SPEC		PAGE CODE	
HSD-GLASS FILLED NYLON COLOR: BLACK CONTACT: PHOS BRONZE		FINISH		DRAWING NO	
SEE TABLE		WEIGHT		A2 00779 C=87543	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 1:1 SHEET 1 of 1 REV G	