


NOTES:


1. MATERIALS AND FINISHES:  
BODIES - BRASS, NICKEL PLATING  
CONTACT - BERYLLIUM COPPER, GOLD PLATING  
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:  
A. IMPEDANCE: 75 OHM  
B. FREQUENCY RANGE: DC - 3 GHz  
C. RETURN LOSS: 30 dB MIN @ 3 GHz
3. MECHANICAL:  
A. DURABILITY: 500 CYCLES MIN.  
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:  
A. QUANTITY: SINGLE PACK  
B. MARKING: BAG TO BE MARKED  
"AMPHENOL RF, APH-HDBNCJ-J, AND DATE CODE"

THIRD ANGLE PROJ. 

REV		DESCRIPTION	DATE	ECO	APPR
A		RELEASED TO MFG.	21-Oct-10	48164	TD



SCALE 5.000



## CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:  
<0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES  
± 0.05mm ± 0.1mm ± 0.2mm ± 0.3mm ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL SEE NOTES	DRAWN T.DENG	DATE 21-Oct-10	TITLE ADAPTOR, 75 OHM HD-BNC, JACK TO JACK	Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China <a href="http://www.amphenolrf.com">www.amphenolrf.com</a>
	ENGINEER BALAJI M	DATE 16-Mar-10		
REFERENCE EAR # 3967 CONFIGURATION LEVEL:	APPROVED S.HSIEH	DATE 22-Oct-10	SCALE: 12.0:1.0 SHEET 2 OF 2	DRAWING NO. APH-HDBNCJ-J ITEM NO. APH-HDBNCJ-J PART NO. APH-HDBNCJ-J
	CAD FILE Root Folder/HD-BNC/APH-HDBNCJ-J	DWG SIZE B	REV A	
FINISH				