




1 AMP PPF2136




2 AMP PPF2133





3 AMP PPF2138



6 AMP PPF2131



10 AMP PPF2139



PPF213★	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH	Connections Input	Output	Approvals UL	CE	SE
PPF2136-1/01	1	0.4mA	11.0	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF2133-2/01	2	0.4mA	3.0	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF2138-3/01	3	0.4mA	1.3	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF2131-6/01	6	0.4mA	0.7	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF2139-10/01	10	0.2mA	0.09	IEC 320	6.3 x 0.8 Faston	■	■	■



Temperature Range: -25°C to +85°C
Operating Voltage: 250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L + N to ground, 2700Vdc,
2 seconds

Varistor:
Zinc oxide type; energy absorption 21Joules
(current impulse defined in IEC 60-2 Section 6)
Varistor voltage: 430Vdc (measured at 1mA);
clamping voltage 710V at 10A.

- Approved
□ Submitted for Approval

DIMENSIONS

All dimensions are nominal and in mm



CIRCUIT DIAGRAM

