



STRIP MATERIAL NUMBER	FINISH
84524-0012	OVERALL NICKEL 80µ" MINIMUM
84524-0018	SELECTIVE HARD GOLD 30µ" MINIMUM OVER NICKEL 50µ" MINIMUM



WIRE INSULATION O.D. RANGE $\frac{.095-.150}{2.41-3.81}$

NOTES:

1. MATERIAL: COPPER ALLOY .0118/0.300 THICK.
2. FINISH: SEE CHART.
3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
4. TERMINAL FOR USE ON XRC CONNECTOR ASSEMBLIES.
5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.
6. TERMINALS COMPLY WITH SECTION 5.3.2 OF THE SAE J1939-11 STANDARD FOR SURFACE VEHICLE RECOMMENDED PRACTICE.



ADD NOTE 6 & UPDATE OD				QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: IPG2013-1752				2013/06/06		mm INCH		IN/MM		2:1		INCH		⊙ □	
DRAWN: WLEUNG				2013/06/07		4 PLACES ± --- ± ---		DRAWN BY		DATE		TITLE		XRC PIN TERMINAL 14-18AWG .095-.150" WIRE DIA.  MOLEX INCORPORATED	
CHKD: KJ02WIK				2013/06/07		3 PLACES ± --- ± .005		CHECKED BY		DATE					
APPR: JFURPHY				2013/06/20		2 PLACES ± .13 ± ---		RDEROSS		2009/04/15					
						1 PLACE ± --- ± ---		APPROVED BY		DATE					
						ANGULAR ± --- °		DTITUS		2010/10/13					
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
								SEE CHART		SD-84524-003				1 OF 1	
								SIZE B							