

85HF(R) SERIES

STANDARD RECOVERY DIODES

Stud Version

Features

- High surge current capability
- Designed for a wide range of applications
- Stud cathode and stud anode version
- Leaded version available
- Types up to 1600V V_{RRM}

85 A

Typical Applications

- Battery charges
- Converters
- Power supplies
- Machine tool controls

Major Ratings and Characteristics

Parameters	85HF(R)		Units
	10 to 120	140 to 160	
$I_{F(AV)}$	85	85	A
@ T_C	140	110	°C
$I_{F(RMS)}$	133		A
I_{FSM} @ 50Hz	1700		A
@ 60Hz	1800		A
I^2t @ 50Hz	14500		A ² s
@ 60Hz	13500		A ² s
V_{RRM} range	100 to 1200	1400 to 1600	V
T_J range	- 65 to 180	- 65 to 150	°C



85HF(R) Series

Bulletin I20203 rev. A 09/98

International
IR Rectifier

ELECTRICAL SPECIFICATIONS

Voltage Ratings

Type number	Voltage Code	V_{RRM} maximum repetitive peak reverse voltage V	V_{RSM} maximum non-repetitive peak reverse voltage V	I_{RRM} max. @ $T_J = T_J$ max. mA
85HF(R)	10	100	200	15
	20	200	300	
	40	400	500	
	60	600	720	9
	80	800	960	
	100	1000	1200	
	120	1200	1440	
	140	1400	1650	4.5
	160	1600	1900	

Forward Conduction

Parameter		85HF(R)		Units	Conditions			
		10 to 120	140 to 160					
I _{F(AV)}	Max. average forward current @ Case temperature	85	85	A	180° conduction, half sine wave			
		140	110	°C				
I _{F(RMS)}	Max. RMS forward current	133		A				
I _{FSM}	Max. peak, one-cycle forward, non-repetitive surge current	1700		A	t = 10ms	No voltage	Sinusoidal half wave, Initial T _J = T _J max.	
		1800			t = 8.3ms	reapplied		
		1450			t = 10ms	100% V _{RRM}		
		1500			t = 8.3ms	reapplied		
I ² t	Maximum I ² t for fusing	14500		A ² s	t = 10ms	No voltage		
		13500			t = 8.3ms	reapplied		
		10500			t = 10ms	100% V _{RRM}		
		9400			t = 8.3ms	reapplied		
I ² √t	Maximum I ² √t for fusing	16000		A ² √s	t = 0.1 to 10ms, no voltage reapplied			
V _{F(TO)1}	Low level value of threshold voltage	0.68		V	(16.7% × π × I _{F(AV)}) < I < π × I _{F(AV)} , T _J = T _J max.			
V _{F(TO)2}	High level value of threshold voltage	0.80			(I > π × I _{F(AV)}), T _J = T _J max.			
r _{f1}	Low level value of forward slope resistance	1.62		mΩ	(16.7% × π × I _{F(AV)}) < I < π × I _{F(AV)} , T _J = T _J max.			
r _{f2}	High level value of forward slope resistance	1.25			(I > π × I _{F(AV)}), T _J = T _J max.			
V _{FM}	Max. forward voltage drop	1.20		V	I _{pk} = 267A, T _J = 25°C, t _p = 400μs rectangular wave			

Thermal and Mechanical Specifications

Parameter		85HF(R)		Units	Conditions
		10 to 120	140 to 160		
T _j	Max. junction operating temperature range	-65 to 180	-65 to 150	°C	
T _{stg}	Max. storage temperature range	-65 to 180	-65 to 150		
R _{thJC}	Max. thermal resistance, junction to case	0.35		K/W	DC operation
R _{thCS}	Max. thermal resistance, case to heatsink	0.25			Mounting surface, smooth, flat and greased
	Maximum shock	1500g			see note (1)
	Maximum constant vibration	20g			50Hz see note (1)
	Maximum constant acceleration	5000g			Stud outwards see note (1)
T	Max. allowed mounting torque ±10%	2.3 - 3.4		Nm	Not lubricated threads
		20 - 30		lbf·in	
wt	Approximate weight	17 (0.6)		g (oz)	
	Case style	DO-203AB (DO5)			See Outline Table

(1) Available only for 88HF

ΔR_{thJC} Conduction

(The following table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC)

Conduction angle	Sinusoidal conduction	Rectangular conduction	Units	Conditions
180°	0.10	0.08	K/W	$T_j = T_j \text{ max.}$
120°	0.11	0.11		
90°	0.13	0.13		
60°	0.17	0.17		
30°	0.26	0.26		


Ordering Information Table

Device Code		85	HF	R	160	M
		①	②	③	④	⑤
1	-	85 = Standard device				
		86 = Not isolated lead				
		87 = Isolated lead with silicone sleeve				
		(Red = Reverse polarity)				
		(Blue = Normal polarity)				
		88 = Type for rotating application				
2	-	Standard diode				
3	-	None = Stud Normal Polarity (Cathode to Stud)				
		R = Stud Reverse Polarity (Anode to Stud)				
4	-	Voltage code: Code x 10 = V_{RRM} (See Voltage Ratings table)				
5	-	None = Stud base DO-203AB (DO-5) 1/4" 28UNF-2A				
		M = Stud base DO-203AB (DO-5) M6 X 1 - (Not available for 88HF)				

85HF(R) Series

Bulletin I20203 rev. A 09/98

Outlines Table



Outlines Table





Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics

85HF(R) Series

Bulletin I20203 rev. A 09/98

International
IOR Rectifier




Fig. 3 - Current Ratings Characteristics




Fig. 4 - Current Ratings Characteristics




Fig. 5 - Forward Power Loss Characteristics




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Forward Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 10 - Maximum Non-Repetitive Surge Current

85HF(R) Series

Bulletin I20203 rev. A 09/98

International
IR Rectifier




Fig. 11 - Forward Voltage Drop Characteristics




Fig. 12 - Thermal Impedance Z_{thJC} Characteristics

International
IR Rectifier

WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245 U.S.A. Tel: (310) 322 3331. Fax: (310) 322 3332.
EUROPEAN HEADQUARTERS: Hurst Green, Oxted, Surrey RH8 9BB, U.K. Tel: ++ 44 1883 732020. Fax: ++ 44 1883 733408.
IR CANADA: 15 Lincoln Court, Brampton, Markham, Ontario L6T3Z2. Tel: (905) 453 2200. Fax: (905) 475 8801.
IR GERMANY: Saalburgstrasse 157, 61350 Bad Homburg. Tel: ++ 49 6172 96590. Fax: ++ 49 6172 965933.
IR ITALY: Via Liguria 49, 10071 Borgaro, Torino. Tel: ++ 39 11 4510111. Fax: ++ 39 11 4510220.
IR FAR EAST: K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo, Japan 171. Tel: 81 3 3983 0086.
IR SOUTHEAST ASIA: 1 Kim Seng Promenade, Great World City West Tower, 13-11, Singapore 237994. Tel: ++ 65 838 4630.
IR TAIWAN: 16 Fl. Suite D.207, Sec. 2, Tun Haw South Road, Taipei, 10673, Taiwan. Tel: 886 2 2377 9936.

<http://www.irf.com>

Fax-On-Demand: +44 1883 733420

Data and specifications subject to change without notice.