

## C2012C0G2A102J060AA (TDK item description : C2012C0G2A102JT\*\*\*\*)

## Applications



Commercial Grade



Please refer to Part No. CGA4C2C0G2A102J060AA for automotive use.


## Feature

Mid

Mid Voltage (100 to 630V)

## Series

C2012 [EIA CC0805]



## Size

Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	0.60mm +/-0.15mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.50mm Min.
Recommended Land Pattern(PA)	1.00 to 1.30mm (Flow Soldering) 0.90 to 1.20mm (Reflow Soldering)
Recommended Land Pattern(PB)	1.00 to 1.20mm (Flow Soldering) 0.70 to 0.90mm (Reflow Soldering)
Recommended Land Pattern(PC)	0.80 to 1.10mm (Flow Soldering) 0.90 to 1.20mm (Reflow Soldering)
Recommended Slit Pattern(SD)	

## Electrical Characteristics





Capacitance	1nF +/-5%
Rated Voltage	100Vdc
Temperature Characteristic	C0G(0+/-30ppm/degC)
Q	1000 Min.
Insulation Resistance	10000MΩ Min.

## Other

Soldering Method	Reflow, Flow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.

**C2012C0G2A102J060AA**

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)



Ripple Temperature Rising
no data available