


# General Purpose Surface Mounted Resistors



## WCR Series

- Excellent reliability
- Wide range of sizes and ohmic values
- Wrap around terminations
- Inner electrode protection



## Electrical Data

	0201	0402	0603	0805	1206	1210	2010	2512
Power rating @ 70°C	watts	0.05	0.063	0.1	0.125	0.25	0.25	0.5
Resistance range	ohms	10R to 1MΩ	1R0 to 1MΩ			1R0 to 10M		
Limiting element voltage	volts	25	50	150		200		
TCR*	ppm/°C	250		100			200	
Resistance Tolerance	%			1				
Standard values				E24 or E96				
Ambient temperature range	°C			-55 to 155				
Zero-ohm Jumper Chip Rating	amps	0.5	1	1.5		2		
Zero-ohm Jumper Chip Resistance	milliohms			<50				

\* Notes – TCR for low values 1R to 10R: -400 to +600ppm/°C, 11R to 100R: ±200ppm/°C  
TCR for high values 3M3 to 10M: ±300ppm/°C

## Physical Data

Dimensions (mm)					
Style	L	W	T	C	A
0201	0.6 ± 0.03	0.3 ± 0.03	0.23 ± 0.03	0.12 ± 0.05	0.15 ± 0.05
0402	1.0 ± 0.05	0.5 ± 0.03	0.35 ± 0.05	0.2 ± 0.1	0.25 ± 0.1
0603	1.6 ± 0.15	0.8 ± 0.15	0.5 ± 0.15	0.25 ± 0.2	0.25 ± 0.2
0805	2.0 ± 0.2	1.25 ± 0.2 - 0.1	0.5 ± 0.15 - 0.10	0.4 ± 0.2	0.4 ± 0.2
1206	3.2 ± 0.1 - 0.25	1.6 ± 0.1 - 0.15	0.55 ± 0.15 - 0.1	0.5 ± 0.2 - 0.25	0.5 ± 0.2 - 0.25
1210	3.2 ± 0.1 - 0.2	2.6 ± 0.15	0.55 ± 0.15 - 0.1	0.5 ± 0.25	0.5 ± 0.2
2010	5.0 ± 0.15	2.5 ± 0.15	0.56 ± 0.15	0.60 ± 0.25	0.60 ± 0.25
2512	6.3 ± 0.15	3.2 ± 0.15	0.56 ± 0.15	0.60 ± 0.25	0.60 ± 0.25

Wrap-around terminations (3 faces)

## Construction


The chips have a high alumina substrate (96% minimum) with a ruthenium oxide resistance element and silver palladium, nickel and tin plated terminations. A glazed protection coat is applied to the resistive element (See Fig.1)

## Terminations

**Solderability** The terminations meet the requirements of IEC 115-1, Clause 4.17.3.2.

**Strength** The terminations meet requirements of IEC 68.2.21.

Figure 1



## General Note

TT electronics reserves the right to make changes in product specification without notice or liability.  
All information is subject to TT electronics' own data and is considered accurate at time of going to print.

# General Purpose Surface Mounted Resistors



## WCR Series

### Marking

All resistors are individually marked with 3 digits. The first two digits are the significant figures and the third defines the number of added zeros. Jumpers are marked 000. Types 0201 and 0402 have no marking.

E96 1% components that can not be marked with 4 digits will be marked with a standard 3 digit code. Details can be supplied upon request.

### Solvent Resistance

The protective epoxy lacquer and marking are resistant to all normal industrial cleaning fluids suitable for printed circuits.

## Performance Data

	Maximum Change								
	0201	0402	0603	0805	1206	1210	2010	2512	
Load: 1000 hrs at 70°C	Δ R%	10R-100K : 1 >100K : 2	4R7-100K : 1 >100K : 2	1R-100K : 1 >100K : 2	3% + 0.1R				
Shelf life: 12 months at room temp.	Δ R%	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Derate linearly to zero from 70°C					zero @ 125 °C				
Short term overload (6.25 x rated power)	Δ R%	2	2	2.5	2.5	2.5	2.5	5	
Max voltage	volts	50	100	100	200	400	400	400	
Climatic	Δ R%	3	3	3	3	3	3	3	
Climatic Catagory					55/125/56				
Long term damp heat	Δ R%				1				
Temperature rapid change	Δ R%	1	1	1	1	1	1	1	
Resistance to solder heat	Δ R%	2.5	2.5	2.5	2.5	2.5	2.5	2.5	
Vibration and bump	Δ R%	1	1	1	1	1	1	1	
Noise					see table 1				
Insulation resistance	ohms				> 1G				
Voltage proof	volts		100	500	500	500	500	500	

### Packaging

All chips are tape mounted and supplied on standard 8mm tape reel, as IEC publication 286-3.

180mm (7 inch) reel is standard

250mm (10 inch) reel carrying double the standard quantity can be supplied by agreement.

### Chip Resistor Labstock For Designers

WCR chip resistors are available in a special package of the most popular sizes containing 50 each of the E24 values.

Please contact the sales desk for full details of this excellent solution for designers and your prototype build requirements.

### Ordering Procedure

Example: WCR1206 at 10 kilohms and 1% tolerance on a reel of 5000 pieces -

Type \_\_\_\_\_ WCR 1206 - 10K F I

Size \_\_\_\_\_

Value (use IEC62 code) \_\_\_\_\_

Tolerance (use IEC62 code) \_\_\_\_\_

F	1%
---	----

Packing \_\_\_\_\_

I	Tape	0201	20000/reel	Standard
		0402	10000/reel	
		0603, 0805, 1206, 1210	5000/reel	
		2010, 2512	4000/reel	

Note: For zero ohm jumper chips use the dummy value & tolerance code **R005J**

### General Note

TT electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT electronics' own data and is considered accurate at time of going to print.

