


Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
Property of c BERG ELECTRONICS.
Droits de reproduction BERG ELECTRONICS by


All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Property of c BERG ELECTRONICS.
Copyright BERG ELECTRONICS by



Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de BERG ELECTRONICS.


All rights strictly reserved. Reproduction or issue to third parties in any form without the written authority from the proprietor.

Property of c BERG ELECTRONICS. Copyright BERG ELECTRONICS by



- NOTES:
1. EJECT FORCE : 3.5 Kg MAX.
 2. EJECT TRAVEL: 8.0mm
 3. MATERIAL
 - 3.1 HEADER ASS'Y :
PLASTIC : HOUSING ...LCP UL94V-O BLACK
PIN : COPPER ALLOY
 - 3.2 EJECT MECHANISM ASS'Y :
PLASTIC : GUIDE: POLYPHTHARAMID UL94V-O BLACK
: PUSH BUTTON: POLYPHTHARAMID UL94V-O BLACK
PLATE : STAINLESS
EMI CONTACT: PHOSPHOR BRONZE
 4. FINISH (PIN)
UNDER PLATING : 0.5µm MIN. Ni
CONTACT AREA : 0.1µm MIN. GOLD OVER 0.5µm MIN. Pd-Ni
SOLDER TAIL(TIN LEAD OPTION): 2.5µm MIN. Sn-Pb
SOLDER TAIL(LEAD FREE OPTION): 2.5µm MIN. PURE TIN
 5. DIM "X"




4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68



4 CARD INSERTION DIRECTION

mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		A FCI www.fclconnect.com	
rev.	ecn no.	dr	date	linear	±0.30	projection	title	product family	code
C				angles	± 2°		NARROW BODY FRONT EJECT TYPE 1/2/3 EJECTOR ASS'Y	PCMCIA	
E				dr	WENDY CHEN 07/13/01	unit		size	sheet
				enqr	MINERVA WANG 07/13/01	mm/inch		dwg no.	2 of
				chr	MINERVA WANG 07/13/01	scale			
				appd	JENN TSAO 07/13/01	1.5:1			
sheet	revision								
index	sheet								


52218-020HAH/020HAHLF



NOTES:

1. EJECT FORCE : 3.5 Kg MAX.
2. EJECT TRAVEL: 8.0mm
3. MATERIAL
3.1 HEADER ASS'Y :
PLASTIC : HOUSING ...LCP UL94V-O BLACK
PIN : COPPER ALLOY
3.2 EJECT MECHANISM ASS'Y :
PLASTIC : GUIDE: POLYPHTHARAMID UL94V-O BLACK
: PUSH BUTTON: POLYPHTHARAMID UL94V-O BLACK
PLATE : STAINLESS
EMI CONTACT: PHOSPHOR BRONZE
4. FINISH (PIN)
UNDER PLATING : 0.5µm MIN. Ni
CONTACT AREA : 0.1µm MIN. GOLD OVER 0.5µm MIN. Pd-Ni
SOLDER TAIL (TIN LEAD OPTION): 2.5µm MIN. Sn-Pb
SOLDER TAIL (LEAD FREE OPTION): 2.5µm MIN. PURE TIN
5. DIM "X"
- | | | |
|----------|---------|------------------|
| 4.25±0.1 | 3.5±0.1 | 5.0±0.1 |
| OTHERS | 36,67 | 1,17,34,35,51,68 |
6. IF LEAD FREE P/N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
7. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
8. IF LEAD FREE P/N. PACKAGING MEETS GS-14-920 SPECIFICATION

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,68



4 CARD INSERTION DIRECTION

mat'l code						tolerance unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
rev.	ecn	no.	dr	date		linear			projection	title PCMCIA R/A EJECTOR ASS'Y 5.0V, TYPE 1/2/3			
E							± 0.30						
							angles $\pm 2^\circ$						
						dr	WENDY CHEN	11/13/02	unit	product family PCMCIA			code
						enqr	SPENCER LAI	11/13/02	mm/inch	size dwg no.			sheet
						chr	SPENCER LAI	11/13/02	scale	A3 52218			3 of
						appd	JENN TSAO	11/13/02	1.5:1				
sheet	revision												
index	sheet												

