



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. V16312

Construction

				Diameters (In)	
1) Component 1		3 X 1 COND			
a) Conductor		12 (65/30) AWG TC		0.093	
b) Insulation		0.046" Wall, Nom. XLPE		0.189	
(1) Separator		Paper Tape, 10% Overlap, Min.			
(2) Color(s)					
Cond	Color	Cond	Color	Cond	Color
1	BLACK#1	2	BLACK#2	3	BLACK#3
2) Cable Assembly		3 Components Cabled			
a) Twists:		2.0 Twists/foot (min)			
b) Core Wrap		Clear Mylar Tape, 25% Overlap, Min.			
3) Shield:		A/P/A Tape, 25% Overlap, Min.			
a) Drain Wire		3 x 16 (26/30) AWG TC			
b) Braid		TC,85% Coverage, Min.			
4) Jacket		0.065" Wall, Nom.,PVC		0.581+/- 0.016	
a) Color(s)		BLACK			
b) Jacket Separator		Tissue Tape, 25% Overlap, Min.			
c) Print		ALPHA WIRE- EXXXXX SERIES V P/N V16312 VFD CABLE 3C12 SHIELDED 1000V FLEXIBLE MOTOR SUPPLY CABLE 600V TYPE TC-ER (UL) RHW-2 CDRS XLPE/PVC 90C DRY/ WET SUN RES DIR BUR 12 AWG --- LLXXXXXX CSA AWM I/II A/B 1000V 90C FT4 CE ROHS [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]			

Applicable Specifications

1) UL		
a) Component 1	RHW-2Wet/Dry	90°C / 600 V _{RMS}
	XHHW-2Wet/Dry	90°C / 600 V _{RMS}
b) Overall	TC	90°C / 600 V _{RMS}
	EXPOSED RUN	
	DIRECT BURIAL	
	SUN RES	
	1000V Flexible Motor Supply Cable	
2) CSA International	AWM I/II A/B	90°C / 1000 V _{RMS}
	FT4	
3) CE:	LVD 73/23/EEC Amendment 93/68/EEC	

Environmental

1) EU Directive 2002/95/EC(RoHS):	
	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-40 to 90°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	229 Lbs, Maximum
4) Sunlight Resistance	Yes
5) Direct Burial	Yes
6) Copper Weight	117 Lbs/1000Ft
7) Cable Weight	225 Lbs/1000Ft
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	1000 V _{RMS}
2) Capacitance	27 pf/ft @1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	49 pf/ft @1 kHz, Nominal
4) Inductance	0.2 µH/ft, Nominal
5) Conductor DCR	1.76 O/1000ft @20°C, Nominal
6) OA Shield DCR	0.71 O/1000ft @20°C, Nominal

Other

1) Packaging	
a) Bulk(Made-to-order)	

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:V16312

V16312 , RoHS-Compliant Commencing With8/19/2009Production

*This document certifies that the Alpha part numbers cited above are manufactured in accordancewith Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003,better known as the RoHS Directives, with regards to restrictions of the use of certain hazardousubstances used in the manufacture of electrical and electronic equipment. The reader is referredto these Directives for the specific definitions and extents of these Directives. **No Exemptions arerequired for RoHS Compliance on this item.***

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	0.1% by weight (1000 ppm)
Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire'sknowledge, information and belief at the date of its release. The information provided is designedonly as a general guide for the safe handling, storage, and any other operation of the productitself or the one that it will become part of. The intent of this document is not to be considered awarranty or quality specification. Regulatory information is for guidance purposes only. Productusers are responsible for determining the applicability of legislation and regulations based ontheir individual usage of the product.

Authorized Signatory for the Alpha Wire Company:

A handwritten signature in black ink, appearing to read 'Dave Watson'.

Dave Watson, Director of Engineering & QA

11/2/2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[V16312 BK199](#)