








LOC	DIST	REVISIONS				
AF	-	P	LTR	DESCRIPTION	DATE	DWN
			A	REVISED PER ECR-13-018775	11DEC2013	KH



RECOMMENDED CUT-OUT FOR
2.00 MAX THICK PANEL

PANEL MUST BE PUNCHED OUT SO THAT THE
HOUSING ENTERS THE PANEL IN THE
SAME DIRECTION AS THE PUNCH.

52.00	46.2	51.60	24	2-1969613-4
47.80	42.0	47.40	22	2-1969613-2
43.60	37.8	43.20	20	2-1969613-0
39.40	33.6	39.00	18	1-1969613-8
35.20	29.4	34.80	16	1-1969613-6
31.00	25.2	30.60	14	1-1969613-4
26.80	21.0	26.40	12	1-1969613-2
22.60	16.8	22.20	10	1-1969613-0
18.40	12.6	18.00	8	1969613-8
14.20	8.4	13.80	6	1969613-6
10.00	4.2	9.60	4	1969613-4
5.80	--	5.40	2	1969613-2
DIM C	DIM F	DIM L	NO. OF POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	18JAN13	 TE Connectivity	
		CHK KURT RANDOLPH	18JAN13		
		APVD KURT RANDOLPH	18JAN13		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±-		PANEL MOUNT PLUG HOUSING	
		1 PLC ±-		VAL-U-LOK	
		2 PLC ±0.25		-	
		3 PLC ±-			
		4 PLC ±-			
MATERIAL		ANGLES ±-		SIZE	
NYLON 6/6, V0		FINISH		CAGE CODE	
		WEIGHT		DRAWING NO	
		-		A200779	
		Customer Drawing		C=1969613	
				RESTRICTED TO	
				-	
				SCALE	
				3:1	
				SHEET	
				1 OF 1	
				REV	
				A	