



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECR-17-008225	08JUN2017	NK	VS

- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 8.38±0.08 [.003±.003] CENTERS.
- 2
- SLOT ACCEPTS 0.91–1.15mm [#19–#17] AWG COPPER MAGNET WIRE.
ONE WIRE MAX PER SLOT
- 3
- IDENTIFICATION NUMBER 24 FOR THE MAGNET WIRE SLOT SIZE
- 4
- 0.25[.010] MAX CARRIER CUT-OFF TABS
- 5
- PRE-PRODUCTION – F.A.S.R. REQUIRED.



SUPERCEDED BY 63720-2	082 PRE-MILLED BRASS	5	63720-2
	4M PRE-MILLED BRASS		63720-1
MATERIAL		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	9-27-93	TE Connectivity			
		CHK	9-27-93				
		APVD	9-27-93	NAME			
		A. HUNT III		TAB, 6.35 [.250] FASTON,™			
		PRODUCT SPEC		MAG-MATE™ Slim Line			
		108-1484		-			
		APPLICATION SPEC					
		114-2140					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		0.002032 [.000080] MIN TIN PLATE		A2	00779	C=63720	-
		CUSTOMER DRAWING		SCALE	10:1	SHEET	1 of 1
				REV G2			