


FEATURES

- EIA STANDARD SIZING 0201, 0402, 0603, 0805, 1206, 1210, 2010 AND 2512
- SUIT FOR HIGH RELIABILITY APPLICATIONS IN HARSH ENVIRONMENTS
- AEC-Q200 QUALIFIED OPTION AVAILABLE (SEE PART NUMBERING SYSTEM)
- ALL SIZES ARE AVAILABLE IN TAPE/REEL FOR AUTOMATIC MOUNTING
- SAC REFLOW SOLDERABLE (THREE TIMES AT 260°C FOR 10 SECONDS)

**RoHS
Compliant**
includes all homogeneous materials

*See Part Number System for Details



SPECIFICATIONS

Type	EIA Size	Power Rating at 70°C	Max. *1 Working Voltage	Max. *2 Overload Voltage	Resistance Tolerance Code	Temperature Coefficient (ppm/°C)	Resistance Range (Ω)*3	Resistance Values	Operating Temperature Range
NRC-AS02	0201	0.05W	25V	50V	±1%(F), ±5%(J)	±200ppm	1 ~ 10M	E-24 & 96	-55°C ~ +125°C
NRC-AS04	0402	0.063W	50V	100V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	-55°C ~ +155°C
NRC-AS06	0603	0.10W	75V	100V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	
NRC-AS10	0805	0.125W	150V	300V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	
NRC-AS12	1206	0.25W	200V	400V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	
NRC-AS25	1210	0.33W	200V	400V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	
NRC-AS50	2010	0.75W	200V	400V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	
NRC-AS100	2512	1.0W	250V	500V	±0.5%(D), ±1%(F), ±5%(J)	±100ppm ±200ppm	10 ~ 1M 1 ~ 9.76 1.02M ~ 10M	E-24 & 96	

Note *1 - Maximum allowable continuous Working Voltage for all resistors is the lower of the two values:

"Maximum Working Voltage" as specified above
or the result of the following formula


$$\sqrt{\text{Power rating (Watts)} \times \text{Resistance (Ohms)}}$$

Note *2 - "Maximum Overload Voltage" for all resistors is the lower of the two values:

"Maximum Overload Voltage" as specified above
or 2x the result of the following formula

$$\sqrt{\text{Power rating (Watts)} \times \text{Resistance (Ohms)}}$$

Power Derating Curve: For operation above 70°C, power rating must be derated according to the following chart:



ZERO OHM JUMPERS*


Part Number	EIA Size	Max. Current at 70°C	Max. Resistance	Operating Temperature Range
NRC-AS02ZOTRF	0201	1A	<50mΩ	-55°C ~ +125°C
NRC-AS04ZOTRF	0402	1A	<50mΩ	
NRC-AS06ZOTRF	0603	1A	<50mΩ	-55°C ~ +155°C
NRC-AS10ZOTRF	0805	2A	<50mΩ	
NRC-AS12ZOTRF	1206	2A	<50mΩ	
NRC-AS25ZOTRF	1210	2.5A	<50mΩ	
NRC-AS50ZOTRF	2010	3.5A	<50mΩ	
NRC-AS100ZOTRF	2512	4A	<50mΩ	

*Optional AEC Q-200 Qualified "TRQYF" is also available



DIMENSIONS (mm)

Type	EIA Size	L	W	H	T	t
NRC-AS02	0201	0.60 ± 0.03	0.30 ± 0.03	0.23 ± 0.03	0.15 ± 0.05	0.15 ± 0.05
NRC-AS04	0402	1.00 ± 0.05	0.50 ± 0.05	0.35 ± 0.05	0.20 ± 0.10	0.20 ± 0.10
NRC-AS06	0603	1.60 ± 0.10	0.80 ± 0.10	0.45 ± 0.10	0.30 ± 0.20	0.30 ± 0.20
NRC-AS10	0805	2.00 ± 0.10	1.25 ± 0.10	0.50 ± 0.10	0.35 ± 0.20	0.40 ± 0.20
NRC-AS12	1206	3.10 ± 0.10	1.55 ± 0.10	0.55 ± 0.10	0.50 ± 0.25	0.50 ± 0.20
NRC-AS25	1210	3.10 ± 0.10	2.60 ± 0.15	0.55 ± 0.10	0.50 ± 0.25	0.50 ± 0.20
NRC-AS50	2010	5.00 ± 0.10	2.50 ± 0.15	0.55 ± 0.10	0.60 ± 0.25	0.50 ± 0.20
NRC-AS100	2512	6.35 ± 0.10	3.10 ± 0.15	0.55 ± 0.10	0.60 ± 0.25	0.50 ± 0.20



PART NUMBER SYSTEM - STANDARD PARTS

PART NUMBER SYSTEM (E-24 VALUES)

NRC-AS 12 J 103 TR F

- Series
- Case Size
- Tolerance Code: J = ±5%
- Resistance Code: First 2 figures are significant, 3rd digit is the multiplier, "R" indicates a decimal point.
- Tape & Reel Packaging
- RoHS compliant

PART NUMBER SYSTEM (E-96 VALUES)

NRC-AS 12 F 1002 TR F

- Series
- Case Size
- Tolerance Code: F = ±1%
- Resistance Code: First 2 figures are significant, 3rd digit is the multiplier, "R" indicates a decimal point.
- Tape & Reel Packaging
- RoHS compliant

PART NUMBER SYSTEM - AUTOMOTIVE OPTION

PART NUMBER SYSTEM (E-24 VALUES)


NRC-AS 12 J 103 TR QY F

- Series
- Case Size
- Tolerance Code: J = ±5%
- Resistance Code: First 2 figures are significant, 3rd digit is the multiplier, "R" indicates a decimal point.
- Tape & Reel Packaging
- RoHS compliant

"QY" denotes optional AEC Q-200 qualified parts suitable for automotive equipment, sourced to special production and inspection at TS-16949 certified production site

PART NUMBER SYSTEM - AUTOMOTIVE OPTION


PART NUMBER SYSTEM (E-96 VALUES)



"QY" denotes optional AEC Q-200 qualified parts suitable for automotive equipment, sourced to special production and inspection at TS-16949 certified production site


Item	Specification			Test Method
	$\pm 0.5\%$ & $\pm 1\%$ tolerance	$\pm 5\%$ tolerance	Zero Ohm Jumper	
Temperature Coefficient of Resistance	As specified			-55°C ~ +125°C, +25°C reference point
Short Time Overload	$\Delta R \pm 1\% + 0.05\Omega$	$\Delta R \pm 2\% + 0.05\Omega$	50m Ω	RCWV x 2.5 or Max Overloading Voltage for 5 Seconds
Insulation Resistance	>10G Ω			Maximum Overload Voltage for 1 Minute
Load Life	$\Delta R \pm 2\% + 0.10\Omega$	$\Delta R \pm 3\% + 0.10\Omega$	100m Ω	Max. WV +70°C, 1.5 hours ON, 0.5 hours OFF Total time 1,000
Damp Heat (with load)	$\Delta R \pm 2\% + 0.10\Omega$	$\Delta R \pm 3\% + 0.10\Omega$	100m Ω	+40°C, 90% ~ 95% RH, Max. WV 1.5 hours ON, 0.5 hours OFF Total time 1,000
Resistance to Dry Heat	$\Delta R \pm 1\% + 0.05\Omega$	$\Delta R \pm 1.5\% + 0.05\Omega$	50m Ω	+125°C or +155°C for 1000 hours
Temperature Cycling	$\Delta R \pm 0.5\% + 0.05\Omega$	$\Delta R \pm 1\% + 0.05\Omega$	50m Ω	-55°C to +125°C or +155°C, 5 cycles
Bending Strength	$\Delta R \pm 1\% + 0.05\Omega$	$\Delta R \pm 2\% + 0.05\Omega$	50m Ω	Bending amplitude 3mm (2mm for 2010 & 2512) One bend for 5 seconds
Resistance to Soldering Heat	$\Delta R \pm 0.5\% + 0.05\Omega$	$\Delta R \pm 1\% + 0.05\Omega$	50m Ω	260°C $\pm 5^\circ\text{C}$ for 10 seconds
Sulfur Test	$\Delta R \pm 0.5\% + 0.05\Omega$	$\Delta R \pm 0.5\% + 0.05\Omega$	50m Ω	1,000ppm H ₂ S, +50°C $\pm 2^\circ\text{C}$, 91 ~ 93% RH for 1,000 hours (no power)
Leaching Test	Individual leaching are $\leq 5\%$ Total leaching area $\leq 10\%$			+260°C for 30 seconds

CONSTRUCTION




E-24	E-96										
Value	Value	Code		Value	Code		Value	Code		Value	Code
100	100	01		102	02		105	03		107	04
110	110	05		113	06		115	07		118	08
120	121	09		124	10		127	11		130	12
130	133	13		137	14		140	15		143	16
150	147	17		150	18		154	19		158	20
160	162	21		165	22		169	23		174	24
180	178	25		182	26		187	27		191	28
200	196	29		200	30		205	31		210	32
220	215	33		221	34		226	35		232	36
240	237	37		243	38		249	39		255	40
270	261	41		267	42		274	43		280	44
300	287	45		294	46		301	47		309	48
330	316	49		324	50		332	51		340	52
360	348	53		357	54		365	55		374	56
390	383	57		392	58		402	59		412	60
430	422	61		432	62		442	63		453	64
470	464	65		475	66		487	67		499	68
510	511	69		523	70		536	71		549	72
560	562	73		576	74		590	75		604	76
620	619	77		634	78		649	79		665	80
680	681	81		698	82		715	83		732	84
750	750	85		768	86		787	87		806	88
820	825	89		845	90		866	91		887	92
910	909	93		931	94		953	95		976	96

Type	EIA Case Size	A	B	W ± 0.20	E ± 0.10	F ± 0.05	P ₀ ± 0.10	P ₁ ± 0.05	P ₂ ± 0.05	φD ₀ +0.1/-0	T
NRC-AS02	0201	0.38±0.05	0.68±0.05	8.0	1.75	3.50	4.00	2.00	2.00	1.50	0.42±0.20
NRC-AS04	0402	0.65±0.10	1.15±0.10	8.0	1.75	3.50	4.00	2.00	2.00	1.50	0.45±0.10
NRC-AS06	0603	1.10±0.10	1.90±0.10	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.70±0.10
NRC-AS10	0805	1.60±0.10	2.40±0.20	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85±0.10
NRC-AS12	1206	1.90±0.10	3.50±0.20	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85±0.10
NRC-AS25	1210	2.90±0.10	3.50±0.20	8.0	1.75	3.50	4.00	4.00	2.00	1.50	0.85±0.10




Type	EIA Case Size	A	B	W ± 0.30	E ± 0.10	F ± 0.05	P ₀ ± 0.10	P ₁ ± 0.05	P ₂ ± 0.05	ΦD ₀ +0.1/-0	T max.
NRC-AS50	2010	2.8±0.10	5.5±0.10	12.0	1.75	5.50	4.00	4.00	2.00	1.50	1.2
NRC-AS100	2512	3.5±0.10	6.7±0.10	12.0	1.75	5.50	4.00	4.00	2.00	1.50	1.2




REEL DIMENSIONS (mm)

Type	EIA Case Size	Reel Quantity	Tape Width	Reel Diameter	ϕB	ϕC	W	T
NRC-AS02	0201	15,000	8mm	178.5 ± 1.5	60.0 +1/-0	13.0 ±0.2	9.0 ±0.5	12.5 ±0.5
NRC-AS04	0402	10,000			100 ±0.5		9.5 ±0.5	13.5 ±0.5
NRC-AS06	0603	5,000						
NRC-AS10	0805	5,000						
NRC-AS12	1206	5,000						
NRC-AS25	1210	5,000						
NRC-AS50	2010	4,000						
NRC-AS100	2512	4,000	12mm		60.0 +1/-0	13.0 ±0.5	13.0 ±0.5	15.5 ±0.5



LAND PATTERN DIMENSIONS (mm)

Type	EIA Case Size	A	B	C
NRC-AS02	0201	0.30	0.25	0.30
NRC-AS04	0402	0.50	0.45	0.60
NRC-AS06	0603	0.90	0.60	0.90
NRC-AS10	0805	1.20	0.70	1.30
NRC-AS12	1206	2.00	0.90	1.60
NRC-AS25	1210	2.00	0.90	2.80
NRC-AS50	2010	3.80	0.90	2.80
NRC-AS100	2512	3.80	1.60	3.50



REFLOW SOLDERING TEMPERATURE PROFILE

