

74153, LS153, S153
Multiplexers

Dual 4-Line To 1-Line Multiplexer
Product Specification

Logic Products

FEATURES

- Non-inverting outputs
- Separate enable for each section
- Common select inputs
- See '253 for 3-state version

DESCRIPTION

The '153 is a dual 4-input multiplexer that can select 2 bits of data from up to eight (8) sources under control of the common Select inputs (S_0, S_1). The two 4-input multiplexer circuits have individual active LOW Enables ($\bar{E}_a, \bar{E}_b$) which can be used to strobe the outputs independently. Outputs (Y_a, Y_b) are forced LOW when the corresponding Enables ($\bar{E}_a, \bar{E}_b$) are HIGH.

$$Y_a = \bar{E}_a \cdot (I_{0a} \cdot \bar{S}_1 \cdot \bar{S}_0 + I_{1a} \cdot \bar{S}_1 \cdot S_0 + I_{2a} \cdot S_1 \cdot \bar{S}_0 + I_{3a} \cdot S_1 \cdot S_0)$$

$$Y_b = \bar{E}_b \cdot (I_{0b} \cdot \bar{S}_1 \cdot \bar{S}_0 + I_{1b} \cdot \bar{S}_1 \cdot S_0 + I_{2b} \cdot S_1 \cdot \bar{S}_0 + I_{3b} \cdot S_1 \cdot S_0)$$

TYPE	TYPICAL PROPAGATION DELAY	TYPICAL SUPPLY CURRENT (TOTAL)
74153	18ns	36mA
74LS153	18ns	6.2mA
74S153	9ns	45mA

ORDERING CODE

PACKAGES	COMMERCIAL RANGE $V_{CC} = 5V \pm 5\%$; $T_A = 0^\circ C$ to $+70^\circ C$
Plastic DIP	N74153N, N74LS153N, N74S153N
Plastic SO	N74LS153D, N74S153D

NOTE:

For information regarding devices processed to Military Specifications, see the Signetics Military Products Data Manual.


INPUT AND OUTPUT LOADING AND FAN-OUT TABLE

PINS	DESCRIPTION	74	74S	74LS
All	Inputs	1uI	1Sul	1LSul
All	Outputs	10uI	10Sul	10LSul


NOTE:

Where a 74 unit load (uI) is understood to be $40\mu A$ I_{IH} and $-1.6mA$ I_{IL} , a 74S unit load (Sul) is $50\mu A$ I_{IH} and $-2.0mA$ I_{IL} , and 74LS unit load (LSul) is $20\mu A$ I_{IH} and $-0.4mA$ I_{IL} .


PIN CONFIGURATION



LOGIC SYMBOL



LOGIC SYMBOL (IEEE/IEC)




Multiplexers

74153, LS153, S153

The '153 can be used to move data to a common output bus from a group of registers. The state of the Select inputs would determine the particular register from which the data came. An alternative application is as a function generator. The device can generate two functions or three variables. This is useful for implementing highly irregular random logic.

LOGIC DIAGRAM



FUNCTION TABLE

SELECT INPUTS		INPUTS (a or b)					OUTPUT
S ₀	S ₁	$\bar{E}$	I ₀	I ₁	I ₂	I ₃	Y
X	X	H	X	X	X	X	L
L	L	L	X	X	X	X	L
L	L	L	H	X	X	X	H
H	L	L	X	L	X	X	L
H	L	L	X	H	X	X	H
L	H	L	X	X	L	X	L
L	H	L	X	X	H	X	H
H	H	L	X	X	X	L	L
H	H	L	X	X	X	H	H

H = HIGH voltage level
L = LOW voltage level
X = Don't care

ABSOLUTE MAXIMUM RATINGS (Over operating free-air temperature range unless otherwise noted.)

PARAMETER	74	74LS	74S	UNIT
V _{CC} Supply voltage	7.0	7.0	7.0	V
V _{IN} Input voltage	-0.5 to +5.5	-0.5 to +7.0	-0.5 to +5.5	V
I _{IN} Input current	-30 to +5	-30 to +1	-30 to +5	mA
V _{OUT} Voltage applied to output in HIGH output state	-0.5 to +V _{CC}	-0.5 to +V _{CC}	-0.5 to +V _{CC}	V
T _A Operating free-air temperature range	0 to 70			°C

RECOMMENDED OPERATING CONDITIONS

PARAMETER	74			74LS			74S			UNIT
	Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	
V _{CC} Supply voltage	4.75	5.0	5.25	4.75	5.0	5.25	4.75	5.0	5.25	V
V _{IH} HIGH-level input voltage	2.0			2.0			2.0			V
V _{IL} LOW-level input voltage			+0.8			+0.8			+0.8	V
I _{IK} Input clamp current			-12			-18			-18	mA
I _{OH} HIGH-level output current			-800			-400			-1000	μA
I _{OL} LOW-level output current			16			8			20	mA
T _A Operating free-air temperature	0		70	0		70	0		70	°C

Multiplexers

74153, LS153, S153

DC ELECTRICAL CHARACTERISTICS (Over recommended operating free-air temperature range unless otherwise noted.)

PARAMETER	TEST CONDITIONS ¹	74153			74LS153			74S153			UNIT
		Min	Typ ²	Max	Min	Typ ²	Max	Min	Typ ²	Max	
V _{OH} HIGH-level output voltage	V _{CC} = MIN, V _{IH} = MIN, V _{IL} = MAX, I _{OH} = MAX	2.4	3.4		2.7	3.4		2.7	3.4		V
V _{OL} LOW-level output voltage	V _{CC} = MIN, V _{IH} = MIN, V _{IL} = MAX	I _{OL} = MAX	0.2	0.4		0.35	0.5			0.5	V
		I _{OL} = 4mA (74LS)				0.25	0.4				V
V _{IK} Input clamp voltage	V _{CC} = MIN, I _I = I _{IK}			-1.5			-1.5			-1.2	V
I _I Input current at maximum input voltage	V _{CC} = MAX	V _I = 5.5V		1.0						1.0	mA
		V _I = 7.0V					0.1				mA
I _{IH} HIGH-level input current	V _{CC} = MAX	V _I = 2.4V		40							μA
		V _I = 2.7V					20			50	μA
I _{IL} LOW-level input current	V _{CC} = MAX	V _I = 0.4V		-1.6			-0.4				mA
		V _I = 0.5V								-2.0	mA
I _{OS} Short-circuit output current ³	V _{CC} = MAX	-18		-57	-20		-100	-40		-100	mA
I _{CC} Supply current ⁴ (total)	V _{CC} = MAX		36	60		6.2	10		45	70	mA

NOTES:

- For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions for the applicable type.
- All typical values are at V_{CC} = 5V, T_A = 25°C.
- I_{OS} is tested with V_{OUT} = +0.5V and V_{CC} = V_{CC} MAX + 0.5V. Not more than one output should be shorted at a time and duration of the short circuit should not exceed one second.
- Measure I_{CC} with all inputs grounded and all outputs open.


AC ELECTRICAL CHARACTERISTICS T_A = 25°C, V_{CC} = 5.0V

PARAMETER		TEST CONDITIONS	74		74LS		74S		UNIT
			$C_L = 30\text{pF}, R_L = 400\Omega$		$C_L = 15\text{pF}, R_L = 2\text{k}\Omega$		$C_L = 15\text{pF}, R_L = 280\Omega$		
			Min	Max	Min	Max	Min	Max	
t_{PLH}	Propagation delay	Waveform 2		34		29		18	ns
t_{PHL}	Select to output			34		38		18	
t_{PLH}	Propagation delay	Waveform 1		30		24		15	ns
t_{PHL}	Enable to output			23		32		13.5	
t_{PLH}	Propagation delay	Waveform 2		18		15		9.0	ns
t_{PHL}	Data to output			23		26		9.0	

Multiplexers

74153, LS153, S153

AC WAVEFORMS



TEST CIRCUITS AND WAVEFORMS

