

# Edison base plug fuses – time-delay, 125 volts, 15-30 amps



## Catalog symbol:

- TL - (amps)
- BP/TL - (amps)
- TL - (amps)RK4

## Description:

Bussmann® series time-delay, loaded link Edison base plug fuse.

## Specifications:

### Ratings

- Volts — 125 Vac or less
- Amps — 15 to 30 A
- Interrupting rating — 10 kA RMS Sym

### Agency Information

- UL® Listed, Std. 248-11, Guide JEFV, File E12112
- CE

### Catalog numbers (amps)

TL - 15	TL - 20	TL - 25	TL - 30
---------	---------	---------	---------

## Recommended fuse holders

Catalog numbers	Type box	Catalog numbers	Type box
SOU	2 1/4" handy	SOY	4" square
SRU		SRY	
SSU		SSY	
SOW	2 3/4" handy	SSY-RL	
SRW		STY	
SSW		SCY	
SOX	4" octagon	SOY-B	Single gang
SRX		SSN	


## Package quantity and weight

Amp ratings	Quantity		Weight	
	Per box	Per card	Per box	Per 5 cards
15 to 30 A	4	3	0.24	1.04

## Features:

- Medium duty time-delay plug fuse
- Will withstand typical motor starting surges
- Use in residential or light-duty circuits that contain electric motors
- Edison base size
- These fuses thread into fuse receptacles or box cover units for supplemental protection

Time-current curve – average melt



The only controlled copy of this Data Sheet is the electronic read-only version located on the Eaton Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2016 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 1035 – SB98107  
May 2016

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series  
product information,  
call 1-855-287-7626 or visit:  
**Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.

