


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MINIMUM BUNDLE DIAMETER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = "L" $\pm .3$ [7]
MLT2.7WS-LP316	2.0" [51]	2.7" [69]	50	10.2" [259]
MLT4WS-LP316	2.0" [51]	4.0" [102]	50	14.3" [362]
MLT6WS-LP316	2.0" [51]	6.0" [152]	50	20.5" [521]
MLT8WS-LP316	2.0" [51]	8.0" [203]	50	26.8" [679]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS (890 NEWTONS) WHEN TESTED ON A 3" MANDREL
PART NO. MLT2.7WS-LP316 TESTED ON A 1 1/2" MANDREL
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
5. MATERIAL: 316 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A
SCALE: 8x

10A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
09A	2/12	MIM	RGRO	----	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		WAVE-TY STANDARD SERIES 316 STAINLESS STEEL	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		N41125BS/10	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x $\pm .1$ [2.54] .xxx $\pm .005$ [.127]		316 STAINLESS STEEL	
.xx $\pm .01$ [.25] ANGLES $\pm 5^\circ$		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		N41125BS_DC	
DRAWN BY	DATE	CHK	SCALE
JAMB	2/12	DPN	2:1
SHT 1 OF 1		A	