

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		BI	REVISED PER ECO-10-012581	17JUN2010	HMR	CR

D

D

C


C

B

B

A




A



1. MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-VO, COLOR GREEN
CLAMP: BRASS, NICKEL PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 3.2mm PCB THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK, WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE: 10-24 AWG, RATED 600V, 30A.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORY INC. FILE No. E60677.
6. IMQ CERTIFICATE WITH SURVIELANCE IN CONFORMITY WITH EN 60998.


7. NOT CUMULATIVE TOLERANCE.

8. PRELIMINARY



796741-3 AS SHOWN

8	76.16	8	796741-8
8	57.12	6	796741-6
	28.56	3	796741-3
	19.04	2	796741-2
L		No. POS.	PART NUMBER



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN E. ZANOLINI 06MAR2001	Tyco Electronics Harrisburg, PA 17105-3608			
				CHK E. ZANOLINI 06MAR2001				
				APVD D. BIEVENOUR 06MAR2001	NAME TERMINAL BLOCK, PCB MOUNT 35 deg. WIRE ENTRY, HIGH CURRENT W/INTERLOCK, 9.52mm PITCH			
DIMENSIONS: mm				PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-796741	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.15 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH				APPLICATION SPEC -	WEIGHT -	CUSTOMER DRAWING		
MATERIAL					SCALE 3	SHEET 1	OF 1	REV BI