




1546842-6 Product Details

[Share](#) | [Print](#) | [Email](#)


1546842-6

TE Internal Number: 1546842-6

 **Active**

 [View 3D PDF](#)

Barrier Strips

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Barrier Strip
- Barrier Style = Single Row, Dual Barrier
- Block Style = Open Bottom with Standoffs
- 9.53 mm Centerline
- Vertical Mount Angle

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [JC6-Q208-XX ASSEMBLY](#) (PDF, English)

Catalog Pages/Data Sheets:

- [1-1773458-2 BARRIER STRIPS QUICK REFERENCE GUIDE](#) (PDF, English)
- [BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version J)
- [3D Model](#) (IGES, Version J)
- [3D Model](#) (STEP, Version J)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical

Electrical Characteristics:

- [Top Hardware](#) = Wire Clamp Combo Head

Body Features:

- [Barrier Style](#) = Single Row, Dual Barrier
- Block Style = Open Bottom with Standoffs
- [Centerline \(in \[mm\]\)](#) = 0.375 [9.53]
- Number of Positions = 6
- [Terminal Style](#) = Quick Connects 6.35 [.250]

Contact Features:

- Mounting Options = End Mounting Ears

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics
- Comment = Other options available upon request, consult our Product Information Center.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates



