



CAP OPTIONS	TOGGLE SWITCHES	TACTILE SWITCHES	SNAP ACTION SWITCHES	SLIDE SWITCHES	ROTARY SWITCHES	ROCKER SWITCHES	PUSHBUTTON SWITCHES	NAVIGATION SWITCHES	KEYLOCK SWITCHES	DIP SWITCHES	DETECTOR SWITCHES	ANTI-VANDAL SWITCHES
----------------	--------------------	---------------------	-------------------------	-------------------	--------------------	--------------------	------------------------	------------------------	---------------------	-----------------	----------------------	-------------------------



RoHS

Electrical Rating: 2A, 48VDC
Electrical Life: 50,000 Cycles
Contact Resistance: 50mΩ Max.
Insulation Resistance: 1000 MΩ Min. @ 500VDC
Dielectric Strength: 2,000VAC
Operating/Storage Temperature: -20°C to 55°C
Travel: 2.20mm
Moisture Protection: IP65
Contact Arrangement: SPDT
Actuation Force: 4 N
Panel Thickness: 1-8mm for Y Function
 1-12mm for T function
Mounting Nut Torque: 5-14Nm

- 22mm diameter panel cutout
- RGB LED option
- Dot, ring or power symbol illumination available
- Multiple function options
- IP65 rated
- SPDT

Series	Actuator Options	Terminal Options	Function Options	Rating Options	Body Finish Options	Actuator Finish Options	Lens Style Options	LED-Color Options	Illumination Voltage Options	Graphic (Optional)
PV7	F - Flat	2 - Solder	T - 1 Pole Off - On 1 Pole On - Off Y - 1 Pole Off - (On) 1 Pole On - (Off)	0 - 2A, 48VDC	N - Nickel Plated S - Stainless Steel 1 - Black Anodized	N - Nickel Plated S - Stainless Steel 1 - Black Anodized	NONE - Non- Illuminated 2 - Dot Illumination 3 - Ring Illumination	NONE- Non- Illuminated 0 - White 1 - Red 2 - Orange 3 - Green 4 - Blue 5 - Yellow F - Red/Orange G - Red/Green H - Red/Blue J - Red/Yellow K - Orange/Green L - Orange/Blue M - Orange/Yellow R - RGB LED	NONE - Non- Illuminated 1 - Base Voltage 3 - 6V 4 - 12V 5 - 24V 6 - 125V 7 - 250V	M01 - Power symbol (sm) laser etched M03 - Power symbol illumi- nated M16 - Power symbol (lg) laser etched

Specifications subject to change without notice







E♦SWITCH®

800.867.2717

2

PV7 SERIES ANTI-VANDAL SWITCH

NON ILLUMINATED T FUNCTION



E-SWITCH®

www.e-switch.com



800.867.2717

3

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS


PV7 SERIES ANTI-VANDAL SWITCH

NON ILLUMINATED Y FUNCTION



**NON ILL.
SCHEMATIC**


$\varnothing 22.00^{+.20}_{-.00}$
[.866^{+.008}_{-.000} in]



**RECOMMENDED
PANEL CUTOUT**
MAX. PANEL THICKNESS
8mm for Y FUNCTION
12mm FOR T FUNCTION

PANEL CUTOUT

$\varnothing 22.00^{+.20}_{-.00}$
[.866^{+.008}_{-.000} in]



**RECOMMENDED
"D" PANEL CUTOUT**
MAX. PANEL THICKNESS 12mm
"D" HOUSING TO BE USED WITH
POWER SYMBOL OR CUSTOM GRAPHICS

POWER SYMBOL PANEL CUTOUT



E-SWITCH®





www.e-switch.com

800.867.2717

4





PV7 SERIES ANTI-VANDAL SWITCH

STANDARD LED T FUNCTION



PV7 SERIES ANTI-VANDAL SWITCH

STANDARD LED Y FUNCTION



E-SWITCH®





www.e-switch.com

800.867.2717

6

PV7 SERIES ANTI-VANDAL SWITCH

RGB LED T FUNCTION



E-SWITCH®

www.e-switch.com





800.867.2717

7

ANTI-VANDAL
SWITCHES
DETECTOR
SWITCHES
DIP
SWITCHES
KEYLOCK
SWITCHES
NAVIGATION
SWITCHES
PUSHBUTTON
SWITCHES
ROCKER
SWITCHES
ROTARY
SWITCHES
SLIDE
SWITCHES
SNAP ACTION
SWITCHES
TACTILE
SWITCHES
TOGGLE
SWITCHES
CAP
OPTIONS


PV7 SERIES ANTI-VANDAL SWITCH

RGB LED Y FUNCTION




PV7 SERIES ANTI-VANDAL SWITCH


ACTUATOR OPTIONS



FLAT NON-ILLUMINATED





FLAT DOT ILLUMINATED





FLAT RING ILLUMINATED

GRAPHIC OPTIONS



M01 GRAPHIC



M03 GRAPHIC



M16 GRAPHIC



ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES

TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS



E-SWITCH®

www.e-switch.com

800.867.2717

9

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PV7F2Y0SS-3Q1/ACC-N01-8](#) [PV7F2T0SS-324](#) [PV7F2Y0SS-231](#) [PV7F2Y0SS-315](#) [PV7F2Y0SS-324](#) [PV7F2Y0SS-325](#) [PV7F2Y0SS-335](#) [PV7F2Y0SS-344](#) [PV7F2Y0SS-354](#) [PV7F2Y0SS-355](#) [PV7F2Y0SS-311](#) [PV7F2T0SS-311](#) [PV7F2T0SS-341](#) [PV7F2T0SS-331](#) [PV7F2Y0SS-331](#) [PV7F2Y0SS-341](#) [PV7F2T0SS-344](#) [PV7F2Y0SS](#) [PV7F2Y0SS-241](#) [PV7F2Y0SS-351](#) [PV7F2Y0SS-3L4](#) [PV7F2Y0SS-3Q1](#) [PV7F2T0SS-231](#) [PV7F2T0SS-3G3](#) [PV7F2Y0SS-314](#) [PV7F2T0SS-316](#) [PV7F2T0SS](#) [PV7F2T0SS-325](#) [PV7F2T0SS-355](#) [PV7F2T0SS-314](#) [PV7F2T0SS-335](#) [PV7F2T0SS-345](#) [PV7F2T0SS-315](#) [PV7F2Y0SS-321](#) [PV7F2T0MM344M03](#) [PV7F2T011-311](#) [PV7F2Y011-311](#) [PV7F2T0SS-313](#) [PV7F2Y0SS-313](#) [PV7F2T0SS-301](#) [PV7F2Y0SS-343](#) [PV7F2Y0SS-3G4](#) [PV7F2Y011-3R3](#) [PV7F2Y0SS-3K1-M03](#) [PV7F2Y0SS-341-M03](#) [PV7F2Y0SS-333](#) [PV7F2Y0SS-344-M09](#) [PV7F2Y0SS-344-M10](#) [PV7F2Y011-345](#) [PV7F2Y0SS-3G1](#) [PV7F2Y0SS-3H1](#) [PV7F2T0SS-331-M03](#) [PV7F2T0SS-331-M01](#) [PV7F2T0SS-341-M18](#) [PV7F2T0NN-314](#) [PV7F2T0SS-333](#) [PV7F2Y0NN-3N1](#) [PV7F2T0SS-331-M18](#) [PV7F2T0SS-301-M16](#) [PV7F2T0SS-3G5](#) [PV7F2Y0SS-341-M01](#)