




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		L	REVISED PER ECR-10-006099	07JUL10	HMR	PD



SECTION A-A SECTION B-B

1. CONTINUOUS STRIP ON REELS

F or O	.210	.220	F	.155	.087	14
					.081	16
TYPE	WIDTH	STRIP LENGTH	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP		±.015	WIRE BARREL CRIMP			

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± -
MATERIAL #2 HARD BRASS	FINISH SEE TABLE

	TIN	.120—.180 DIA		16—14 AWG	42752—2	
	—				42752—1	
	FINISH	INSULATION RANGE	WIRE SIZE	PART NO		
DWN P FORTNEY	4/16/90	 Tyco Electronics Corporation Harrisburg, PA 17105—3608				
CHK JR RUTH	4/16/90					
APVD G YETTER	4/16/90	NAME RING				
PRODUCT SPEC —						
APPLICATION SPEC —						
WEIGHT —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		A3	00779	C—42752	—	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV L