




Features

- 3/4 " Rectangular / Multiturn
Cermet / Industrial / Sealed
- Low PC board profile - only 1/4 " high
- Panel mount option available
- Transparent housing available, can be set visually without hook-up and instrumentation ("P" style only)

- RoHS compliant * version available

3006 - Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range
.....10 to 5 megohms
(see standard resistance table)

Resistance Tolerance±10 % std.
(tighter tolerance available)

Absolute Minimum Resistance
.....1.0 % or 2 ohms max.
(whichever is greater)

Contact Resistance Variation
.....1.0 % or 1 ohm max.
(whichever is greater)

Adjustability
Voltage±0.01 %
Resistance±0.05 %

Resolution.....Infinite

Insulation Resistance500 vdc.
1,000 megohms min.

Dielectric Strength
Sea Level1,000 vac
80,000 Feet250 vac

Adjustment Angle15 turns nom.

Environmental Characteristics

Power Rating (400 volts max.)
70 °C0.75 watt
125 °C0 watt

Temperature Range-55 °C to +125 °C

Temperature Coefficient±100 ppm/°C

Seal Test.....85 °C Fluorinert[†]

Humidity.....MIL-STD-202 Method 103
96 hours
(3 % ΔTR, 20 Megohms IR)

Vibration.....20 G (2 % ΔTR; 2 % ΔVR)

Shock.....50 G (2 % ΔTR; 2 % ΔVR)

Load Life ...1,000 hours 0.75 watt 70 °C
(4 % ΔTR)

Rotational Life200 cycles
(3 % ΔTR; 1 % or 1 ohm,
whichever is greater, CRV)

Physical Characteristics

Torque5.0 oz-in. max.

Mechanical StopsWiper idles

Terminals.....Solderable pins

Weight0.04 oz.

MarkingManufacturer's
trademark, resistance code,
terminal numbers, date code,
manufacturer's model number
and style


Wiper50 % (Actual TR) ±10 %

Flammability.....U.L. 94V-0


Standard Packaging.....25 pcs. per tube

Adjustment ToolH-90


Common Dimensions




3006P



3006W



3006Y



TOLERANCES: ± 0.25 (.010) EXCEPT WHERE NOTED

DIMENSIONS ARE: $\frac{\text{MM}}{(\text{INCHES})}$

How To Order

3006 P - 1 - 103 Z LF

Model _____

Style _____

Standard or Modified
Product Indicator _____
-1 = Standard Product
-7 = Transparent Housing

Resistance Code _____

Optional Suffix Letter _____
Z = Panel Mount
(Factory Installed)

Terminations _____
LF = 100 % Tin-plated (RoHS compliant)
Blank = 90 % Tin / 10 % Lead-plated
(Standard)

Consult factory for other available options.

Standard Resistance Table

Resistance (Ohms)	Resistance Code
10	100
20	200
50	500
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
25,000	253
50,000	503
100,000	104
200,000	204
250,000	254
500,000	504
1,000,000	105
2,000,000	205

Popular distribution values listed in boldface.
Special resistances available.

