


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—	O	RELEASED(FJ00-1962-00)	20DEC00	H.T I.E

-1 ; AS SHOWN






NOTES


- △ MATERIAL ; HOUSING:HIGH TEMPERATURE THERMO PLASTIC UL94V-0.
CONTACT:COPPER ARROY.
2. FINISH ; CONTACT AREA : GOLD PLATE OVER Ni PLATE.
SOLDERING AREA : GOLD PLATE OVER Ni PLATE.
△ POLYIMIDE FILM (ADHESIVE TAPE) ; THK 0.08.

注記

- △ 材料 ; ハウジング : 耐熱性熱可塑性樹脂 UL94V-0
コンタクト : 銅合金
2. めっき仕様 ; 接触部 : ニッケル下地
金めっき
半田付部 : ニッケル下地
金めっき
△ ポリイミド フィルム (粘着テープ) ; 厚さ 0.08

SECT B-B
(SCALE 4-1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH

GENERAL TORELANCE

10± : ±0.2
30± >10 : ±0.25
>30 : ±0.3
ANGLE : ±3°

DWN H.TAGUCHI 14DEC00

CHK K.ASAKAWA 20DEC00

APVD I.ENOMOTO 20DEC00

PRODUCT SPEC

108-5773

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMPTyco Electronics Corporation
Kawasaki, Japan

NAME

CARD EDGE 35 DUAL POS. SMT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1473151

SCALE 1-1

SHEET 1 OF 2

REV 0

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P


LTR

DESCRIPTION


DATE

DWN

APVD



RECOMMENDED P.C. BOARD PATTERN LAYOUT
(CONNECTOR MOUNTING SIDE)




RECOMMENDED MATING BOARD EDGE CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL



FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP

Tyco Electronics Corporation
Kawasaki, Japan

NAME

CARD EDGE 35 DUAL POS. SMT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1473151

SCALE 1-1

SHEET 2 OF 2

REV 0

GENERAL TOLERANCE

10 ± 0.2
30 ± 0.25
>30 ± 0.3
ANGLE ± 3°