



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		20A 12VDC 10A 24VDC		Mounting Hole		Circuit Diagram			
Configured For		12VDC 14V							
Contact Resistance		50m ohm Max.							
Insulation Resistance		DC 500V 100M ohm Min.							
Dielectric Strength		AC 1500V 1 minute							
Operation Temperature		-20°~85°							
Switch Function		4P SPDT ON-OFF-ON Lamp Dependent		Thickness(mm)		X(mm)		Y(mm)	
Lamp Type		LED 12VDC 14V w/resistor		0.75~1.25		21.2±0.1		36.6 ^{+0.2} ₋₀	
				1.25~2.0				36.8 ^{+0.2} ₋₀	
				2.0~3.0				37.0 ^{+0.2} ₋₀	

*** MATERIAL:**






Frame: Nylon 66, Black

Actuator: Nylon 66 with 33%GF, Black

Lens 1: Red, Super bright LED

Lens 2: Green, Super bright LED

Water proof and dust proof to fit IP-56



DATE CODE

RoHS Compliant

2	Added dependent to function & Lamp Type. 12/13/2011.
1	Removed AC Rating marks and added DC Rating marks.8/23/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/19/10

Rev. 2

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB260D501BBRG1**