


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Voltage: 3VDC
2. Operating Voltage: 2 ~ 5VDC
3. Max. Rated Current: 25mA at 3VDC
4. Resonant Frequency: 3.4±0.5KHz
5. Min. Sound Pressure Level: 80dB at 3VDC/30cm
6. Tone Nature: Continuous
7. Case Material: ABS
8. Operating Temperature: -20~+60°C
9. Store Temperature: -30~+70°C
10. Weight: 8g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:
Jason Nash
DATE:
09-03-09
CHECKED BY:
Jason Nash
DATE:
09-03-09
APPROVED BY:
Jason Nash
DATE:
09-03-09

DRAWING TITLE:
Piezo Buzzer & Transducer
SIZE DWG. NO. ELECTRONIC FILE REV
A MCKPI-G2310L-3964 25R0629.dwg A
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1