




P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	EC 0G3B 0215 05	22SEP05	BSV	RCJ



SECTION A-A
SCALE 10:1

1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: 3-6mm² [12-10 AWG].
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
5. THIS CONTACT HAS NO INSULATION BARREL.

GOLD	0.30 [.012]	PH BRZ	1-770247-0
GOLD	0.30 [.012]	PH BRZ	770247-4
PRE-TIN	0.30 [.012]	PH BRZ	770247-3
FINISH	MATERIAL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	02APR04	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK C.JONES	02APR04				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME C.JONES			
		0 PLC ± -		PRODUCT SPEC			
		1 PLC ± -		APPLICATION SPEC			
MATERIAL		FINISH		WEIGHT			
-		-		CUSTOMER DRAWING			
				SIZE A2	CAGE CODE 00779	DRAWING NO C=770247	RESTRICTED TO
				SCALE 4:1	SHEET 1 of 1	REV E	

METRIC