

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

To all our customers

Regarding the change of names mentioned in the document, such as Mitsubishi Electric and Mitsubishi XX, to Renesas Technology Corp.

The semiconductor operations of Hitachi and Mitsubishi Electric were transferred to Renesas Technology Corporation on April 1st 2003. These operations include microcomputer, logic, analog and discrete devices, and memory chips other than DRAMs (flash memory, SRAMs etc.)

Accordingly, although Mitsubishi Electric, Mitsubishi Electric Corporation, Mitsubishi Semiconductors, and other Mitsubishi brand names are mentioned in the document, these names have in fact all been changed to Renesas Technology Corp. Thank you for your understanding. Except for our corporate trademark, logo and corporate statement, no changes whatsoever have been made to the contents of the document, and these changes do not constitute any alteration to the contents of the document itself.

Note : Mitsubishi Electric will continue the business operations of high frequency & optical devices and power devices.

Renesas Technology Corp.
Customer Support Dept.
April 1, 2003

MITSUBISHI MICROCOMPUTERS

M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

DESCRIPTION

The M35014-XXXSP and M35015-XXXSP are TV screen display control IC which can be used to display information such as program schedules, the date and messages on the TV screen.

The differences among M35014-XXXSP and M35015-XXXSP are noted below.

The descriptions that follow describe the M35014-XXXSP unless otherwise noted.


Type name	M35014-XXXSP	M35015-XXXSP
Characters available	64	512
Data input	8 bits serial input	16 bits serial input
Exclusion function	Exclusion 1 function	Exclusion 1 and 2 function
CONT7F function	Normal/7F ₁₆ writing mode	Normal/FF ₁₆ writing mode

For M35014-001SP and M35015-001SP that are standard ROM version of M35014-XXXSP and M35015-XXXSP respectively, the I/O polarity of pin and the character pattern are also mentioned.

FEATURES

- Screen composition 24 columns × 10 lines
- Number of characters displayed 240 (Max.)
- Character composition 12 × 18 dot matrix
- Characters available
 - M35014-XXXSP 64 characters
 - M35015-XXXSP 512 characters
- Character sizes available ... 4 (horizontal) × 4 (vertical)
- Display locations available
 - Horizontal direction 62 locations
 - Vertical direction 64 locations
- Blinking Character units
 - Cycle : approximately 1 second, or approximately 0.5 seconds
 - Duty : 25%, 50%, or 75%
- Data input
 - M35014-XXXSP By the 8-bit serial input function
 - M35015-XXXSP By the 16-bit serial input function
- Coloring
 - Background coloring (composite video signal)
- Blanking
 - Total blanking (14 × 18 dots)
 - Border size blanking
 - Character size blanking
- Synchronization signal
 - Composite synchronization signal generation (PAL, NTSC, M-PAL)
- Synchronized separation circuit Built-in
- 4 output ports (2 digital lines)
- Oscillation stop function
 - Be possible to stop the oscillation for display and for synchronized signal generation

PIN CONFIGURATION (TOP VIEW)



Outline 20P4B

Note : The pins remarked "*" are selectable the input or output polarity when the character ROM masked.

- Exclusion function
 - M35014-XXXSP 1
 - M35015-XXXSP 2
- Reversed character display function

APPLICATION

TV, VCR, Camcorder

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS


PIN DESCRIPTION

Pin Number	Symbol	Pin name	Input /Output	Function
1	OSC1	Pins for attachment of external oscillator circuit	Input	There are the pins for attaching an external display oscillator circuit. The standard oscillation frequency is approximately 7MHz. This oscillation frequency determines the horizontal position of the display on the TV screen and the width of the characters.
2	OSC2		Output	
3	$\overline{CS}$	Chip select input	Input	This is the chip select pin, and when serial data transmission is being carried out, it goes to "L". Hysteresis input. Built-in pull-up resistor is included.
4	SCK	Serial clock input	Input	When $\overline{CS}$ pin is "L", SIN serial data is taken in when SCK rises. Hysteresis input. Built-in pull-up resistor is included.
5	SIN	Serial data input	Input	This is the pin for serial input of data and addresses for the display control register and the display data memory. Hysteresis input. Built-in pull-up resistor is included.
6	$\overline{AC}$	Auto-clear input	Input	When "L", this pin resets the internal IC circuit. Hysteresis input. Built-in pull-up resistor is included.
7	V _{DD2}	Power pin	—	Please connect to +5V with the analog circuit power pin.
8	CVIDEO	Composite video signal output	Output	This is the output pin for composite video signals. It outputs 2V _{P-P} composite video signals. In superimpose mode, character output etc. is superimposed on the external composite video signals from CVIN.
9	LECHA	Character level input	Input	This is the input pin which determines the "white" character color level in the composite video signal.
10	CVIN	Composite video signal input	Input	This is the input pin for external composite video signals. In superimpose mode, character output etc. is superimposed on these external composite video signals.
11	V _{SS}	Earthing pin	—	Please connect to GND using circuit earthing pin.
12	P0	Port P0 output	Output	This pin can be toggled between port pin output and BLNK1* (character background) signal output. Polarity can be selected when the character ROM is masked.
13	P1	Port P1 output	Output	This pin can be toggled between port pin output and CO1* (character) signal output. Polarity can be selected when the character ROM is masked.
14	P2	Port P2 output	Output	This pin can be toggled between port pin output and BLNK2* (character background) signal output. Polarity can be selected when the character ROM is masked.
15	P3	Port P3 output	Output	This pin can be toggled between port pin output and CO2* (character) signal output. Polarity can be selected when the character ROM is masked.
16	OSCOU†	Pins for attachment of external oscillator circuit for synchronization signal generation	Output	These are the pins for attaching an external oscillator circuit for generating the synchronization signal. An oscillation of 14.32MHz is needed for NTSC, 17.73MHz is needed for PAL and 14.30MHz is needed for M-PAL.
17	OSCIN		Input	
18	HOR*	Horizontal synchronization signal input	Input	This pin inputs the horizontal synchronization signal. Hysteresis input. Polarity can be selected when the character ROM is masked.
19	VERT*	Vertical synchronization signal input	Input	This pin inputs the vertical synchronization signal. Hysteresis input. Polarity can be selected when the character ROM is masked.
20	V _{DD1}	Power pin	—	Please connect to +5V with the digital circuit power pin.

Note : The pins remarked "*" are selectable the input or output polarity when the character ROM masked.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS



mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

MEMORY CONSTITUTION

Address 00₁₆ to EF₁₆ are assigned to the display RAM,
address F0₁₆ to F8₁₆ are assigned to the display control
registers.

Bit Address	DA7	DA6	DA5	DA4	DA3	DA2	DA1	DA0	Remarks
00 ₁₆	EXP	0	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀	Display RAM
⋮	Expansion bit	⋮	Character code						
EF ₁₆	EXP	0	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀	
F0 ₁₆	PTD 3	PTD 2	PTD 1	PTD 0	PTC 3	PTC 2	PTC 1	PTC 0	Port output specify
F1 ₁₆	TBASE 1	TBASE 0	HP 5	HP 4	HP 3	HP 2	HP 1	HP 0	Horizontal display start position specify
F2 ₁₆	$\overline{\text{INT}}/\text{NON}$	SEPV	VP 5	VP 4	VP 3	VP 2	VP 1	VP 0	Vertical display start position specify
F3 ₁₆	VSZ 21	VSZ 20	VSZ 11	VSZ 10	HSZ 21	HSZ 20	HSZ 11	HSZ 10	Character size specify
F4 ₁₆	DSP 7	DSP 6	DSP 5	DSP 4	DSP 3	DSP 2	DSP 1	DSP 0	Display mode specify
F5 ₁₆	$\overline{\text{N}}/\text{P}$	TEST 2	TEST 1	TEST 0	EXP 1	EXP 0	DSP 9	DSP 8	Expansion
F6 ₁₆	EQP	PAL H	MPAL	ALL 24	FSC	BLINK 2	BLINK 1	BLINK 0	Blinking specify and so on
F7 ₁₆	BLKHF	BB	BG	BR	LEVEL 0	PHASE 2	PHASE 1	PHASE 0	Raster color specify
F8 ₁₆	DSP ON	CONT7F	STOP 1	STOP IN	RAM ERS	EX	BLK 1	BLK 0	Control display

Fig. 1 Memory constitution (M35014-XXXSP)

At the M35014-XXXSP

The internal circuit is reset and all display control registers (address F0₁₆ to F8₁₆) are set to "0" and display RAM (address 00₁₆ to EF₁₆) are set to "7F₁₆" when the $\overline{\text{AC}}$ pin level is "L". The memory constitution is shown in Figure 1.

At the M35015-XXXSP

The internal circuit is reset and all display control registers (address F0₁₆ to F8₁₆) are set to "0" and display RAM (address 00₁₆ to EF₁₆) are set to "FF₁₆" when the $\overline{\text{AC}}$ pin level is "L". The memory constitution is shown in Figure 2.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

Address \ Bit	DAF	DAE	DAD	DAC	DAB	DAA	DA9	DA8	DA7	DA6	DA5	DA4	DA3	DA2	DA1	DA0	Remarks	
00 ₁₆	0	0	0	0	0	REV	BLINK	C ₈	C ₇	C ₆	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀	Display RAM	
⋮	⋮	⋮	⋮	⋮	⋮	Reversed character	Blinking	Character code										
EF ₁₆	0	0	0	0	0	REV	BLINK	C ₈	C ₇	C ₆	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀		
F0 ₁₆	0	0	0	0	0	0	0	0	PTD3	PTD2	PTD1	PTD0	PTC3	PTC2	PTC1	PTC0	Port output specify	
F1 ₁₆	0	0	0	0	0	0	0	0	TBAS1	TBAS0	HP5	HP4	HP3	HP2	HP1	HP0	Horizontal display start position specify	
F2 ₁₆	0	0	0	0	0	0	0	0	INT/ NON	SEPV	VP5	VP4	VP3	VP2	VP1	VP0	Vertical display start position specify	
F3 ₁₆	0	0	0	0	0	0	0	0	VSZ 21	VSZ 20	VSZ 11	VSZ 10	HSZ 21	HSZ 20	HSZ 11	HSZ 10	Character size specify	
F4 ₁₆	0	0	0	0	0	0	0	0	DSP7	DSP6	DSP5	DSP4	DSP3	DSP2	DSP1	DSP0	Display mode specify	
F5 ₁₆	0	0	0	0	0	0	0	0	N/P	TEST 2	TEST 1	TEST 0	EXP1	EXP0	DSP9	DSP8	Expansion	
F6 ₁₆	0	0	0	0	0	0	0	0	EQP	PALH	MPAL	ALL 24	FSC	BLINK 2	BLINK 1	BLINK 0	Blinking specify and so on	
F7 ₁₆	0	0	0	0	0	0	0	0	BLKHF	BB	BG	BR	LEVEL 0	PHASE 2	PHASE 1	PHASE 0	Raster color specify	
F8 ₁₆	0	0	0	0	0	0	0	0	DSPON	CONT 7F	STOP 1	STOP IN	RAMERS	EX	BLK1	BLK0	Control display	

Fig. 2 Memory constitution (M35015-XXXSP)

※DA8 to DAF of the display control registers (addresses F0₁₆ to F8₁₆) are set to "0".

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

SCREEN CONSTITUTION

The screen lines and rows are determined from each address of the display RAM. The screen constitution is shown in Figure 3.

Row Line	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
1	00 ₁₆	01 ₁₆	02 ₁₆	03 ₁₆	04 ₁₆	05 ₁₆	06 ₁₆	07 ₁₆	08 ₁₆	09 ₁₆	0A ₁₆	0B ₁₆	0C ₁₆	0D ₁₆	0E ₁₆	0F ₁₆	10 ₁₆	11 ₁₆	12 ₁₆	13 ₁₆	14 ₁₆	15 ₁₆	16 ₁₆	17 ₁₆
2	18 ₁₆	19 ₁₆	1A ₁₆	1B ₁₆	1C ₁₆	1D ₁₆	1E ₁₆	1F ₁₆	20 ₁₆	21 ₁₆	22 ₁₆	23 ₁₆	24 ₁₆	25 ₁₆	26 ₁₆	27 ₁₆	28 ₁₆	29 ₁₆	2A ₁₆	2B ₁₆	2C ₁₆	2D ₁₆	2E ₁₆	2F ₁₆
3	30 ₁₆	31 ₁₆	32 ₁₆	33 ₁₆	34 ₁₆	35 ₁₆	36 ₁₆	37 ₁₆	38 ₁₆	39 ₁₆	3A ₁₆	3B ₁₆	3C ₁₆	3D ₁₆	3E ₁₆	3F ₁₆	40 ₁₆	41 ₁₆	42 ₁₆	43 ₁₆	44 ₁₆	45 ₁₆	46 ₁₆	47 ₁₆
4	48 ₁₆	49 ₁₆	4A ₁₆	4B ₁₆	4C ₁₆	4D ₁₆	4E ₁₆	4F ₁₆	50 ₁₆	51 ₁₆	52 ₁₆	53 ₁₆	54 ₁₆	55 ₁₆	56 ₁₆	57 ₁₆	58 ₁₆	59 ₁₆	5A ₁₆	5B ₁₆	5C ₁₆	5D ₁₆	5E ₁₆	5F ₁₆
5	60 ₁₆	61 ₁₆	62 ₁₆	63 ₁₆	64 ₁₆	65 ₁₆	66 ₁₆	67 ₁₆	68 ₁₆	69 ₁₆	6A ₁₆	6B ₁₆	6C ₁₆	6D ₁₆	6E ₁₆	6F ₁₆	70 ₁₆	71 ₁₆	72 ₁₆	73 ₁₆	74 ₁₆	75 ₁₆	76 ₁₆	77 ₁₆
6	78 ₁₆	79 ₁₆	7A ₁₆	7B ₁₆	7C ₁₆	7D ₁₆	7E ₁₆	7F ₁₆	80 ₁₆	81 ₁₆	82 ₁₆	83 ₁₆	84 ₁₆	85 ₁₆	86 ₁₆	87 ₁₆	88 ₁₆	89 ₁₆	8A ₁₆	8B ₁₆	8C ₁₆	8D ₁₆	8E ₁₆	8F ₁₆
7	90 ₁₆	91 ₁₆	92 ₁₆	93 ₁₆	94 ₁₆	95 ₁₆	96 ₁₆	97 ₁₆	98 ₁₆	99 ₁₆	9A ₁₆	9B ₁₆	9C ₁₆	9D ₁₆	9E ₁₆	9F ₁₆	AO ₁₆	A1 ₁₆	A2 ₁₆	A3 ₁₆	A4 ₁₆	A5 ₁₆	A6 ₁₆	A7 ₁₆
8	A8 ₁₆	A9 ₁₆	AA ₁₆	AB ₁₆	AC ₁₆	AD ₁₆	AE ₁₆	AF ₁₆	B0 ₁₆	B1 ₁₆	B2 ₁₆	B3 ₁₆	B4 ₁₆	B5 ₁₆	B6 ₁₆	B7 ₁₆	B8 ₁₆	B9 ₁₆	BA ₁₆	BB ₁₆	BC ₁₆	BD ₁₆	BE ₁₆	BF ₁₆
9	C0 ₁₆	C1 ₁₆	C2 ₁₆	C3 ₁₆	C4 ₁₆	C5 ₁₆	C6 ₁₆	C7 ₁₆	C8 ₁₆	C9 ₁₆	CA ₁₆	CB ₁₆	CC ₁₆	CD ₁₆	CE ₁₆	CF ₁₆	D0 ₁₆	D1 ₁₆	D2 ₁₆	D3 ₁₆	D4 ₁₆	D5 ₁₆	D6 ₁₆	D7 ₁₆
10	D8 ₁₆	D9 ₁₆	DA ₁₆	DB ₁₆	DC ₁₆	DD ₁₆	DE ₁₆	DF ₁₆	E0 ₁₆	E1 ₁₆	E2 ₁₆	E3 ₁₆	E4 ₁₆	E5 ₁₆	E6 ₁₆	E7 ₁₆	E8 ₁₆	E9 ₁₆	EA ₁₆	EB ₁₆	EC ₁₆	ED ₁₆	EE ₁₆	EF ₁₆

The hexadecimal numbers in the boxes show the display RAM address.

Fig. 3 Screen constitution

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

REGISTERS DESCRIPTION

(1) Address F0₁₆

DA	Register	Contents		Remarks
		Status	Function	
0	PTC0	①	P0 output (port P0)	Port output control
		1	BLNK1* output	
1	PTC1	①	P1 output (port P1)	
		1	CO1* output	
2	PTC2	①	P2 output (port P2)	
		1	BLNK2* output	
3	PTC3	①	P3 output (port P3)	Port data control
		1	CO2* output	
4	PTD0	①	P0 output "L"	
		1	P0 output "H"	
5	PTD1	①	P1 output "L"	
		1	P1 output "H"	
6	PTD2	①	P2 output "L"	
		1	P2 output "H"	
7	PTD3	①	P3 output "L"	
		1	P3 output "H"	

Note : The mark ① around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(2) Address F1₁₆


DA	Register	Contents		Remarks																	
		Status	Function																		
0	HP0 (LSB)	⓪	If HS is the horizontal display start location, $HS = T \times (4 \sum_{n=0}^5 2^n HP_n + N).$ T : The oscillation cycle of oscillator OSC1, CSC2 <table><tr><td>HSZ11</td><td>HSZ10</td><td rowspan="2">N</td></tr><tr><td>HSZ21</td><td>HSZ20</td></tr><tr><td>0</td><td>0</td><td>9</td></tr><tr><td>0</td><td>1</td><td>10</td></tr><tr><td>1</td><td>0</td><td>11</td></tr><tr><td>1</td><td>1</td><td>12</td></tr></table>	HSZ11	HSZ10	N	HSZ21	HSZ20	0	0	9	0	1	10	1	0	11	1	1	12	Horizontal display start location is specified using the 6 bits from HP5 to HP0. Note : HP5 to 0 = (000000₂) and (000001₂) setting is forbidden.
HSZ11	HSZ10	N																			
HSZ21	HSZ20																				
0	0	9																			
0	1	10																			
1	0	11																			
1	1	12																			
1	HP1	⓪																			
		1																			
2	HP2	⓪																			
		1																			
3	HP3	⓪																			
		1																			
4	HP4	⓪																			
		1																			
5	HP5 (MSB)	⓪																			
		1																			
6	TBASE0	⓪	No correction for the synchronous error by a noise.	The synchronized signal correction setting.																	
		1	Correction for the synchronous error by a noise.																		
7	TBASE1	⓪	No correction for a lack of the synchronized signal.																		
		1	Correction for a lack of the synchronized signal.																		

Note : The mark ⓪ around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(3) Address F₂₁₆

DA	Register	Contents		Remarks
		Status	Function	
0	VP0 (LSB)	⓪	If VS is the vertical display start location, $VS = H \times (4 \sum_{n=0}^5 2^n VP_n + 3).$ H : Cycle with the horizontal synchronizing pulse 	The vertical start location is specified using the 6 bits from VP5 to VP0.
		1		
1	VP1	⓪		
		1		
2	VP2	⓪		
		1		
3	VP3	⓪		
		1		
4	VP4	⓪		
		1		
5	VP5 (MSB)	⓪		
		1		
6	SEPV	⓪	Input both horizontal synchronization signal and vertical synchronization signal.	The contents of synchronization signal input in 'superimpose display' is altered.
		1	Input the horizontal (composite) synchronization signal only.	
7	INT/NON	⓪	Interlace	Scanning lines control (only in internal synchronization)
		1	Non-interlace	

Note : The mark ⓪ around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

mitsubishi microcomputers
M35014-XXXSP,M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(4) Address F3₁₆

DA	Register	Contents		Remarks											
		Status	Function												
0	HSZ10	⓪	<table><tr><td>HSZ10 HSZ11</td><td>0</td><td>1</td></tr><tr><td>0</td><td>1T/1dot</td><td>2T/1dot</td></tr><tr><td>1</td><td>3T/1dot</td><td>4T/1dot</td></tr></table>	HSZ10 HSZ11	0	1	0	1T/1dot	2T/1dot	1	3T/1dot	4T/1dot	Character size setting in the horizontal direction for the first line.		
		HSZ10 HSZ11		0	1										
0	1T/1dot	2T/1dot													
1	3T/1dot	4T/1dot													
1															
1	HSZ11	⓪													
		1													
2	HSZ20	⓪		<table><tr><td>HSZ20 HSZ21</td><td>0</td><td>1</td></tr><tr><td>0</td><td>1T/1dot</td><td>2T/1dot</td></tr><tr><td>1</td><td>3T/1dot</td><td>4T/1dot</td></tr></table>	HSZ20 HSZ21	0	1	0	1T/1dot	2T/1dot	1	3T/1dot		4T/1dot	Character size setting in the horizontal direction for the 2nd line to 10th line.
		HSZ20 HSZ21			0	1									
0	1T/1dot	2T/1dot													
1	3T/1dot	4T/1dot													
1															
3	HSZ21	⓪													
		1													
4	VSZ10	⓪	<table><tr><td>VSZ10 VSZ11</td><td>0</td><td>1</td></tr><tr><td>0</td><td>1H/1dot</td><td>2H/1dot</td></tr><tr><td>1</td><td>3H/1dot</td><td>4H/1dot</td></tr></table>		VSZ10 VSZ11	0	1	0	1H/1dot	2H/1dot	1	3H/1dot	4H/1dot	Character size setting in the vertical direction for the first line.	
		VSZ10 VSZ11			0	1									
0	1H/1dot	2H/1dot													
1	3H/1dot	4H/1dot													
1															
5	VSZ11	⓪													
		1													
6	VSZ20	⓪		<table><tr><td>VSZ20 VSZ21</td><td>0</td><td>1</td></tr><tr><td>0</td><td>1H/1dot</td><td>2H/1dot</td></tr><tr><td>1</td><td>3H/1dot</td><td>4H/1dot</td></tr></table>	VSZ20 VSZ21	0	1	0	1H/1dot	2H/1dot	1	3H/1dot	4H/1dot		Character size setting in the vertical direction for the 2nd line to 10th line.
		VSZ20 VSZ21			0	1									
0	1H/1dot	2H/1dot													
1	3H/1dot	4H/1dot													
1															
7	VSZ21	⓪													
		1													

Note : The mark ⓪ around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(5) Address F4₁₆

DA	Register	Contents		Remarks																												
		Status	Function																													
0	DSP0	①	Line 1 is in the display mode specified by BLK0 and BLK1.	DSP0 to DSP9 are each controlled independently.																												
		1	Line 1 is in a different display mode.																													
1	DSP1	①	Line 2 is in the display mode specified by BLK0 and BLK1.	<table><tr><th>BLK1</th><th>BLK0</th><th>DSPn</th><th>Display mode for line n</th></tr><tr><td rowspan="2">0</td><td rowspan="2">0</td><td>0</td><td>Border (Note1)</td></tr><tr><td>1</td><td>Character</td></tr><tr><td rowspan="2">0</td><td rowspan="2">1</td><td>0</td><td>Character</td></tr><tr><td>1</td><td>Border</td></tr><tr><td rowspan="2">1</td><td rowspan="2">0</td><td>0</td><td>Border</td></tr><tr><td>1</td><td>Matrix-outline</td></tr><tr><td rowspan="2">1</td><td rowspan="2">1</td><td>0</td><td>Matrix-outline</td></tr><tr><td>1</td><td>Character</td></tr></table>	BLK1	BLK0	DSPn	Display mode for line n	0	0	0	Border (Note1)	1	Character	0	1	0	Character	1	Border	1	0	0	Border	1	Matrix-outline	1	1	0	Matrix-outline	1	Character
		BLK1	BLK0		DSPn	Display mode for line n																										
0	0	0	Border (Note1)																													
		1	Character																													
0	1	0	Character																													
		1	Border																													
1	0	0	Border																													
		1	Matrix-outline																													
1	1	0	Matrix-outline																													
		1	Character																													
2	DSP2	①	Line 3 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 3 is in a different display mode.																													
3	DSP3	①	Line 4 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 4 is in a different display mode.																													
4	DSP4	①	Line 5 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 5 is in a different display mode.																													
5	DSP5	①	Line 6 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 6 is in a different display mode.																													
6	DSP6	①	Line 7 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 7 is in a different display mode.																													
7	DSP7	①	Line 8 is in the display mode specified by BLK0 and BLK1.																													
		1	Line 8 is in a different display mode.																													

Note : The mark ① around the status value means the reset status by the "L" level is input to AC pin.

mitsubishi microcomputers
M35014-XXXSP,M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(6) Address F5₁₆

DA	Register	Contents		Remarks												
		Status	Function													
0	DSP8	⓪	Line 9 is in the display mode specified by BLK0 and BLK1.	See the remarks of address F4 ₁₆ .												
		1	Line 9 is in the different display mode.													
1	DSP9	⓪	Line 10 is in the display mode specified by BLK0 and BLK1.													
		1	Line 10 is in the different display mode.													
2	EXP0	⓪	<table><tr><td></td><td>EXP0</td><td>0</td><td>1</td></tr><tr><td>EXP1</td><td>0</td><td>Normal character + Blinking</td><td>Reversed character (No blinking)</td></tr><tr><td></td><td>1</td><td>Normal character + Exclusion</td><td>Reversed character + Exclusion</td></tr></table>		EXP0	0	1	EXP1	0	Normal character + Blinking	Reversed character (No blinking)		1	Normal character + Exclusion	Reversed character + Exclusion	For M35014-XXXSP, these registers are used to extend the function of the EXP bits in the addresses 0 ₁₆ to EF ₁₆ of the display RAM. For M35015-XXXSP, these registers are used to extend the function of the REV bits and BLINK bits in the addresses 0 ₁₆ to EF ₁₆ of the display RAM.
	EXP0	0		1												
EXP1	0	Normal character + Blinking		Reversed character (No blinking)												
	1	Normal character + Exclusion		Reversed character + Exclusion												
3	EXP1	⓪														
		1														
4	TEST0	⓪	TEST0 to TEST2=(000 ₂)→Normal display (010 ₂)→Space display													
5	TEST1	1														
		⓪														
6	TEST2	1														
		⓪														
7	N/P	⓪			<table><tr><td></td><td>MPAL</td><td>0</td><td>1</td></tr><tr><td>N/P</td><td>0</td><td>NTSC</td><td>M-PAL</td></tr><tr><td></td><td>1</td><td>PAL</td><td>Do not use</td></tr></table>		MPAL	0	1	N/P	0	NTSC	M-PAL		1	PAL
	MPAL	0	1													
N/P	0	NTSC	M-PAL													
	1	PAL	Do not use													
	1															

Note : The mark ⓪ around the status value means the reset status by "L" level is input to AC pin.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(7) Address F6₁₆

DA	Register	Contents		Remarks									
		Status	Function										
0	BLINK0	①	<table><tr><td>BLINK0 \ BLINK1</td><td>0</td><td>1</td></tr><tr><td>0</td><td>Blinking OFF</td><td>Duty 25%</td></tr><tr><td>1</td><td>Duty 50%</td><td>Duty 75%</td></tr></table>	BLINK0 \ BLINK1	0	1	0	Blinking OFF	Duty 25%	1	Duty 50%	Duty 75%	Blinking duty ratio can be altered.
BLINK0 \ BLINK1	0	1											
0	Blinking OFF	Duty 25%											
1	Duty 50%	Duty 75%											
	1												
1	BLINK1	①											
	1												
2	BLINK2	①	Division of vertical synchronization signal into 1/64. Cycle approximately 1 second.	Blinking cycle can be altered.									
	1	Division of vertical synchronization signal into 1/32. Cycle approximately 0.5 second.											
3	FSC	①	OSCIN oscillation frequency 4 × fsc	Oscillation frequency setting for OSCIN terminal (only effective with NTSC).									
	1	OSCIN oscillation frequency 2 × fsc											
4	ALL24	①	Blanking with all 24 characters in matrix-outline size.	Horizontal display range can be altered when all characters are in matrix-outline size (Note 2).									
	1	Horizontal display period blanked.											
5	MPAL	①	<table><tr><td>MPAL \ N/P</td><td>0</td><td>1</td></tr><tr><td>0</td><td>NTSC</td><td>M-PAL</td></tr><tr><td>1</td><td>PAL</td><td>Do not use</td></tr></table>	MPAL \ N/P	0	1	0	NTSC	M-PAL	1	PAL	Do not use	Synchronization signal is selected with this register and N/P register (address F5 ₁₆).
MPAL \ N/P	0	1											
0	NTSC	M-PAL											
1	PAL	Do not use											
	1												
6	PALH	①	Interlace 1 Noninterlace 1	In NTSC mode, status is "0".									
	1	Interlace 2 Noninterlace 2											
7	EQP	①	Not include the equivalent pulse	Setting the contents of composite synchronized signal at non-interlace.									
	1	Include the equivalent pulse											

Notes 1. The mark ① around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.
2. Fix to "0" this register at external synchronous.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP,M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(8) Address F7₁₆

DA	Register	Contents					Remarks																																														
		Status	Function																																																		
0	PHASE0	①	<table><tr><th>PHASE2</th><th>PHASE1</th><th>PHASE0</th><th>NTSC Phase angle(color)</th><th>PAL phase angle(color)</th></tr><tr><td>0</td><td>0</td><td>0</td><td>(Black)</td><td>(Black)</td></tr><tr><td>0</td><td>0</td><td>1</td><td>$\pi/2$ [rad.]</td><td>$\pm \pi/2$ [rad.]</td></tr><tr><td>0</td><td>1</td><td>0</td><td>$7\pi/4$ [rad.]</td><td>$\mp \pi/4$ [rad.]</td></tr><tr><td>0</td><td>1</td><td>1</td><td>same phase</td><td>same phase</td></tr><tr><td>1</td><td>0</td><td>0</td><td>π [rad.]</td><td>$\pm \pi$ [rad.]</td></tr><tr><td>1</td><td>0</td><td>1</td><td>$3\pi/4$ [rad.]</td><td>$\pm 3\pi/4$ [rad.]</td></tr><tr><td>1</td><td>1</td><td>0</td><td>$3\pi/2$ [rad.]</td><td>$\mp \pi/2$ [rad.]</td></tr><tr><td>1</td><td>1</td><td>1</td><td>(White)</td><td>(White)</td></tr></table>					PHASE2	PHASE1	PHASE0	NTSC Phase angle(color)	PAL phase angle(color)	0	0	0	(Black)	(Black)	0	0	1	$\pi/2$ [rad.]	$\pm \pi/2$ [rad.]	0	1	0	$7\pi/4$ [rad.]	$\mp \pi/4$ [rad.]	0	1	1	same phase	same phase	1	0	0	π [rad.]	$\pm \pi$ [rad.]	1	0	1	$3\pi/4$ [rad.]	$\pm 3\pi/4$ [rad.]	1	1	0	$3\pi/2$ [rad.]	$\mp \pi/2$ [rad.]	1	1	1	(White)	(White)	Raster color setting. Coloring by composite video signals means that the phase angle of the background color signals for the color burst signals can be varied. The angle can be varied in units of $\pi/4$ rad. This differs from coloring by RGB output.
PHASE2	PHASE1	PHASE0	NTSC Phase angle(color)	PAL phase angle(color)																																																	
0	0	0	(Black)	(Black)																																																	
0	0	1	$\pi/2$ [rad.]	$\pm \pi/2$ [rad.]																																																	
0	1	0	$7\pi/4$ [rad.]	$\mp \pi/4$ [rad.]																																																	
0	1	1	same phase	same phase																																																	
1	0	0	π [rad.]	$\pm \pi$ [rad.]																																																	
1	0	1	$3\pi/4$ [rad.]	$\pm 3\pi/4$ [rad.]																																																	
1	1	0	$3\pi/2$ [rad.]	$\mp \pi/2$ [rad.]																																																	
1	1	1	(White)	(White)																																																	
1	PHASE1	①																																																			
		1																																																			
2	PHASE2	①																																																			
		1																																																			
3	LEVEL0	①	Internal bias OFF					Generation of composite video signal bias potential																																													
		1	Internal bias ON																																																		
4	BR	①	<table><tr><th>BB</th><th>BG</th><th>BR</th><th>NTSC phase angle(color)</th><th>PAL phase angle(color)</th></tr><tr><td>0</td><td>0</td><td>0</td><td>(Black)</td><td>(Black)</td></tr><tr><td>0</td><td>0</td><td>1</td><td>$\pi/2$ [rad.]</td><td>$\pm \pi/2$ [rad.]</td></tr><tr><td>0</td><td>1</td><td>0</td><td>$7\pi/4$ [rad.]</td><td>$\mp \pi/4$ [rad.]</td></tr><tr><td>0</td><td>1</td><td>1</td><td>same phase</td><td>same phase</td></tr><tr><td>1</td><td>0</td><td>0</td><td>π [rad.]</td><td>$\pm \pi$ [rad.]</td></tr><tr><td>1</td><td>0</td><td>1</td><td>$3\pi/4$ [rad.]</td><td>$\pm 3\pi/4$ [rad.]</td></tr><tr><td>1</td><td>1</td><td>0</td><td>$3\pi/2$ [rad.]</td><td>$\mp \pi/2$ [rad.]</td></tr><tr><td>1</td><td>1</td><td>1</td><td>(White)</td><td>(White)</td></tr></table>					BB	BG	BR	NTSC phase angle(color)	PAL phase angle(color)	0	0	0	(Black)	(Black)	0	0	1	$\pi/2$ [rad.]	$\pm \pi/2$ [rad.]	0	1	0	$7\pi/4$ [rad.]	$\mp \pi/4$ [rad.]	0	1	1	same phase	same phase	1	0	0	π [rad.]	$\pm \pi$ [rad.]	1	0	1	$3\pi/4$ [rad.]	$\pm 3\pi/4$ [rad.]	1	1	0	$3\pi/2$ [rad.]	$\mp \pi/2$ [rad.]	1	1	1	(White)	(White)	Character background color setting.
BB	BG	BR	NTSC phase angle(color)	PAL phase angle(color)																																																	
0	0	0	(Black)	(Black)																																																	
0	0	1	$\pi/2$ [rad.]	$\pm \pi/2$ [rad.]																																																	
0	1	0	$7\pi/4$ [rad.]	$\mp \pi/4$ [rad.]																																																	
0	1	1	same phase	same phase																																																	
1	0	0	π [rad.]	$\pm \pi$ [rad.]																																																	
1	0	1	$3\pi/4$ [rad.]	$\pm 3\pi/4$ [rad.]																																																	
1	1	0	$3\pi/2$ [rad.]	$\mp \pi/2$ [rad.]																																																	
1	1	1	(White)	(White)																																																	
5	BG	①																																																			
		1																																																			
6	BB	①																																																			
		1																																																			
7	BLKHF	①	The halftone displaying "OFF" in superimpose					This register is available in the superimpose displaying only.																																													
		1	The halftone displaying "ON" in superimpose																																																		

Note : The mark ① around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

(9) Address F8₁₆

DA	Register	Contents		Remarks									
		Status	Function										
0	BLK0	①	<table><tr><td>BLK0 \ BLK1</td><td>0</td><td>1</td></tr><tr><td>0</td><td>Blanking OFF</td><td>Character size</td></tr><tr><td>1</td><td>Border size</td><td>Matrix-outline size</td></tr></table>	BLK0 \ BLK1	0	1	0	Blanking OFF	Character size	1	Border size	Matrix-outline size	Display mode variable
		BLK0 \ BLK1		0	1								
0	Blanking OFF	Character size											
1	Border size	Matrix-outline size											
1													
1	BLK1	①											
		1											
2	EX	①	External synchronization	Synchronization signal switching									
		1	Internal synchronization										
3	RAMERS	①	RAM not erased	This register does not have the function as register. If RAM is erase continuously, set DSPON (address F8 ₁₆) to "0".									
		1	RAM erased										
4	STOPIN	①	Oscillaion of OSCIN, OSCOUT for synchronization signals.	OSCIN oscillation stop (Note 2)									
		1	Stop oscillation of OSCIN, OSCOUT, for synchronization signals.										
5	STOP1	①	Oscillation of OSC1, OSC2 for display.	OSC1 and OSC2 oscillation switching. To stop the oscillation, set CS pin to "H" level and DSPON (address F8 ₁₆) to "0".									
		1	Stop the oscillation OSC1, OSC2 for display.										
6	CONT7F	①	Normal write mode.	Usually "0" fix. Writing mode of the serial data input switching. (Note 3) For M35015-XXXSP, continuously writing mode (character code FF ₁₆).									
		1	Continuously writing mode (character code 7F ₁₆) ^{Note.3}										
7	DSPON	①	Display OFF	Display can be altered.									
		1	Display ON										

Notes 1. The mark ① around the status value means the reset status by the "L" level is input to $\overline{AC}$ pin.

2. When crystal oscillation move from external synchronous to internal synchronous at stop state (STOPIN=1), leave the crystal oscillation state (STOPIN=0) before 1V (vertical synchronous NTSC, M-PAL about 16.7ms, PAL 20ms) or more.

MITSUBISHI MICROCOMPUTERS

M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

DISPLAY FORMS

M35014-XXXSP has the following five display forms as the blanking function, when CO1*, BLNK1*, CO2*, and BLNK2* are output.

- (1) Blanking OFF : Blanking output signal (BLNK*) is cut off.
- (2) Character size : Blanking same as the character size.

- (3) Border size : Blanking the background as a size from character.
- (4) Matrix-outline size : Blanking the background as a size from all character font size.

This display format allows each line (from the first line to the tenth line) to be controlled independently, so that two kinds of display formats can be combined on the same screen.




Fig. 4 Display forms at each display mode

MITSUBISHI MICROCOMPUTERS

M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

EXCLUSION FUNCTION

For M35014-XXXSP, the function expansion that is set with the EXP1 and EXP0 registers (DA3 and DA2 of address F5₁₆) is performed when "1" is set to DA7 of display RAM (EXP bit).

Table 1 Display form of M35014-XXXSP

Register		Display form
EXP1	EXP0	
0	0	Normal character + Blinking
0	1	Reversed character (no blinking)
1	0	Normal character + Exclusion 1
1	1	Reversed character + Exclusion 1

For M35015-XXXSP, the displays shown in table 2 are available with the combination of DA9 (BLINK bit), DAA (REV bit) of display RAM and EXP1, EXP0 register (DA3 and DA2 of address F5₁₆).

When the exclusion 1 function is selected, CO2 * and BLNK2* side are not displayed.

When the exclusion 2 function is selected, CO1*, BLNK1*, and video signal side are not displayed.

The character of exclusion 2 and exclusion 1 are prohibited to be next to each other horizontally. Insert "FF₁₆" of character between the character of exclusion 2 and that of exclusion 1.

Table 2 Display form of M35015-XXXSP

Register		RAM		Display form
EXP1	EXP0	REV	BLINK	
0	0	0	0	Normal character
		0	1	Normal character + Blinking
		1	0	Reversed character
		1	1	Reversed character + Blinking
0	1	0	0	Normal character + Exclusion 2
		0	1	Normal character + Blinking + Exclusion 1
		1	0	Reversed character + Exclusion 2
		1	1	Reversed character + Blinking + Exclusion 1
1	0	0	0	Normal character
		0	1	Normal character + Exclusion 1
		1	0	Reversed character
		1	1	Reversed character + Exclusion 1
1	1	0	0	Normal character
		0	1	Normal character + Blinking
		1	0	Normal character + Exclusion 1
		1	1	Normal character + Blinking + Exclusion 1

mitsubishi MICROCOMPUTERS
M35014-XXXSP,M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

The figure 5 and 6 show the display examples using ports
P0 to P3 (digital output).




Fig. 5 Display example using ports P0(BLNK1*) and P1(CO1*) (display line)




Fig. 6 Display example using ports P2(BLNK2*) and P3(CO2*) (record line)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

DATA INPUT EXAMPLE

Data of display RAM and display control registers can be set by the serial input function. Example of data setting at M35014-XXXSP is shown in Figure 7, and example of data setting at M35015-XXXSP is shown in Figure 8.

No.	Memory Contents		DA 7	DA 6	DA 5	DA 4	DA 3	DA 2	DA 1	DA 0
	Address/Data	Addition								
1	Address F8 ₁₆	Display OFF	1	1	1	1	1	0	0	0
2	Data (F8 ₁₆)		0	0	0	0	1	×	×	×
3	Data (00 ₁₆)	Setting to display RAM (address 00 ₁₆ to EF ₁₆) and registers (addresses F0 ₁₆ to F8 ₁₆)	EXP	0	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
4	Data (01 ₁₆)		EXP	0	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
	...									
242	Data (EF ₁₆)		EXP	0	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
243	Data (F0 ₁₆)		PTD 3	PTD 2	PTD 1	PTD 0	PTC 3	PTC 2	PTC 1	PTC 0
244	Data (F1 ₁₆)		0	0	HP 5	HP 4	HP 3	HP 2	HP 1	HP 0
245	Data (F2 ₁₆)		0	0	VP 5	VP 4	VP 3	VP 2	VP 1	VP 0
246	Data (F3 ₁₆)		VSZ 21	VSZ 20	VSZ 11	VSZ 10	HSZ 21	HSZ 20	HSZ 11	HSZ 10
247	Data (F4 ₁₆)		DSP 7	DSP 6	DSP 5	DSP 4	DSP 3	DSP 2	DSP 1	DSP 0
248	Data (F5 ₁₆)		N/P	0	0	0	EXP 1	EXP 0	DSP 9	DSP 8
249	Data (F6 ₁₆)		EQP	PAL H	MPAL	ALL 24	FSC	BLINK 2	BLINK 1	BLINK 0
250	Data (F7 ₁₆)		BLKHF	BB	BG	BR	1	PHASE 2	PHASE 1	PHASE 0
251	Data (F8 ₁₆)	Display ON	1	0	0	0	0	EX	BLK 1	BLK 0

Fig. 7 Example of data setting by the serial input function (M35014-XXXSP)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

No.	Memory Contents		DAF	DAE	DAD	DAC	DAB	DAA	DA9	DA8	DA7	DA6	DA5	DA4	DA3	DA2	DA1	DA0
	Address/Data	Addition																
1	Address (F8 ₁₆)	Display OFF	0	0	0	0	0	0	0	0	1	1	1	1	1	0	0	0
2	Data (F8 ₁₆)		0	0	0	0	0	0	0	0	0	0	0	0	1	×	×	×
3	Data (00 ₁₆)	Setting to display RAM (address 00 ₁₆ to EF ₁₆) and registers (addresses F0 ₁₆ to F8 ₁₆)	0	0	0	0	0	REV	BLINK	C ₈	C ₇	C ₆	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
4	Data (01 ₁₆)		0	0	0	0	0	REV	BLINK	C ₈	C ₇	C ₆	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
	⋮																	
	⋮																	
242	Data (EF ₁₆)		0	0	0	0	0	REV	BLINK	C ₈	C ₇	C ₆	C ₅	C ₄	C ₃	C ₂	C ₁	C ₀
243	Data (F0 ₁₆)		0	0	0	0	0	0	0	PTD	PTD	PTD	PTD	PTC	PTC	PTC	PTC	PTC
										3	2	1	0	3	2	1	0	
244	Data (F1 ₁₆)		0	0	0	0	0	0	0	0	0	HP	HP	HP	HP	HP	HP	HP
												5	4	3	2	1	0	
245	Data (F2 ₁₆)		0	0	0	0	0	0	0	0	0	VP	VP	VP	VP	VP	VP	VP
												5	4	3	2	1	0	
246	Data (F3 ₁₆)		0	0	0	0	0	0	0	0	VSZ	VSZ	VSZ	VSZ	HSZ	HSZ	HSZ	HSZ
											21	20	11	10	21	20	11	10
247	Data (F4 ₁₆)		0	0	0	0	0	0	0	0	DSP	DSP	DSP	DSP	DSP	DSP	DSP	DSP
											7	6	5	4	3	2	1	0
248	Data (F5 ₁₆)		0	0	0	0	0	0	0	0	N/P	0	0	0	EXP	EXP	DSP	DSP
														1	0	9	8	
249	Data (F6 ₁₆)		0	0	0	0	0	0	0	0	EQP	PALH	MPAL	ALL	FSC	BLINK	BLINK	BLINK
											24			24		2	1	0
250	Data (F7 ₁₆)		0	0	0	0	0	0	0	0	BLKHF	BB	BG	BR	1	PHASE	PHASE	PHASE
															2	1	0	
251	Data (F8 ₁₆)	Display ON	0	0	0	0	0	0	0	0	1	0	0	0	0	EX	BLK	BLK
																1	0	

Fig. 8 Example of data setting by the serial input function (M35015-XXXSP)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

SERIAL DATA INPUT TIMING

At the M35014-XXXSP

- (1) Serial data should be input with the LSB first.
- (2) The address consists of 8 bits.
- (3) The data consists of 8 bits.
- (4) The 8 bits in the SCK after the $\overline{CS}$ signal has fallen are the address, and for succeeding input data, the address is incremented every 8 bits.

At the M35015-XXXSP

- (1) Serial data should be input with the LSB first.
- (2) The address consists of 16 bits.
- (3) The data consists of 16 bits.
- (4) The 16 bits in the SCK after the $\overline{CS}$ signal has fallen are the address, and for succeeding input data, the address is incremented every 16 bits.




Fig. 9 Serial input timing (M35014-XXXSP)




Fig. 10 Serial input timing (M35015-XXXSP)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

CONT7F FUNCTION

When the register CONT7F (DA6 of address $F8_{16}$) is set to "1" and data input as the timing shown in Figure 11, the character code $7F_{16}$ ^{Note.1} (blank) can be set to display RAM automatically. However, be necessary to set the hold time. While this function is operating, never stop the display oscillation OSC1 and OSC2, and set the register STOP1 (DA5 of address $F8_{16}$) to "0".

Note.1 For M35015-XXXSP, the character code FF_{16} (blank) can be set to display RAM automatically.




Fig. 11 CONT7F functional timing

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

TIME BASE (SYNCHRONOUS SIGNAL CORRECTION) FUNCTION

Time base function can correct the errors from the lost synchronous signal or disordered synchronization by a noise, using the reference clock fosc1.

The following are the correction method.

- (1) Time base 0—TBASE0 (DA6 of address F1₁₆)="1".
 - Cut-off a noise effect to synchronous signal.
 - Cut-off a noise during D period of Figure 12.
- (2) Time base 1—TBASE1 (DA7 of address F1₁₆)="1"
 - Correct the lost synchronous signal.
 - Generate the pulse if the synchronous signal has not input during C period of Figure 12. And stop to display the character till the next synchronous signal is input.




Fig. 12 Example of time base function

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

CHARACTER FONT

Images are composed on a 12×18 dot matrix, and characters can be linked vertically and horizontally with other characters to allow the display the continuous symbols.




Fig. 13 Character font and border

Character code $7F_{16}$ is fixed as blank, without a background at the M35014-XXXSP.

Character code FF_{16} is fixed as blank, without a background at the M35015-XXXSP.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

TIMING REQUIREMENTS ($T_A = -20^\circ\text{C}$ to $+70^\circ\text{C}$, $V_{DD} = 5 \pm 0.5\text{V}$, unless otherwise noted)

Serial data input at the M35014-XXXSP

Symbol	Parameter	Limits			Unit	Remarks
		Min.	Typ.	Max.		
$t_w(\text{SCK})$	SCK width	200	—	—	ns	See Figure 14
$t_{su}(\overline{\text{CS}})$	$\overline{\text{CS}}$ setup time	200	—	—	ns	
$t_h(\overline{\text{CS}})$	$\overline{\text{CS}}$ hold time	2	—	—	μs	
$t_{su}(\text{SIN})$	SIN setup time	200	—	—	ns	
$t_h(\text{SIN})$	SIN hold time	200	—	—	ns	
t_{word}	1 word writing time	5	—	—	μs	




Fig. 14 Serial input timing requirements (M35014-XXXSP)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

TIMING REQUIREMENTS ($T_a = -20^\circ\text{C}$ to $+70^\circ\text{C}$, $V_{DD} = 5 \pm 0.5\text{V}$, unless otherwise noted)

Serial data input at the M35015-XXXSP

Symbol	Parameter	Limits			Unit	Remarks
		Min.	Typ.	Max.		
$t_w(\text{SCK})$	SCK width	200	—	—	ns	See Figure 15
$t_{su}(\overline{\text{CS}})$	$\overline{\text{CS}}$ setup time	200	—	—	ns	
$t_h(\overline{\text{CS}})$	$\overline{\text{CS}}$ hold time	2	—	—	μs	
$t_{su}(\text{SIN})$	SIN setup time	200	—	—	ns	
$t_h(\text{SIN})$	SIN hold time	200	—	—	ns	
t_{word}	1 word writing time	10	—	—	μs	




Fig. 15 Serial input timing requirements (M35015-XXXSP)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Conditions	Ratings	Unit
V_{DD}	Supply voltage	With respect to V_{SS}	-0.3 to 6.0	V
V_I	Input voltage		$V_{SS}-0.3 \leq V_I \leq V_{DD}+0.3$	V
V_O	Output voltage		$V_{SS} \leq V_O \leq V_{DD}$	V
P_d	Power dissipation	$T_a=25^\circ\text{C}$	300	mW
T_{opr}	Operating temperature		-20 to 70	$^\circ\text{C}$
T_{stg}	Storage temperature		-40 to 125	$^\circ\text{C}$

RECOMMENDED OPERATING CONDITIONS ($V_{DD}=5\text{V}$, $T_a=-20$ to 70°C , unless otherwise noted)

Symbol	Parameter	Limits			Unit
		Min.	Typ.	Max.	
V_{DD}	Supply voltage	4.5	5.0	5.5	V
V_{IH}	"H" level input voltage SIN, SCK, CS, AC, HOR*, VERT*	$0.8V_{DD}$	V_{DD}	V_{DD}	V
V_{IL}	"L" level input voltage SIN, SCK, CS, AC, HOR*, VERT*	0	0	$0.2V_{DD}$	V
V_{CVIN}	Composite-video signal input voltage CVIN	—	$2V_{P-P}$	—	V
f_{OSC1}	Oscillating frequency for display	6.3	7.0	7.7	MHz
f_{OSCIN}	Oscillating frequency for synchronized signal	—	14.30 14.32 17.73	—	MHz

ELECTRICAL CHARACTERISTICS ($V_{DD}=5\text{V}$, $f_{OSC1}=7.0\text{MHz}$, $T_a=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
V_{DD}	Supply voltage	$T_a=-20$ to 70°C	4.5	5.0	5.5	V
I_{DD}	Supply current		—	—	20	mA
V_{OH}	"H" level output voltage, P0 to P3	$V_{DD}=4.5\text{V}$, $I_{OH}=0.4\text{mA}$	3.5	—	—	V
V_{OL}	"L" level output voltage, P0 to P3	$V_{DD}=4.5\text{V}$, $I_{OL}=0.4\text{mA}$	—	—	0.4	V
R_I	Pull-up resistance SCK, AC, CS, SIN		10	30	100	k Ω

VIDEO SIGNAL INPUT CONDITIONS ($V_{DD}=5\text{V}$, $T_a=-20$ to 70°C , unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
V_{IN-SC}	Composite-video signal input clamp voltage	Sync-chip voltage	—	1.5	—	V

Note for Supplying Power

Timing of power supplying to $\overline{AC}$ pin

The internal circuit of M35014-XXXSP/M35015-XXXSP is reset when the level of the auto clear input pin $\overline{AC}$ is "L". This pin is hysteresis input with the pull-up resistor. The timing about power supplying of $\overline{AC}$ pin is shown in Figure 16.




Fig. 16 Timing of power supplying to $\overline{AC}$ pin

After supplying the power (V_{DD} and V_{SS}) to M35014-XXXSP/M35015-XXXSP and the supply voltage becomes more than $0.8 \times V_{DD}$, it needs to keep V_{IL} time; t_w of the $\overline{AC}$ pin for more than 1ms.

Power supply timing about V_{DD1} pin and V_{DD2} pin.

The power need to supply to V_{DD1} and V_{DD2} at a time, though it is separated perfectly between the V_{DD1} as the digital line and the V_{DD2} as the analog line.

PRECAUTION FOR USE

Notes on noise and latch-up

In order to avoid noise and latch-up, connect a bypass capacitor ($\approx 0.1\mu F$) directly between the V_{DD} pin and V_{SS} pin using a heavy wire.

Ask your crystal oscillator manufacture to examine the matching conditions between this device and the crystal oscillator.

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

STANDARD ROM TYPE : M35014-001SP

M35014-001SP is a standard ROM type of M35014-XXXSP.
 The input/output polarity and character patterns are fixed
 to the contents of Table 3 and Figure 17 and 18.

Table 3 Input/output polarity of pins

Pin name	I/O	Polarity
HOR*	Input	Negative
VERT*	Input	Negative
P3(CO2*)	Output	Positive
P2(BLNK2*)	Output	Positive
P1(CO1*)	Output	Positive
P0(BLNK1*)	Output	Positive




Fig. 17 M35014-001SP character patterns (1)

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 18 M35014-001SP character patterns (2)

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS

STANDARD ROM TYPE : M35015-001SP

M35015-001SP is a standard ROM type of M35015-XXXSP.
 The input/output polarity and character patterns are fixed
 to the contents of Table 4 and Figure 19 to 29.

Table 4 Input/output polarity of pins

Pin name	I/O	Polarity
HOR*	Input	Negative
VERT*	Input	Negative
P3(CO2*)	Output	Positive
P2(BLNK2*)	Output	Positive
P1(CO1*)	Output	Positive
P0(BLNK1*)	Output	Positive




Fig. 19 M35015-001SP character patterns (1)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 20 M35015-001SP character patterns (2)

mitsubishi MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 21 M35015-001SP character patterns (3)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 22 M35015-001SP character patterns (4)

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 23 M35015-001SP character patterns (5)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 24 M35015-001SP character patterns (6)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS



Fig. 25 M35015-001SP character patterns (7)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS



Fig. 26 M35015-001SP character patterns (8)

mitsubishi microcomputers
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS



Fig. 27 M35015-001SP character patterns (9)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP,M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS



Fig. 28 M35015-001SP character patterns (10)

MITSUBISHI MICROCOMPUTERS
M35014-XXXSP, M35015-XXXSP

SCREEN CHARACTER and PATTERN DISPLAY CONTROLLERS




Fig. 29 M35015-001SP character patterns (11)