




RoHS



KMMX Series Micro Universal Serial Bus 3.0

Features

- Also Known as SuperSpeed USB
- More Compact Footprint than Mini-USB
- Meets the USB-IF 3.0 Specification
- Stainless Steel Shell, Which Yields 10,000 Insertion Cycles
- Used in Portable Devices Such as Mobile Phones, PDAs, and Digital Cameras



Performance Specifications

Materials and Finish

Insulator: LCP+50%GF UL 94V-0 Rated, Black Color

Contacts: 30μ" Gold Plating over Nickel on Contact Area,
Gold Flash Plating on Solder Tail

Shell: Stainless Steel, Nickel Plated

Electrical Characteristics

Rated Voltage: 5V AC (RMS Max.)

Rated Current: 1.8A (only Pin 1,5); 0.25A For Other Pins

Dielectric Withstanding Voltage: 100V AC for 1 min.

Insulation Resistance: 100 Megohms Min.

Contact Resistance: 50 milliohms Max.

Operating Temperature: See Drawing

Mechanical Characteristics

Insertion Force: 35N Max.

Withdrawal Force: 8N Min.

Durability: 10000 cycles Min.

UNIVERSAL SERIAL BUS 3.0

KMMX Series

Documentation & Ordering Information

Kycon Part

Part Number Builder

Series	Type	Mounting Option	Insulator Option	Plating Option	Packaging
--------	------	--------------------	---------------------	-------------------	-----------

Series

KMMX - Micro Universal Serial Bus

Type

AB10 - AB Type, 10 pins

B10 - B Type, 10 pins

Mounting Option

SMT1S - Surface Mount with Through Hole Shield Tabs

SMT4S - Surface Mount with SMT Shield Tabs

Insulator Color Option

B - Black

Plating Option

30 - 30μ" Gold


Packaging

TR - Tape and Reel

*See next page for dimensions

KMMX-AB10-SMT1SB30


Dimensions in mm



Pin Number	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND
6	MicA_SSTX-
7	MicA_SSTX+
8	GND_DRAIN
9	MicA_SSRX-
10	MicA_SSRX+

KMMX-B10-SMT4SB30

Dimensions in mm



Pin Number	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND
6	MicA_SSTX-
7	MicA_SSTX+
8	GND_DRAIN
9	MicA_SSRX-
10	MicA_SSRX+

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KMMX-AB10-SMT1SB30TR](#) [KMMX-AB10-SMT4SB30TR](#) [KMMX-B10-SMT1SB30TR](#) [KMMX-B10-SMT4SB30TR](#)