




REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
B		ECO-15-006810	29DEC2015	LL SH

- MATERIAL:
 - HOUSING
PBT POLYESTER, BLACK, UL 94V-0.
 - TERMINALS
0.33 THICK PHOSPHOR BRONZE PLATED WITH 1.27µm MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2µm MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE.
 - SHIELD
0.25 THICK COPPER ALLOY PLATED WITH 2.03µm MINIMUM BRIGHT TIN OVER 1.27µm MINIMUM NICKEL.
 - LIGHT EMITTING DIODE (LED)
DIFFUSED EPOXY LENS, 12.95 CARBON STL WIREFRAME LEADS PREPLATED WITH 2.29µm SILVER OVER 1.02µm NICKEL UNDERPLATE OVER 2.03µm COPPER UNDERPLATE.
 - LED ACTION PIN - COMPLIANT PIN CONTACTS 0.3 THICK BRASS PLATED WITH 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- ALL DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
 - 4 DRILLED HOLE DIA = 1.02±.025.
COPPER THICKNESS = 0.025-0.075.
TIN THICKNESS = 0.008 MIN.
 - 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
 - 6 DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN.
 - 7 CONTACTS ARE NOT INTENDED TO BE ALIGNED WITH EACH OTHER.
 - 8 SUGGESTED OPERATING CURRENT FOR LEDS IS 20 mA.



LED COLOR	DESCRIPTION	PART NUMBER
GREEN/YELLOW	WITH GROUND CLIP	6368035-4
GREEN/YELLOW	WITHOUT GROUND CLIP	6368035-3
GREEN	WITHOUT GROUND CLIP	6368035-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: L. VARELA 29 JUL 2005	TE Connectivity NAME: STACKED MODULAR JACK ASSEMBLY 2 X 6 OFFSET, W/LEDS, 8 POSN, RJ45 SHIELDED PANEL GROUND, CAT 5
mm	0 PLC ±.13	CHK: J. WESTMAN 29 JUL 2005	
	1 PLC ±0.13	APVD: S. FLICKINGER 29 JUL 2005	
	2 PLC ±.13	PRODUCT SPEC: 108-1854	
	3 PLC ±.13	APPLICATION SPEC: 114-2160	SIZE: CAGE CODE DRAWING NO. RESTRICTED TO
MATERIAL:	FINISH:	WEIGHT:	A100779C=6368035
		CUSTOMER DRAWING	SCALE: 4:1 SHEET 1 OF 2 REV B

