

Amp	Volt	Hz	IP Ident. colour + h	Part No.	Panel sockets straight	2 P +	IEC/EN 60309		EAN No. 4015609...
					flange dimension 75 x 75, fingerproof according to VBG 4				
16	230 110 400	50/60 50/60 50/60	6 4 9	411 306 411 304 411 309	 			10 128	018734 018727 018758
32	230 110 400	50/60 50/60 50/60	6 4 9	430 306 430 304 430 309	 			10 208	019564 019557 019571
					flange dimension 107 x 100, fingerproof according to VBG 4				
63	230 110 400	50/60 50/60 50/60	6 4 9	460 306 460 304 460 309	 			5 586	020287 020270 020294
125	see page 2/134				flange dimension 62 x 62, fingerproof according to VBG 4				
16	230 110 400	50/60 50/60 50/60	6 4 9	410 306 410 304 410 309	 			10/60 117	018376 018369 018406
					installation in switch cabinets, junction box mountable on DIN-rails, seizes 4,5 MCB module units				
16	230 110 400	50/60 50/60 50/60	6 4 9	411 306VS 411 304VS 411 309VS	 			10 201	132546 160754 160761
32	230 110 400	50/60 50/60 50/60	6 4 9	430 306VS 430 304VS 430 309VS	 			10 277	160969 160952 160976

Amp	Volt	Hz	IP Ident. colour + h	Part No.	Panel sockets straight	2 P +	IEC/EN 60 309		EAN No. 4015609...																																	
					detachable flange, flange dimension 62 x 62, fingerproof according to VBG 4																																					
16	230	50/60	6	412 306	 																																					
	110	50/60	4	412 304																																						
	400	50/60	9	412 309																																						
					fixing dimension = a + b, flange dim. = d + e																																					
					<table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>h</th><th>n</th><th>p</th></tr><tr><td>16 A</td><td>47</td><td>47</td><td>5,5</td><td>62</td><td>62</td><td>58</td><td>50</td><td>32</td><td>8,5</td></tr></table>	Ampère	a	b	c	d	e	f	h	n	p	16 A	47	47	5,5	62	62	58	50	32	8,5																	
Ampère	a	b	c	d	e	f	h	n	p																																	
16 A	47	47	5,5	62	62	58	50	32	8,5																																	
					detachable flange, flange dimension 80 x 80, fingerproof according to VBG 4																																					
32	230	50/60	6	431 306	 																																					
	110	50/60	4	431 304																																						
	400	50/60	9	431 309																																						
					fixing dimension = a + b, flange dimension = d + e																																					
					<table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>h</th><th>n</th><th>p</th></tr><tr><td>32 A</td><td>60</td><td>60</td><td>5,5</td><td>80</td><td>80</td><td>60</td><td>71</td><td>32</td><td>8,5</td></tr></table>	Ampère	a	b	c	d	e	f	h	n	p	32 A	60	60	5,5	80	80	60	71	32	8,5																	
Ampère	a	b	c	d	e	f	h	n	p																																	
32 A	60	60	5,5	80	80	60	71	32	8,5																																	
					mondo RAL 7035 light grey																																					
16	230	50/60	6	415 306	 																																					
	110	50/60	4	415 304																																						
	400	50/60	9	415 309																																						
230 50/60 6 415 306 RW																																										
RW = clear white, RAL 9010																																										
230 50/60 6 415 306 PW																																										
PW = pearl white, RAL 1013																																										
32	230	50/60	6	435 306	 																																					
	110	50/60	4	435 304																																						
	400	50/60	9	435 309																																						
230 50/60 6 435 306 RW																																										
RW = clear white, RAL 9010																																										
230 50/60 6 435 306 PW																																										
PW = pearl white, RAL 1013																																										
					fixing dimension = a + b, flange dimension = d + e																																					
					<table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>h</th><th>n</th><th>r</th><th>z</th></tr><tr><td>16 A</td><td>30,4</td><td>65,2</td><td>4,1</td><td>90</td><td>90</td><td>38</td><td>65</td><td>36</td><td>96</td><td>/</td></tr><tr><td>32 A</td><td>60</td><td>60</td><td>4,1</td><td>90</td><td>90</td><td>45</td><td>75</td><td>31</td><td>104</td><td>80</td></tr></table>	Ampère	a	b	c	d	e	f	h	n	r	z	16 A	30,4	65,2	4,1	90	90	38	65	36	96	/	32 A	60	60	4,1	90	90	45	75	31	104	80				
Ampère	a	b	c	d	e	f	h	n	r	z																																
16 A	30,4	65,2	4,1	90	90	38	65	36	96	/																																
32 A	60	60	4,1	90	90	45	75	31	104	80																																