

NTE2430 Silicon NPN Transistor High Voltage Amp/Switch (Compl to NTE2431)

Description:

The NTE2430 is a silicon NPN transistor in a SOT-89 type surface mount package designed for use in amplifier and switching applications.


Absolute Maximum Ratings:

Collector-Base Voltage (Open Emitter), V_{CBO}	400V
Collector-Emitter Voltage (Open Base), V_{CEO}	350V
Emitter-Base Voltage (Open Collector), V_{EBO}	5V
DC Collector Current, I_C	1A
Base Current, I_B	500mA
Total Power Dissipation ($T_A \leq +25^\circ\text{C}$, Note 1), P_{tot}	1W
Operating Junction Temperature, T_J	+150°C
Storage Temperature Range, T_{stg}	-65° to +150°C
Thermal Resistance, Junction-to-Ambient (Note 1), R_{thJA}	125K/W

Note 1. Device mounted on a ceramic substrate; area = 2.5cm², thickness = 0.7mm.

Electrical Characteristics: ($T_J = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Collector Cutoff Current	I_{CES}	$V_{CE} = 300V, I_B = 0$	—	—	20	nA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = 5V, I_C = 0$	—	—	10	μA
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 50mA, I_B = 4mA$	—	—	500	mV
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 50mA, I_B = 4mA$	—	—	1.3	V
DC Current Gain	h_{FE}	$V_{CE} = 10V, I_C = 20mA$	40	—	—	
Collector Capacitance	C_c	$I_E = I_C = 0, V_{CB} = 10, f = 1MHz$	—	—	2	pF
Transitional Frequency	f_T	$V_{CE} = 10V, I_C = 10mA, f = 5MHz$	70	—	—	MHz



Bottom View