



Micro Commercial Components



Micro Commercial Components  
 20736 Marilla Street Chatsworth  
 CA 91311  
 Phone: (818) 701-4933  
 Fax: (818) 701-4939

# MBR1080CT THRU MBR10100CT

## 10 Amp Schottky Barrier Rectifier 80-100 Volts

### Features

- Metal of silicon rectifier, majority carrier conductor
- Guard ring for transient protection
- Low power loss high efficiency
- High surge capacity, High current capability
- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0 and MSL Rating 1

### Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +175°C
- Mounting Torque: 5 in-lbs Maximum


| MCC Catalog Number | Device Marking | Maximum Recurrent Peak Reverse Voltage | Maximum RMS Voltage | Maximum DC Blocking Voltage |
|--------------------|----------------|--|---------------------|-----------------------------|
| MBR1080CT          | MBR1080CT      | 80V                                    | 56V                 | 80V                         |
| MBR10100CT         | MBR10100CT     | 100V                                   | 70V                 | 100V                        |

### Electrical Characteristics @ 25°C Unless Otherwise Specified

|   |             |               |  |
|---|-------------|---------------|--|
| Average Forward Current                                 | $I_{F(AV)}$ | 10A           | $T_C = 100^\circ\text{C}$  |
| Peak Forward Surge Current                              | $I_{FSM}$   | 120A          | 8.3ms, half sine   |
| Maximum Forward Voltage Drop Per Element                | $V_F$       | .85V<br>.75V  | $I_{FM} = 5A$<br>$T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$ |
| Maximum DC Reverse Current At Rated DC Blocking Voltage | $I_R$       | 0.2mA<br>15mA | $T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$                  |
| Typical Junction Capacitance                            | $C_J$       | 300pF         | Measured at 1.0MHz, $V_R=4.0V$   |

Notes:1.High Temperature Solder Exemption Applied, see EU Directive Annex 7.

### TO-220AB



| DIM | DIMENSIONS |      |       |       | NOTE |
|-----|------------|------|-------|-------|------|
|     | INCHES     |      | MM    |       |      |
| A   | .560       | .625 | 14.22 | 15.88 |      |
| B   | .380       | .420 | 9.65  | 10.67 |      |
| C   | .140       | .190 | 3.56  | 4.82  |      |
| D   | .020       | .045 | 0.51  | 1.14  |      |
| F   | .139       | .161 | 3.53  | 4.09  | Ø    |
| G   | .190       | .110 | 2.29  | 2.79  |      |
| H   | ---        | .250 | ---   | 6.35  |      |
| J   | .012       | .025 | 0.30  | 0.64  |      |
| K   | .500       | .580 | 12.70 | 14.73 |      |
| L   | .045       | .060 | 1.14  | 1.52  |      |
| N   | .190       | .210 | 4.83  | 5.33  |      |
| Q   | .100       | .135 | 2.54  | 3.43  |      |
| R   | .080       | .115 | 2.04  | 2.92  |      |
| S   | .045       | .055 | 1.14  | 1.39  |      |
| T   | .230       | .270 | 5.84  | 6.86  |      |
| U   | ----       | .050 | ----  | 1.27  |      |
| V   | .045       | ---- | 1.15  | ----  |      |

**RATING AND CHARACTERISTIC CURVES**  
**MBR1080CT thru MBR 10100CT**

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.4 - TYPICAL FORWARD CHARACTERISTICS





FIG.5 - TYPICAL JUNCTION CAPACITANCE





Micro Commercial Components

## Ordering Information

|                  |                |
|------------------|----------------|
| Device           | Packing        |
| (Part Number)-BP | Bulk;1Kpcs/Box |

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

[www.mccsemi.com](http://www.mccsemi.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[MBR10100CT-BP](#)