

# R82 Series, Radial, 5 mm Lead Spacing, 50 – 400 VDC (Automotive Grade)

## Overview

The R82 Series is constructed of metallized polyester film (wound or stacked technology) with radial leads of tinned wire. Radial leads are electrically welded to the contact metal layer on the ends of the capacitor winding. The capacitor is encapsulated in a self-extinguishing solvent resistant plastic case with thermosetting resin material meeting the UL 94V-0 requirements.

Automotive grade devices are available and meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.

## Applications

Typical applications include blocking, coupling, decoupling, timing and oscillator circuits. Not suitable for across-the-line application (see Suppressor Capacitors).

## Benefits

- Voltage range: 50 – 400 VDC
- Capacitance range: 0.001  $\mu$ F – 4.7  $\mu$ F
- Lead Spacing: 5 mm
- Capacitance tolerance:  $\pm 5\%$ ,  $\pm 10\%$ ,  $\pm 20\%$
- Climatic category: 55/105/56
- Operating temperature range of -55°C to +105°C
- RoHS compliance and lead-free terminations
- Tape and reel packaging in accordance with IEC 60286-2
- Self-healing
- Automotive (AEC-Q200) grades available


## Part Number System

| R82                  | D                                                 | C           | 3470                                                                                                                        | AA                         | 60                   | J                                                 |
|----------------------|---------------------------------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------|---------------------------------------------------|
| Series               | Rated Voltage (VDC)                               | Length (mm) | Capacitance Code (pF)                                                                                                       | Lead and Packaging Code    | Internal Use         | Capacitance Tolerance                             |
| Metallized Polyester | C = 50<br>D = 63<br>E = 100<br>I = 250<br>M = 400 | C = 5.0     | Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added. | See Ordering Options Table | 30<br>50<br>60<br>70 | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ |

## Ordering Options Table

| Lead Spacing<br>Nominal (mm) | Type of Leads and Packaging                | LL Lead Length<br>(mm) | Lead and<br>Packaging<br>Code |
|------------------------------|--------------------------------------------|------------------------|-------------------------------|
| 5                            | <b>Standard Lead and Packaging Options</b> |                        |                               |
|                              | Bulk (Bag)–Short Leads                     | 4 +1.5/-0              | AA                            |
|                              | Ammo Pack                                  | $H_0=18.5 \pm 0.5$     | DQ                            |
|                              | <b>Other Lead and Packaging Options</b>    |                        |                               |
|                              | Tape & Reel (Standard Reel)                | $H_0 = 18.5 \pm 0.5$   | CK                            |
|                              | Bulk (Bag)–Short Leads                     | 2.7 +0.5/-0            | JA                            |
|                              | Bulk (Bag)–Short Leads                     | 3.5 +0.5/-0            | JB                            |
|                              | Bulk (Bag)–Short Leads                     | 10 +/- 1               | JC                            |
|                              | Bulk (Bag)–Short Leads                     | 4.0 +0.5/-0            | JE                            |
|                              | Bulk (Bag)–Short Leads                     | 3.2 +0.3/-0.2          | JH                            |
|                              | Bulk (Bag)–Long Leads                      | 21 +/- 1               | JG                            |
|                              | Bulk (Bag)–Long Leads                      | 17 +/- 2               | Z3                            |
|                              | Bulk (Bag)–Long Leads                      | 30 +5/-0               | 40                            |

## Dimensions – Millimeters



| p                                                                              |           | B       |           | H       |           | L       |           | d       |           |
|--------------------------------------------------------------------------------|-----------|---------|-----------|---------|-----------|---------|-----------|---------|-----------|
| Nominal                                                                        | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance |
| 5.0                                                                            | +/-0.4    | 2.5     | +0.1      | 6.5     | +0.1      | 7.2     | +0.2      | 0.6     | +/-0.05   |
| 5.0                                                                            | +/-0.4    | 3.5     | +0.1      | 7.5     | +0.1      | 7.2     | +0.2      | 0.6     | +/-0.05   |
| 5.0                                                                            | +/-0.4    | 4.5     | +0.1      | 9.5     | +0.1      | 7.2     | +0.3      | 0.6     | +/-0.05   |
| 5.0                                                                            | +/-0.4    | 5.0     | +0.1      | 10.0    | +0.1      | 7.2     | +0.3      | 0.6     | +/-0.05   |
| 5.0                                                                            | +/-0.4    | 6.0     | +0.1      | 11.0    | +0.1      | 7.2     | +0.3      | 0.6     | +/-0.05   |
| 5.0                                                                            | +/-0.4    | 7.2     | +0.1      | 13.0    | +0.1      | 7.2     | +0.3      | 0.6     | +/-0.05   |
| Note: See Ordering Options Table for lead length (LL/H <sub>0</sub> ) options. |           |         |           |         |           |         |           |         |           |

## Performance Characteristics

|                                         |                                                                                                                                                                     |           |           |              |               |                |               |
|-----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-----------|--------------|---------------|----------------|---------------|
| Dielectric                              | Polyester film (polyethylene terephthalate).                                                                                                                        |           |           |              |               |                |               |
| Plates                                  | Metal layer deposited by evaporation under vacuum.                                                                                                                  |           |           |              |               |                |               |
| Winding                                 | Non-inductive type.                                                                                                                                                 |           |           |              |               |                |               |
| Leads                                   | Tinned wire.                                                                                                                                                        |           |           |              |               |                |               |
| Protection                              | Plastic case, thermosetting resin filled. Box material is solvent resistant and flame retardant according to UL94.                                                  |           |           |              |               |                |               |
| Related Documents                       | IEC 60384-2                                                                                                                                                         |           |           |              |               |                |               |
| Rated Voltage $V_R$ (VDC)               | 50                                                                                                                                                                  | 63        | 100       | 250          | 250           | 400            | 400           |
| Rated Voltage $V_R$ (VAC)               | 30                                                                                                                                                                  | 40        | 63        | 140          | 160           | 160            | 200           |
| Capacitance Range ( $\mu\text{F}$ )     | 2.2 – 4.7                                                                                                                                                           | 0.1 – 1.5 | 0.001 – 1 | 0.022 – 0.22 | 0.0068 – 0.15 | 0.0068 – 0.068 | 0.001 – 0.047 |
| Capacitance Values                      | E6 series (IEC 60063) measured @ 1 kHz and $+20 \pm 1^\circ\text{C}$                                                                                                |           |           |              |               |                |               |
| Capacitance Tolerance                   | $\pm 5\%$ , $\pm 10\%$ , $\pm 20\%$                                                                                                                                 |           |           |              |               |                |               |
| Operating Temperature Range             | $-55^\circ\text{C}$ to $105^\circ\text{C}$                                                                                                                          |           |           |              |               |                |               |
| Rated Temperature $T_R$                 | $+85^\circ\text{C}$                                                                                                                                                 |           |           |              |               |                |               |
| Voltage Derating                        | Above $+85^\circ\text{C}$ DC and AC voltage derating is 1.25%/°C                                                                                                    |           |           |              |               |                |               |
| Climatic Category                       | 55/105/56 IEC 60068-1                                                                                                                                               |           |           |              |               |                |               |
|                                         | Average relative humidity $\leq 75\%$                                                                                                                               |           |           |              |               |                |               |
|                                         | RH = 95% for 30 days per year                                                                                                                                       |           |           |              |               |                |               |
|                                         | RH = 85% for further days limited by average value per year                                                                                                         |           |           |              |               |                |               |
| Test Voltage                            | $1.4 \times V_R$ VDC for 2 seconds (between terminations) @ $+25^\circ\text{C} \pm 5^\circ\text{C}$                                                                 |           |           |              |               |                |               |
| Capacitance Drift                       | Maximum 3% after a 2 year storage period at a temperature of $+10^\circ\text{C}$ to $+40^\circ\text{C}$ and a relative humidity of 40% to 60%                       |           |           |              |               |                |               |
| Reliability<br>(Reference MIL-HDBK-217) | Operational life >200,000 hours                                                                                                                                     |           |           |              |               |                |               |
|                                         | Failure rate $\leq 1$ FIT, $T = +40^\circ\text{C}$ , $V = 0.5 \times V_R$                                                                                           |           |           |              |               |                |               |
|                                         | Failure criteria: open or short circuit, cap. change > 10%, DF 2 times the catalog limits, IR < 0.005 x initial limit                                               |           |           |              |               |                |               |
| Maximum Pulse Steepness                 | dV/dt according to Table 1. For peak to peak voltages lower than rated voltage ( $V_{pp} < V_R$ ), the specified dv/dt can be multiplied by the factor $V_R/V_{pp}$ |           |           |              |               |                |               |
| Temperature Coefficient                 | $+400 (\pm 200)$ ppm/°C at 1 kHz                                                                                                                                    |           |           |              |               |                |               |
| Self Inductance<br>(Lead Length ~ 2 mm) | Approximately 7 nH. Maximum 1nH per 1 mm lead and capacitor length.                                                                                                 |           |           |              |               |                |               |


## Performance Characteristics cont'd

| Dissipation Factor $\tan\delta$ | Maximum Values @ 25°C ±5°C                       |             |                      |                 |
|---------------------------------|--------------------------------------------------|-------------|----------------------|-----------------|
|                                 | Frequency                                        | C ≤ 0.1 μF  | C > 1 μF             |                 |
|                                 | 1 kHz                                            | 0.80%       | 0.80%                |                 |
|                                 | 10 kHz                                           | 1.20%       | 1.20%                |                 |
|                                 | 100 kHz                                          | 2.50%       | –                    |                 |
| Insulation Resistance           | Measured @ +25°C ±5°C, according to IEC 60384–2  |             |                      |                 |
|                                 | Minimum Values Between Terminals                 |             |                      |                 |
|                                 | Voltage Charge/Time                              | C ≤ 0.33 μF | 0.33 μF < C ≤ 1.0 μF | C > 1.0 μF      |
|                                 | 50 VDC for V <sub>R</sub> ≤ 100 VDC<br>1 minute  | ≥ 15,000 MΩ | ≥ 5,000 MΩ • μF      | ≥ 1,000 MΩ • μF |
|                                 | 100 VDC for V <sub>R</sub> > 100 VDC<br>1 minute | ≥ 30,000 MΩ |                      |                 |


## Qualification

Automotive Grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at [www.aecouncil.com](http://www.aecouncil.com).

## Maximum Voltage ( $V_{rms}$ ) vs. Frequency (Sinusoidal Waveform/ $T_h \leq 40^\circ\text{C}$ ) Lead Spacing 5 mm



## Maximum Current ( $I_{rms}$ ) vs. Frequency (Sinusoidal Waveform/ $T_h \leq 40^\circ\text{C}$ ) Lead Spacing 5 mm



## Environmental Test Data

| Damp Heat, Steady State Test      | Test Conditions:                                             |                                                     | Performances                                                                                                                     |
|-----------------------------------|--------------------------------------------------------------|-----------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
|                                   | Temperature:<br>Relative humidity (RH):<br>Test duration:    | +40°C ±2°C<br>93% ±2%<br>56 days                    | Δ C/C  ≤ 5%,<br>Δ tanδ ≤ 0.005 @ 1 kHz<br>IR after test ≥ 50% of initial limit                                                   |
| Endurance Test                    | Test Conditions                                              |                                                     | Performances                                                                                                                     |
|                                   | Temperature:<br>Voltage applied:<br>Test duration:           | +105°C ±2°C<br>1.25 x V <sub>C</sub><br>2,000 hours | Δ C/C  ≤ 5%,<br>Δ tanδ ≤ 0.003 @10 kHz for C ≤ 1μF<br>Δ tanδ ≤ 0.002 @ 1 kHz for C > 1μF<br>IR after test ≥ 50% of initial limit |
| Resistance to Soldering Heat Test | Test Conditions                                              |                                                     | Performances                                                                                                                     |
|                                   | Solder bath temperature:<br>Dipping time (with heat screen): | 260°C ±5°C<br>10 seconds ±1 second                  | Δ C/C  ≤ 2%,<br>Δ tanδ ≤ 0.003 @10 kHz for C ≤ 1μF<br>Δ tanδ ≤ 0.002 @ 1 kHz for C > 1μF<br>IR after test ≥ initial limit        |

## Environmental Compliance

All KEMET MKT capacitors are RoHS Compliant.



RoHS Compliant

Table 1 – Ratings &amp; Part Number Reference

| VDC       | VAC       | Capacitance Value (μF) | Dimensions in mm |             |            | Lead Spacing | dV/dt (V/μs) | Maximum K <sub>0</sub> (V <sup>2</sup> /μs) | New KEMET Part Number   | Legacy Part Number       |
|-----------|-----------|------------------------|------------------|-------------|------------|--------------|--------------|---------------------------------------------|-------------------------|--------------------------|
|           |           |                        | B                | H           | L          |              |              |                                             |                         |                          |
| 50        | 30        | 2.2                    | 6.0              | 11.0        | 7.2        | 5.0          | 100          | 10000                                       | 82CC4220(1)70(2)        | R82CC4220(1)70(2)        |
| <b>50</b> | <b>30</b> | <b>3.3</b>             | <b>7.2</b>       | <b>13.0</b> | <b>7.2</b> | <b>5.0</b>   | <b>25</b>    | <b>2500</b>                                 | <b>82CC4330(1)30(2)</b> | <b>R82CC4330(1)30(2)</b> |
| <b>50</b> | <b>30</b> | <b>4.7</b>             | <b>7.2</b>       | <b>13.0</b> | <b>7.2</b> | <b>5.0</b>   | <b>25</b>    | <b>2500</b>                                 | <b>82CC4470(1)30(2)</b> | <b>R82CC4470(1)30(2)</b> |
| 63        | 40        | 0.10                   | 2.5              | 6.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3100(1)50(2)        | R82DC3100(1)50(2)        |
| 63        | 40        | 0.15                   | 2.5              | 6.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3150(1)60(2)        | R82DC3150(1)60(2)        |
| 63        | 40        | 0.22                   | 2.5              | 6.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3220(1)60(2)        | R82DC3220(1)60(2)        |
| 63        | 40        | 0.33                   | 3.5              | 7.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3330(1)60(2)        | R82DC3330(1)60(2)        |
| 63        | 40        | 0.47                   | 3.5              | 7.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3470(1)60(2)        | R82DC3470(1)60(2)        |
| 63        | 40        | 0.68                   | 4.5              | 9.5         | 7.2        | 5.0          | 160          | 20160                                       | 82DC3680(1)60(2)        | R82DC3680(1)60(2)        |
| 63        | 40        | 1.0                    | 5.0              | 10.0        | 7.2        | 5.0          | 160          | 20160                                       | 82DC4100(1)60(2)        | R82DC4100(1)60(2)        |
| 63        | 40        | 1.5                    | 6.0              | 11.0        | 7.2        | 5.0          | 160          | 20160                                       | 82DC4150(1)60(2)        | R82DC4150(1)60(2)        |
| 100       | 63        | 0.0010                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1100(1)50(2)        | R82EC1100(1)50(2)        |
| 100       | 63        | 0.0015                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1150(1)50(2)        | R82EC1150(1)50(2)        |
| 100       | 63        | 0.0022                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1220(1)50(2)        | R82EC1220(1)50(2)        |
| 100       | 63        | 0.0033                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1330(1)50(2)        | R82EC1330(1)50(2)        |
| 100       | 63        | 0.0047                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1470(1)50(2)        | R82EC1470(1)50(2)        |
| 100       | 63        | 0.0068                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC1680(1)50(2)        | R82EC1680(1)50(2)        |
| 100       | 63        | 0.010                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2100(1)50(2)        | R82EC2100(1)50(2)        |
| 100       | 63        | 0.015                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2150(1)50(2)        | R82EC2150(1)50(2)        |
| 100       | 63        | 0.022                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2220(1)50(2)        | R82EC2220(1)50(2)        |
| 100       | 63        | 0.033                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2330(1)50(2)        | R82EC2330(1)50(2)        |
| 100       | 63        | 0.047                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2470(1)60(2)        | R82EC2470(1)60(2)        |
| 100       | 63        | 0.068                  | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC2680(1)60(2)        | R82EC2680(1)60(2)        |
| 100       | 63        | 0.10                   | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC3100(1)70(2)        | R82EC3100(1)70(2)        |
| 100       | 63        | 0.15                   | 3.5              | 7.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC3150(1)70(2)        | R82EC3150(1)70(2)        |
| 100       | 63        | 0.22                   | 3.5              | 7.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC3220(1)70(2)        | R82EC3220(1)70(2)        |
| 100       | 63        | 0.33                   | 4.5              | 9.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC3330(1)70(2)        | R82EC3330(1)70(2)        |
| 100       | 63        | 0.47                   | 4.5              | 9.5         | 7.2        | 5.0          | 200          | 40000                                       | 82EC3470(1)70(2)        | R82EC3470(1)70(2)        |
| 100       | 63        | 0.68                   | 5.0              | 10.0        | 7.2        | 5.0          | 200          | 40000                                       | 82EC3680(1)70(2)        | R82EC3680(1)70(2)        |
| 100       | 63        | 1.00                   | 6.0              | 11.0        | 7.2        | 5.0          | 200          | 40000                                       | 82EC4100(1)70(2)        | R82EC4100(1)70(2)        |
| 250       | 140       | 0.022                  | 2.5              | 6.5         | 7.2        | 5.0          | 130          | 65000                                       | 82IC2220(1)6(2)         | R82IC2220(1)6(2)         |
| 250       | 140       | 0.047                  | 3.5              | 7.5         | 7.2        | 5.0          | 130          | 65000                                       | 82IC2470(1)6(2)         | R82IC2470(1)6(2)         |
| 250       | 140       | 0.068                  | 3.5              | 7.5         | 7.2        | 5.0          | 130          | 65000                                       | 82IC2680(1)6(2)         | R82IC2680(1)6(2)         |
| 250       | 140       | 0.10                   | 4.5              | 9.5         | 7.2        | 5.0          | 130          | 65000                                       | 82IC3100(1)6(2)         | R82IC3100(1)6(2)         |
| 250       | 140       | 0.15                   | 5.0              | 10.0        | 7.2        | 5.0          | 130          | 65000                                       | 82IC3150(1)6(2)         | R82IC3150(1)6(2)         |
| 250       | 140       | 0.22                   | 6.0              | 11.0        | 7.2        | 5.0          | 130          | 65000                                       | 82IC3220(1)6(2)         | R82IC3220(1)6(2)         |
| 250       | 160       | 0.0068                 | 2.5              | 6.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC1680(1)50(2)        | R82IC1680(1)50(2)        |
| 250       | 160       | 0.010                  | 2.5              | 6.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2100(1)5(2)         | R82IC2100(1)5(2)         |
| 250       | 160       | 0.015                  | 2.5              | 6.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2150(1)5(2)         | R82IC2150(1)5(2)         |
| 250       | 160       | 0.022                  | 3.5              | 7.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2220(1)5(2)         | R82IC2220(1)5(2)         |
| 250       | 160       | 0.033                  | 3.5              | 7.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2330(1)5(2)         | R82IC2330(1)5(2)         |
| 250       | 160       | 0.047                  | 4.5              | 9.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2470(1)5(2)         | R82IC2470(1)5(2)         |
| 250       | 160       | 0.068                  | 4.5              | 9.5         | 7.2        | 5.0          | 250          | 125000                                      | 82IC2680(1)5(2)         | R82IC2680(1)5(2)         |
| 250       | 160       | 0.10                   | 5.0              | 10.0        | 7.2        | 5.0          | 250          | 125000                                      | 82IC3100(1)55(2)        | R82IC3100(1)55(2)        |
| 250       | 160       | 0.15                   | 6.0              | 11.0        | 7.2        | 5.0          | 250          | 125000                                      | 82IC3150(1)5(2)         | R82IC3150(1)5(2)         |
| 400       | 160       | 0.0068                 | 2.5              | 6.5         | 7.2        | 5.0          | 200          | 160000                                      | 82MC1680(1)6(2)         | R82MC1680(1)6(2)         |
| 400       | 160       | 0.015                  | 3.5              | 7.5         | 7.2        | 5.0          | 200          | 160000                                      | 82MC2150(1)6(2)         | R82MC2150(1)6(2)         |
| 400       | 160       | 0.033                  | 4.5              | 9.5         | 7.2        | 5.0          | 200          | 160000                                      | 82MC2330(1)6(2)         | R82MC2330(1)6(2)         |
| 400       | 160       | 0.047                  | 5.0              | 10.0        | 7.2        | 5.0          | 200          | 160000                                      | 82MC2470(1)6(2)         | R82MC2470(1)6(2)         |
| 400       | 160       | 0.068                  | 6.0              | 11.0        | 7.2        | 5.0          | 200          | 160000                                      | 82MC2680(1)6(2)         | R82MC2680(1)6(2)         |
| 400       | 200       | 0.0010                 | 2.5              | 6.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1100(1)5(2)         | R82MC1100(1)5(2)         |
| 400       | 200       | 0.0015                 | 2.5              | 6.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1150(1)5(2)         | R82MC1150(1)5(2)         |
| 400       | 200       | 0.0022                 | 2.5              | 6.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1220(1)5(2)         | R82MC1220(1)5(2)         |
| 400       | 200       | 0.0033                 | 2.5              | 6.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1330(1)5(2)         | R82MC1330(1)5(2)         |
| 400       | 200       | 0.0047                 | 2.5              | 6.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1470(1)5(2)         | R82MC1470(1)5(2)         |
| 400       | 200       | 0.0068                 | 3.5              | 7.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC1680(1)5(2)         | R82MC1680(1)5(2)         |
| 400       | 200       | 0.010                  | 3.5              | 7.5         | 7.2        | 5.0          | 400          | 320000                                      | 82MC2100(1)5(2)         | R82MC2100(1)5(2)         |

(1) Insert lead and packaging code. See Ordering Options Table for available options.

(2) J = 5%, K = 10%, M = 20%

**Bold denotes wound capacitor technology**

**Table 1 – Ratings & Part Number Reference**

| VDC | VAC | Capacitance Value (μF) | Dimensions in mm |        |        | Lead Spacing | dV/dt (V/μs) | Maximum $K_0$ (V <sup>2</sup> /μs) | New KEMET Part Number | Legacy Part Number |
|-----|-----|------------------------|------------------|--------|--------|--------------|--------------|------------------------------------|-----------------------|--------------------|
|     |     |                        | B                | H      | L      |              |              |                                    |                       |                    |
| 400 | 200 | 0.015                  | 4.5              | 9.5    | 7.2    | 5.0          | 400          | 320000                             | 82MC2150(1)5(2)       | R82MC2150(1)5(2)   |
| 400 | 200 | 0.022                  | 4.5              | 9.5    | 7.2    | 5.0          | 400          | 320000                             | 82MC2220(1)5(2)       | R82MC2220(1)5(2)   |
| 400 | 200 | 0.033                  | 5.0              | 10.0   | 7.2    | 5.0          | 400          | 320000                             | 82MC2330(1)5(2)       | R82MC2330(1)5(2)   |
| 400 | 200 | 0.047                  | 6.0              | 11.0   | 7.2    | 5.0          | 400          | 320000                             | 82MC2470(1)5(2)       | R82MC2470(1)5(2)   |
| VDC | VAC | Capacitance Value (μF) | B (mm)           | H (mm) | L (mm) | Lead Spacing | dV/dt (V/μs) | Max $K_0$ (V <sup>2</sup> /μs)     | New KEMET Part Number | Legacy Part Number |

(1) Insert lead and packaging code. See Ordering Options Table for available options.

(2) J = 5%, K = 10%, M = 20%

## Soldering Process

The implementation of the RoHS directive has resulted in the selection of SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 mm to 15 mm), and great care has to be taken during soldering. The recommended solder profiles from KEMET should be used. Please consult KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760-1 Edition 2 serves as a solid guideline for successful soldering. Please see Figure 1.


Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the above the recommended limits may result to degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after the curing of surface mount parts. Consult KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Please allow time for the capacitor surface temperature to return to a normal temperature before the second soldering cycle.

**Figure 1**


| Dielectric<br>Film Material | Maximum Preheat<br>Temperature         |                                         |                                        | Maximum<br>Peak Soldering<br>Temperature |                                        |
|-----------------------------|----------------------------------------|-----------------------------------------|----------------------------------------|------------------------------------------|----------------------------------------|
|                             | Capacitor<br>Lead<br>Spacing<br><10 mm | Capacitor<br>Lead<br>Spacing =<br>15 mm | Capacitor<br>Lead<br>Spacing<br>>15 mm | Capacitor<br>Lead<br>Spacing<br><15 mm   | Capacitor<br>Lead<br>Spacing<br>>15 mm |
| Polyester                   | 130°C                                  | 130°C                                   | 130°C                                  | 270°C                                    | 270°C                                  |
| Polypropylene               | 100°C                                  | 110°C                                   | 130°C                                  | 260°C                                    | 270°C                                  |
| Polyphenylene<br>Sulphide   | 150°C                                  | 150°C                                   | 160°C                                  | 270°C                                    | 270°C                                  |

## Wave Soldering Recommendations



## Manual Soldering Recommendations

Following is the recommendation for manual soldering with a soldering iron.



The soldering iron tip temperature should be set at 350°C (+10°C maximum) with the soldering duration not to exceed more than 3 seconds.

## Soldering Process cont'd

### Selective Soldering Recommendations

Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is preheated and transported over the solder bath as in normal flow soldering without touching the solder. When the board is over the bath, it is stopped and pre-designed solder pots are lifted from the bath with molten solder only at the places of the selected components, and pressed against the lower surface of the board to solder the components.

The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document, **however, instead of two baths, there is only one bath with a time from 3 to 10 seconds.** In selective soldering, the risk of overheating is greater than in double wave flow soldering, and great care must be taken so that the parts are not overheated.

## Marking

- KEMET's logo
- Capacitance
- Capacitance tolerance
- Rated DC voltage

## Packaging Quantities

| Lead Spacing | Thickness (mm) | Height (mm) | Length (mm) | Bulk Short Leads | Bulk Long Leads | Standard Reel 355 mm | Ammo Taped |
|--------------|----------------|-------------|-------------|------------------|-----------------|----------------------|------------|
| 5            | 2.5            | 6.5         | 7.2         | 3,000            | 4,000           | 2,500                | 3,500      |
|              | 3.5            | 7.5         | 7.2         | 2,000            | 3,000           | 1,800                | 2,500      |
|              | 4.5            | 9.5         | 7.2         | 1,500            | 2,000           | 1,400                | 1,900      |
|              | 5.0            | 10.0        | 7.2         | 1,000            | 1,500           | 1,200                | 1,700      |
|              | 6.0            | 11.0        | 7.2         | 2,000            | 1,000           | 1,000                | 1,400      |
|              | 7.2            | 13.0        | 7.2         | 1,500            | 750             | 800                  | 1,150      |

## Lead Taping & Packaging (IEC 60286-2)

Figure 1 – Lead Space 5 & 7.5 mm





Figure 2 – Lead Space 7.5 mm



| Description                          | Symbol            | Dimensions (mm) |          |          |           |
|--------------------------------------|-------------------|-----------------|----------|----------|-----------|
|                                      |                   | Lead Spacing    |          |          | Tolerance |
|                                      |                   | 5               | 7.5      | 7.5      |           |
|                                      |                   | Figure 1        | Figure 1 | Figure 2 |           |
| Lead wire diameter                   | d                 | 0.5–0.6         | 0.5–0.6  | 0.5–0.6  | ±0.05     |
| Taping lead space                    | P                 | 12.7            | 12.7     | 12.7     | ±1        |
| Feed hole lead space                 | P <sub>0</sub>    | 12.7            | 12.7     | 12.7     | ±0.2*     |
| Centering of the lead wire           | P <sub>1</sub>    | 3.85            | 2.6      | 3.75     | ±0.7      |
| Centering of the body                | P <sub>2</sub>    | 6.35            | 6.35     |          | ±1.3      |
| Lead spacing                         | F                 | 5               | 7.5      | 7.5      | +0.6 -0.1 |
| Component alignment                  | Δh                | 0               | 0        | 0        | ±2        |
| Height of component from tape center | H <sub>0</sub> ** | 18.5            | 18.5     | 18.5     | ±0.5      |
| Carrier tape width                   | W                 | 18              | 18       | 18       | +1 -0.5   |
| Hold down tape width                 | W <sub>0</sub>    | 6               | 6        | 6        | minimum   |
| Hole position                        | W <sub>1</sub>    | 9               | 9        | 9        | ±0.5      |
| Hold down tape position              | W <sub>2</sub>    | 3               | 3        | 3        | maximum   |
| Feed hole diameter                   | D <sub>0</sub>    | 4               | 4        | 4        | ±0.2      |
| Tape thickness                       | t                 | 0.7             | 0.7      | 0.7      | ±0.2      |

\*Maximum 1 mm on 20 lead spaces.


\*\*H<sub>0</sub> = 16.5 mm is available upon request.

For orders of capacitors with lead space = 7.5 mm, please specify the requested version (Figure 1 or Figure 2).

## Ammo Specifications



| Dimensions in mm |     |    |
|------------------|-----|----|
| H                | W   | T  |
| 360 *            | 340 | 59 |

\* Lower dimension available upon request (maximum 295 mm)



## Reel Specifications

| Dimensions in mm |    |            |
|------------------|----|------------|
| D                | H  | W          |
| 355              | 30 | 55 maximum |



## KEMET Corporation World Headquarters

2835 KEMET Way  
Simpsonville, SC 29681

Mailing Address:  
P.O. Box 5928  
Greenville, SC 29606

www.kemet.com  
Tel: 864-963-6300  
Fax: 864-963-6521

**Corporate Offices**  
Fort Lauderdale, FL  
Tel: 954-766-2800

## North America

**Southeast**  
Lake Mary, FL  
Tel: 407-855-8886

**Northeast**  
Wilmington, MA  
Tel: 978-658-1663

**Central**  
Novi, MI  
Tel: 248-306-9353

**West**  
Milpitas, CA  
Tel: 408-433-9950

**Mexico**  
Guadalajara, Jalisco  
Tel: 52-33-3123-2141

## Europe

**Southern Europe**  
Paris, France  
Tel: 33-1-4646-1006

Sasso Marconi, Italy  
Tel: 39-051-939111

**Central Europe**  
Landsberg, Germany  
Tel: 49-8191-3350800

Kamen, Germany  
Tel: 49-2307-438110

**Northern Europe**  
Bishop's Stortford, United Kingdom  
Tel: 44-1279-460122

Espoo, Finland  
Tel: 358-9-5406-5000

## Asia

**Northeast Asia**  
Hong Kong  
Tel: 852-2305-1168

Shenzhen, China  
Tel: 86-755-2518-1306

Beijing, China  
Tel: 86-10-5829-1711

Shanghai, China  
Tel: 86-21-6447-0707

Taipei, Taiwan  
Tel: 886-2-27528585

**Southeast Asia**  
Singapore  
Tel: 65-6586-1900

Penang, Malaysia  
Tel: 60-4-6430200

Bangalore, India  
Tel: 91-806-53-76817

*Note: KEMET reserves the right to modify minor details of internal and external construction at any time in the interest of product improvement. KEMET does not assume any responsibility for infringement that might result from the use of KEMET Capacitors in potential circuit designs. KEMET is a registered trademark of KEMET Electronics Corporation.*

## Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.