

# Electronic Training Equipment & Breadboard / Accessories



## Power Project Board

136259/PP272-ROHS



### PP-272 Power Project Board

#### Specifications

1. DC power +5 V/1 A  
Variable power 0 ~  $\pm 15$  V/500 mA with short circuit protection
2. Solderless breadboard RH-53 interconnected 2420 tie points
3. Edge plate :  
EP-3 edge plate for the best placement of non-dip size components
4. Power switch with light
5. AC 110 V/220 V, 120 V/240 V, 50/60 Hz
6. Dimension :  
Main body 250 x 200 x 80 mm, With box 305 x 235 x 85 mm
7. Weight : 2.5 Kg