



DM78C Digital Multi-Tester

- Smallest, go anywhere meter
- 5 functions/16 ranges
- Auto-off saves batteries
- Data Hold
- Protective case included
- 3200-count display with analog bargraph

No hassle warranty

No waiting.

*No shipping
charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

Included Accessories

Pocket carrying case, test leads, battery, and users manual.





DM78C Digital Multi-Tester

Data Sheet

General Specifications

Display:	3¾ digits LCD, max reading 3400
Range selection:	Autoranging and manual range lock
Overrange indication:	OL
Polarity indication:	- is displayed; + is implied
Battery warning:	⚡ displayed when $<1.25\text{ V} \pm 0.1\text{ V}$
Sampling rate:	2/sec display. 20/sec bargraph
Environment:	Indoor operation, 2000 m (6561 ft) max
Temperature/Humidity:	Operation: $0\text{ }^{\circ}\text{C}$ to $40\text{ }^{\circ}\text{C}$ ($32\text{ }^{\circ}\text{F}$ to $104\text{ }^{\circ}\text{F}$), $<70\%$ RH non-condensing Storage: $-20\text{ }^{\circ}\text{C}$ to $60\text{ }^{\circ}\text{C}$ ($-4\text{ }^{\circ}\text{F}$ to $140\text{ }^{\circ}\text{F}$), $<80\%$ RH non-condensing
Battery type:	Two 1.5 V (L1154F or LR-44)
Battery life:	70 hours continuous operation
Continuity test:	Beeper alert
Auto-OFF:	After 10 minutes of non-use
Dimensions (H x W x D):	130 x 77 x 18 mm (5.1" x 3.1" x 0.6")
Weight (including battery):	110 g (3.9 oz) including case

Specifications $23\text{ }^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$, 80 % RH Max; Maximum input, all functions/ranges: 600 VDC or AC rms

Function	Range	Accuracy
DC Voltage		
340 mV, 3.4, 34, 340, 600 V	3.4 V range	$\pm 1.0\%$ rdg + 2 dgts
	All other ranges	$\pm 2.0\%$ rdg. + 2 dgts
Resolution	100 μV in 340 mV range	
Input Impedance	340 mV range: $> 100\text{ M}\Omega$	
	3.4 V range: $10\text{ M}\Omega$	
	All other ranges: $9.1\text{ M}\Omega$	
AC Voltage (50~60 Hz)		
	3.4, 34, 340, 600 V	$\pm 4.0\%$ rdg. + 5 dgts
Resolution	1 mV in 3.4 V range	
Input Impedance	3.4 V range: $10\text{ M}\Omega$	
	All other ranges: $9.1\text{ M}\Omega$	
Resistance		
Ranges	340 Ω , 3.4, 34, 340 k Ω , 3.4, 34 M Ω	
Resolution	100 m Ω in 340 Ω range	
	340 Ω , 3.4, 34, 340 k Ω ranges:	$\pm 2.0\%$ rdg + 4 dgts
	3.4 M Ω range:	$\pm 3.0\%$ rdg + 4 dgts
	34 M Ω range:	$\pm 5.0\%$ rdg + 5 dgts
Test Voltage	-0.45 Vdc typical (-1.2 Vdc on 340 Ω rng)	
Diode Test		
Range	3.4 V	$\pm 3.0\%$ rdg + 3 dgts
Test Current	0.6 mA ($V_f = 0.6\text{ V}$)	
Continuity Check		
Range	340 Ω	
Indication	at approx $R < 35\text{ }\Omega$	
Test Current	0.7 mA	

Amprobe® Test Tools
website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe
In den Engematten 14
79286 Glottental, Germany
Tel.: +49 (0) 7684 8009 - 0

©2008 Amprobe Test Tools. All rights reserved.
3/2008 1646641 D-US-N Rev C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[DM78C](#)