




REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	05/25/06	HO	05/25/06



NOTE:

1. CABLE:


[28AWG(7/0.127)x1P+DRAIN(7/0.127)+AL/MY+MY]x4C+28AWG(7/0.127)x1P+28AWG(7/0.127)x3C+AL/MY+AL+85%(24/8/0.12)BRAID]TIN
INSULATION(A): Foam-PE, OD=ø0.95±0.05mm, UL-1598, COLOR: SEE WIRE LIST
INSULATION(B): HD-PE, OD=ø0.70±0.05mm, UL1598, COLOR: SEE WIRE LIST
INSULATION(C): HD-PE, OD=ø0.70±0.05mm, UL1598, COLOR: SEE WIRE LIST
JACKET: PVC, OD=ø7.3±0.15mm, UL20276, COLOR: BLACK
PRINT(FOR PI): "PAN-INTERNATIONAL 20276 E87647 AWM 80°C 30V VW-1" U

2. 100% TEST OPEN\SHORT\MISWIRE

3. SPECIFICATION SAME AS DIGITAL VISUAL INTERFACE VER:1.0

WIRE LIST

J1	GROPE	COLOR	J2
1	TROOP A(1)	GREEN	1
2		WHITE	2
3		DRAIN	3
6	TROOP B(5)	ORANGE	6
7		YELLOW	7
9	TROOP A(2)	BLUE	9
10		WHITE	10
11	TROOP C(7)	DRAIN	11
14		WHITE	14
15		RED	15
16	TROOP C(8)	PURPLE	16
17	TROOP A(3)	BROWN	17
18		WHITE	18
19		DRAIN	19
22	TROOP A(4)	DRAIN	22
23		RED	23
24	SHELL	WHITE	24
		BRAID	SHELL



SPC TYPE No.	LENGTH
SPC19948	72±1 [1829±25.4]
SPC19947	120±2 [3048±50.8]

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
EKLAS ODISH	04/17/06
CHECKED BY:	DATE:
THOMAS LEE	05/25/06
APPROVED BY:	DATE:
HISHAM ODISH	05/25/06

DRAWING TITLE:

Digital Video Interface (DVD) Cable M/M, Single Link

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-732	TA-732.DWG	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	